


PIDG

TE Internal #: 35109 Closed Ring Tongue Terminal, 12 – 10 AWG, #10 Stud Size, 5 mm [. 197 in] Stud Diameter, Closed Barrel, Straight, Tin, Partially Insulated, PIDG

View on TE.com >

Terminals & Splices > Ring Terminals > PIDG Ring Tongue Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 5180 – 13100 CMA

Stud Size: **#10**

All PIDG Ring Tongue Terminals (411)





Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal #10				
Stud Size					
Sealable	No				
Wire Insulation Support Retention Type	Insulation Support				
Configuration Features					
Number of Holes	1				
Electrical Characteristics					
Voltage Rating	300 V				
Body Features					
Product Weight	2.24 g				
Contact Features					
Military Part Class	Class I				
Barrel Type	Closed				

Closed Ring Tongue Terminal, 12 – 10 AWG, #10 Stud Size, 5 mm [.197 in] Stud Diameter, Closed Barrel, Straight, Tin, Partially Insulated, PIDG



Terminal Orientation	Straight				
Terminal Plating Material	Tin				
Mechanical Attachment					
Wire Insulation Support	With				
Dimensions					
Wire Size	5180 – 13100 CMA				
Stud Diameter	5 mm[.197 in]				
Tongue Thickness	.99 mm[.039 in]				
Product Length	27.51 mm[1.08 in]				
Compatible Insulation Diameter (Max)	6.35 mm[.25 in]				
Compatible Insulation Diameter Range	3.81 – 6.35 mm[.15 – .25 in]				
Usage Conditions					
Insulation Option	Partially Insulated				
Operating Temperature Range	105 °C[221 °F]				
Operation/Application					
Compatible With Wire Base Material	Copper				
Compatible With Wire Plating Material	Tin				

Industry Standards

Government Qualified Terminal	Yes
Packaging Features	
Packaging Quantity	500
Packaging Method	Loose Piece
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC

Closed Ring Tongue Terminal, 12 – 10 AWG, #10 Stud Size, 5 mm [.197 in] Stud Diameter, Closed Barrel, Straight, Tin, Partially Insulated, PIDG



Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



Closed Ring Tongue Terminal, 12 – 10 AWG, #10 Stud Size, 5 mm [.197 in] Stud Diameter, Closed Barrel, Straight, Tin, Partially Insulated, PIDG






Also in the Series | PIDG



Knife Disconnects(11)	PCB Terminals(5)	Quick Disconnects(47)	Ring Terminals(589)



Customers Also Bought



Closed Ring Tongue Terminal, 12 – 10 AWG, #10 Stud Size, 5 mm [.197 in] Stud Diameter, Closed Barrel, Straight, Tin, Partially Insulated, PIDG



TE Part #MC300E2-N-19-5PN TE Part #1520231-1 RECEPTACLE ASSY.PIN MC3/2 7410K4=20 AMP TOGGLE FLUSH MOU

Documents

CAD Files

Customer View Model ENG_CVM_CVM_35109_V.2d_dxf.zip

English

3D PDF

3D

Customer View Model ENG_CVM_CVM_35109_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_35109_V.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use

Datasheets & Catalog Pages PIDG TERMINALS & SPLICES Quick Reference Guide

English

Product Specifications Application Specification

English

Agency Approvals

UL Report

English

UL Report

English