OMRON ELECTRONICS

See full Datasheet below...



BUY NOW



BUY NOW

masterelectronics.com & onlinecomponents.com are **authorized** e-commerce distributors of electronic components.



General Purpose Relay

G7L

- A high-capacity, high-withstand voltage relay compatible with mometary voltage drops
- No contact chattering for mometary voltage drops up to 50% of rated voltage
- UL Class B construction standard
- Wide-range AC-activated coil that handles 100 to 120 VAC at either 50 or 60 Hz
- Miniature hinge for maximum switching capacity, particularly for inductive loads
- Flame resistant materials (UL94V-0-qualifying) used for all insulation material
- Quick-connect, screw, and PCB terminals available
- Standard models are UL, CSA, and TUV approved; VDE versions now available
- Conforming to IEC 950





Ordering Information

To Order: Select the part number and add the desired coil voltage rating (e.g., G7L-1A-T-CB-*AC100/120*). Replaces G5D series.

		Part number			
Туре	Contact form	Quick-connect terminal	Screw terminal	PCB terminal	
E bracket	SPST-NO	G7L-1A-T-CB (see note 1)	G7L-1A-B-CB (see note 1)	I —	
	DPST-NO	G7L-2A-T-CB (see note 1)	G7L-2A-B-CB (see note 1)	I —	
E bracket	SPST-NO	G7L-1A-TJ-CB (see note 1)	G7L-1A-BJ-CB (see note 1)	I —	
(with test button)	DPST-NO	G7L-2A-TJ-CB (see note 1)	G7L-2A-BJ-CB (see note 1)	I —	
Upper bracket	SPST-NO	G7L-1A-TUB-CB	G7L-1A-BUB-CB	I —	
	DPST-NO	G7L-2A-TUB-CB	G7L-2A-BUB-CB	I —	
Upper bracket	SPST-NO	G7L-1A-TUBJ-CB	G7L-1A-BUBJ-CB	I —	
(with test button)	DPST-NO	G7L-2A-TUBJ-CB	G7L-2A-BUBJ-CB	I —	
PCB mounting	SPST-NO	_	_	G7L-1A-P-CB	
	DPST-NO	_	_	G7L-2A-P-CB	

Note: 1. E bracket or socket must be used for mounting (part number R99-07G5D). Refer to "Accessories" section for options and part numbers.

2. For VDE approved versions, please consult OMRON.



OMRON G7L

■ MODEL NUMBER LEGEND

G7L- \square \square \square \square \square \square 1 2 3 4 5 6

1. Contact form

1A: SPST-NO 2A: DPST-NO

2. Terminal shape

Quick-connect terminals T:

PCB terminals P: B: Screw terminals

3. Mounting construction

No symbol: E bracket type UB: Upper bracket type

4. Special functions

No symbol: Without test button With test button J:

5. 80: VDE approved version (includes UL, CSA and TÜV)

6. CB: Class B insulation

7. Rated coil voltage

■ ACCESSORIES

Quick-connect terminals

	Model				
	Contact form				
Description	SPST-NO		DPST-NO		Part number
E-brackets	G7L-1A-T	G7L-1A-TJ	G7L-2A-T	G7L-2A-TJ	R99-07G5D
Track mounting adaptor					P7LF-D
Front connecting socket					P7LF-06 (see note)
Cover					P7LF-C

Screw terminals

	Model					
	Contact form					
Description	SPST-NO		DPST-NO		Part number	
E-brackets	G7L-1A-B	G7L-1A-BJ	G7L-2A-B	G7L-2A-BJ	R99-07G5D	
Track mounting adaptor					P7LF-D	

Note: P7LF-C cover is supplied with the P7LF-06 socket.

Specifications

■ CONTACT DATA


	G7L-1A-T, G7L-1A-B		G7L-2A-T, G7L-2A-B		G7L-1A-P, G7L-2A-P	
Load	Resistive load (cosφ = 1)	Inductive load (cosφ = 0.4)	Resistive load (cosφ = 1)	Inductive load (cosφ = 0.4)	Resistive load (cosφ = 1)	Inductive load (cosφ = 0.4)
Rated load	30 A, 220 VAC	25 A, 220 VAC		20 A, 220 VAC		
Contact material	AgCdO					
Carry current	30 A		25 A		20 A	
Max. operating voltage	250 VAC	250 VAC				
Max. operating current	30 A		25 A		20 A	
Max. switching capacity	6,600 VA	5,500 VA			4,400 VA	
Min. permissible load	100 mA, 5 VDC					


Note: P level: $\lambda_{60} = 0.1 \times 10^{-6}$ operation.

■ COIL INTERNAL CIRCUIT

DC operating coil

AC operating coil







G7L ______ G7L

■ COIL DATA

AC

Rated voltage	Rated current	Resistance	Must operate	Must release	Max. voltage	Power
(V)	(mA)	(Ω)	% of rated volt	% of rated voltage		
6	283	18.90	75% max.	15% min.	110% max.	Approx.1.70
12	142	75				to 2.50 VA
24	71	303				
50	34	1,310				
100/120	17.00/20.40	5,260	75 volts	18 volts	132 volts]
200/240	8.50/10.20	21,000	150 volts	36 volts	264 volts	1

DC

Rated voltage	Rated current	Resistance	Must operate	Must release	Max. voltage	Power
(V)	(mA)	(Ω)	% of rated volta	age		consumption
6	317	18.90	75% max.	15% min.	110% max.	Approx.1.90 W
12	158	75				
24	79	303			1	
48	40	1,220				
100	19	5,260				

Note: 1. The rated current and coil resistance are measured at a coil temperature of 23°C (73°F) with tolerances of +15%/-20% for AC rated current and ±15% for DC coil resistance.

2. Performance characteristic data are measured at a coil temperature of 23°C (73°F).

■ CHARACTERISTICS


Contact resistance		50 m $Ω$ max.		
Operate time		30 ms max.		
Release time		30 ms max.		
Max. operating Mechanical		1,800 operations/hour		
frequency	Electrical	1,800 operations/hour (under rated load)		
Insulation resistance		1,000 MΩ min. (at 500 VDC)		
Dielectric strength		4,000 VAC, min./5,000 VAC typical, 50/60 Hz for 1 minute between coil and contacts		
		2,000 VAC, 50/60 Hz for 1 minute between contacts of same pole		
		2,000 VAC, 50/60 Hz for 1 minute between contacts of different poles (DPST-NO type)		
Impulse withstand volt	age	Between coil and contact: 10,000 V (impulse wave used: 1.20 x 50 μs)		
Vibration	Mechanical durability	10 to 55 Hz; 1.50 mm (0.06 in) double amplitude		
	Malfunction durability	10 to 55 Hz; 1.50 mm (0.06 in) double amplitude		
Shock	Mechanical durability	1,000 m/s ² (approx. 100 G)		
	Malfunction durability	1,000 m/s ² (approx.10 G)		
Life expectancy	Mechanical	5,000,000 operations min. (at 1,800 operations/hour)		
	Electrical	100,000 operations min. (at 1,800 operations/hour under rated load)		
Ambient temperature		-20° to 85°C (-4° to 185°F)		
Humidity		35% to 85% RH		
Weight		Quick-connect terminal type: approx. 90 g (3.17 oz)		
		PCB terminal type: approx. 100 g (3.52 oz)		
		Screw terminal type: approx. 120 g (4.23 oz)		

Note: Data shown are of initial value.


OMRON G7L === _____ G7L

■ CHARACTERISTIC DATA

Maximum switching capacity



Electrical service life




Switching current (A)


Dimensions_

Unit: mm (inch)

■ RELAYS

G7L-1A-T (E Bracket Attached)*






Terminal arrangement/ Internal connections (Top view)




Mounting holes (Bottom view)



G7L-2A-T (E Bracket Attached)





Terminal arrangement/ Internal connections (Top view)




Mounting holes




^{*} E bracket must be ordered separately.

OMRON G7L = - G7L

G7L-1A-TJ (E Bracket Attached)*







Terminal arrangement/ Internal connections (Top view)




Mounting holes (Bottom view)



G7L-2A-TJ (E Bracket Attached)*






Terminal arrangement/ Internal connections (Top view)




Mounting holes


(Bottom view)



G7L-1A-TUB



Terminal arrangement/ Internal connections (Top view)




Mounting holes


(Bottom view)




G7L-2A-TUB



Terminal arrangement/ Internal connections (Top view)



Mounting holes




^{*} E bracket must be ordered separately.

G7L ______ OMRON _____ G7L


Unit: mm (inch)

■ RELAYS (continued)

G7L-1A-TUBJ




Terminal arrangement/ Internal connections (Top view)




Mounting holes (Bottom view)



G7L-2A-TUBJ



Terminal arrangement/ Internal connections (Top view)





Mounting holes (Bottom view)

Two 4.5 (.177) dia. holes or M4 tapped holes

- 60±.20 (2.362±.007)

G7L-1A-B (E bracket Attached)*






Terminal arrangement/ Internal connections (Top view)





Mounting holes

(Bottom view)



G7L-2A-B (E bracket Attached)*





Terminal arrangement/ Internal connections (Top view)


Mounting holes




^{*} E bracket must be ordered separately.

G7L ______ OMRON _____ G7L

G7L-1A-BJ (E bracket Attached)*






Terminal arrangement/ Internal connections (Top view)




Mounting holes (Bottom view)



G7L-2A-BJ (E bracket Attached)*







Terminal arrangement/ Internal connections (Top view)




Mounting holes (Bottom view)



G7L-1A-BUB




Terminal arrangement/ Internal connections (Top view)



Mounting holes (Bottom view)




G7L-2A-BUB




Terminal arrangement/ Internal connections

(Top view)



Mounting holes




^{*} E bracket must be ordered separately.

OMRON G7L = = G7L


Unit: mm (inch)

■ RELAYS (continued)


G7L-1A-BUBJ




Terminal arrangement/ Internal connections (Top view)




Mounting holes (Bottom view)




G7L-2A-BUBJ






Terminal arrangement/ Internal connections (Top view)




Mounting holes

(Bottom view)



G7L-1A-P




Terminal arrangement/ Internal connections (Top view)




Mounting holes

(Bottom view)



G7L-2A-P




Terminal arrangement/ Internal connections

(Top view)



Mounting holes







G7L ______ G7L

■ ACCESSORIES

E bracket R99-07G5D









Mounting holes (Bottom view)




Adaptor P7LF-D









Mounting holes (Bottom view)




Front connecting socket P7LF-06





Mounting holes (Bottom view)




- Note: 1. To protect against electric shock, use the P7LF-C cover on terminals.
 - 2. P7LF-C cover is supplied with P7LF-06 socket

G7L ______ G7L

Unit: mm (inch)

■ ACCESSORIES (continued)


Cover P7LF-C



Note: P7LF-C cover is supplied with P7LF-06 socket


Mounting track


PFP-100N, PFP-50N





PFP-100N2






Note: 1. It is recommended that a panel thickness of 1.60 to 2.00 mm (0.06 to 0.08 in) be used.


2. L = Length

PFP-100N L = 1 m (39.00 in) PFP-50N L = 50 cm (19.60 in) PFP-100N2 L = 1 m (39.00 in)

End plate PFP-M



Spacer PFP-S





G7L ______ OMRON _____ G7L

■ APPROVALS

UL recognized type (File No. E41643)/ CSA certified type (File No. LR35535)

Туре	Contact form	Terminal type	Contact ratings
G7L-1A-T-CB	SPST-NO	Quick-connect	30 A, 277 VAC (Resistive) 30,000 c
G7L-1A-TJ-CB			30 A, 120 VAC (General purpose) 30,000 c
G7L-1A-TUB-CB			30 A, 277 VAC (General purpose) 30,000 c
G7L-1A-TUBJ-CB			1.5 kW, 120 VAC (Tungsten)
G7L-1A-B-CB		Screw	1.5 HP, 120 VAC
G7L-1A-BJ-CB			3 HP, 240/265/277 VAC
G7L-1A-BUB-CB			20 FLA/120 LRA, 120 VAC, 30,000 c
G7L-1A-BUBJ-CB			17 FLA/102 LRA, 277 VAC, 30,000 c
G7L-1A-P-CB		PCB	TV-10, 120 VAC
			20 A (2.4 kW), 120 VAC (Tungsten)
G7L-2A-T-CB	DPST-NO	Quick-connect	30 A, 277 VAC (Resistive) 30,000 c
G7L-2A-TJ-CB			30 A, 120 VAC (General purpose) 30,000 c
G7L-2A-TUB-CB			30 A, 277 VAC (General purpose) 30,000 c
G7L-2A-TUBJ-CB			1.5 kW, 120 VAC (Tungsten)
G7L-2A-B-CB		Screw	1.5 HP, 120 VAC
G7L-2A-BJ-CB			3 HP, 240/265/277 VAC
G7L-2A-BUB-CB			20 FLA/120 LRA, 120 VAC, 30,000 c
G7L-2A-BUBJ-CB			17 FLA/102 LRA, 277 VAC, 30,000 c
G7L-2A-P-CB		PCB	TV-10, 120 VAC
			20 A (2.4 kW), 120 VAC (Tungsten)

TÜV (File No. R9251551)

Туре	Contact form	Coil ratings	Terminal type	Contact ratings
G7L-1A-T-CB	SPST-NO	6, 12, 24, 48,	Quick-connect	25 A, 240 VAC, (cosφ = 1)
G7L-1A-TJ-CB		100, 110, 200,		25 A, 240 VAC, $(\cos \varphi = 0.4)$
G7L-1A-TUB-CB		220 VDC		
G7L-1A-TUBJ-CB				
G7L-1A-B-CB		12, 24, 50,	Screw	30 A, 240 VAC, $(\cos \varphi = 1)$
G7L-1A-BJ-CB		100/120, 200/240		25 A, 240 VAC, (cosφ = 0.4)
G7L-1A-BUB-CB		VAC		$30 \text{ A}, 240 \text{ VAC}, (\cos \varphi = 0.4)$
G7L-1A-BUBJ-CB				
G7L-1A-P-CB			PCB	20 A, 240 VAC, (cosφ = 1)
				20 A, 240 VAC, $(\cos \varphi = 0.4)$
G7L-2A-T-CB	DPST-NO		Quick-connect	25 A, 240 VAC, (cosφ = 1)
G7L-2A-TJ-CB				25 A, 240 VAC, $(\cos \varphi = 0.4)$
G7L-2A-TUB-CB				
G7L-2A-TUBJ-CB				
G7L-2A-B-CB			Screw	25 A, 240 VAC, (cosφ = 1)
G7L-2A-BJ-CB				25 A, 240 VAC, $(\cos \varphi = 0.4)$
G7L-2A-BUB-CB				
G7L-2A-BUBJ-CB				
G7L-2A-P-CB			PCB	20 A, 240 VAC, (cosφ = 1)
				20 A, 240 VAC, (cosφ = 0.4)

VDE recognized type (Licence no. 1530 UG)

Note: 1. Please consult OMRON for details of VDE approvals.

2. The G7L relay conforms to the following standards: Electrical safety: DIN IEC 255 Teil 1-00/DIN VDE 0435 Teil 201/05. 83

DIN VDE 0435 Teil 201 A1/05. 90

DIN IEC 255 Teil 0-20/DIN VDE 0435 Teil 120/10. 81

DIN EN 60 950/VDE 0805/11. 93

EMC: prEN 50082-2, EN 55022

- 3. The rated values approved by each of the safety standards (e.g., UL and CSA) may be different from the performance characteristics individually defined in this catalog.
- 4. In the interest of product improvement, specifications are subject to change.

11

OMRON - G7L

Precautions

HANDLING

- To preserve initial performance, do not drop or otherwise subject the power relay to shock.
- The case is not designed to be removed during normal handling and operation. Doing so may affect performance.
- Use the power relay in a dry environment free from excessive dust, SO2, H2S, or organic gas.
- Do not allow a voltage greater than the maximum allowable coil voltage to be applied continuously.
- Do not use the power relay outside of specified voltages and currents.
- · Do not allow the ambient operating temperature to exceed the specified limit.

■ INSTALLATION

- · Although there are not specific limits on the installation site, it should be as dry and dust-free as possible.
- PCB terminal-equipped relays weigh approximately 100 g. Be sure that the PCB is strong enough to support them. We recommend dual-side through-hole PCBs to reduce solder cracking from heat stress.
- · Quick-connect terminals can be connected to fast on receptacle #250 and positive-lock connectors.
- · Allow suitable slack on leads when wiring, and do not subject the terminals to excessive force.


■ CLEANING PCB TERMINALS

· PCB terminals have semi-sealed construction which prevents flux from entering the relay base. It is recommended that the user should apply a tape seal over the vent hole prior to wave soldering or cleaning. The tape should then be removed after processing.

OPERATING COIL

As a rule, either a battery or a DC power supply with a maximum 5% ripple is used for the operating voltage for DC relays. Before using a rectified AC supply, confirm that the ripple is not greater than 5%. Ripple greater than this can lead to variations in the operating and reset voltages.

As excessive ripple can generate beats, the insertion of a smoothing capacitor is recommended as shown below.



- When driving a transistor, check the leakage current and connect a bleeder resistor if necessary.
- Momentary voltage drops on coil input voltage should not exceed one second duration after contact mating with no shock or vibration.

■ APPLICATIONS

- · Compressors for package air conditioners and heater switching controllers
- · Switching controllers for power tools or motors
- · Power controllers for water heaters
- · Power controllers for dryers

- Lamp control, motor drivers, and power supply switching in copy machines, facsimiles, and other OA equipment
- · Lighting controllers
- · Power controllers for packers or food processing equipment
- · Magnetron control in microwaves

MRON

OMRON ELECTRONICS. INC.

One East Commerce Drive Schaumburg, IL 60173

1-800-55-OMRON

OMRON CANADA. INC.

885 Milner Avenue Scarborough, Ontario M1B 5V8

416-286-6465