General purpose accelerometer



787A-10


SPECIFICATIONS


Sensitivity, ±5%, 25°C	10 mV/g
Acceleration range, VDC > 25 V	500 g peak
Amplitude nonlinearity	1%
Frequency response: ±10% ±3 dB	1 - 5,000 Hz 0.5 - 10,000 Hz
Resonance frequency	22 kHz
Transverse sensitivity, max	5% of axial
Temperature response: -50°C +120°C	–20% +10%
Power requirement: Voltage source Current regulating diode	18 - 30 VDC 2 - 10 mA
Electrical noise, equiv. g: Broadband 2.5 Hz to 25 kHz Spectral 10 Hz 100 Hz 1,000 Hz	4,000 μg 25 μg/√Hz 23 μg/√Hz 23 μg/√Hz
Output impedance, max	100 Ω
Bias output voltage	12 VDC
Grounding	case isolated, internally shielded
Temperature range	–50° to +120°C
Vibration limit	500 g peak
Shock limit	5,000 g peak
Electromagnetic sensitivity, equiv. g, ma	x 70 μg/gauss
Sealing	hermetic
Base strain sensitivity, max	0.002 g/µstrain
Sensing element design	PZT, shear
Weight	145 grams
Case material	316L stainless steel
Mounting	1/4-28 captive hex head screw, 0.046" diameter safety wire hole
Mating connector	2 pin, MIL-C-5015 style
Recommended cabling	twisted, shielded pair

Accessories supplied: 1/4-28 captive hex head screw; calibration data (level 2)

Key features

- High amplitude range
- Side exit
- · Manufactured in ISO 9001 facility







Connections	
Function	Connector pin
power/signal	Α
common	В
ground	shell

Note: Due to continuous process improvement, specifications are subject to change without notice. This document is cleared for public release.

CE