

Evaluating the ADL8100 GaAs, pHEMT, MMIC, Low Noise Amplifier, 0.01 GHz to 20 GHz

FEATURES

- 2-layer Rogers 4350B evaluation boards with heat spreaders
- ▶ End launch, 2.9 mm RF connectors
- Through calibration path (depopulated connectors)

EVALUATION KIT CONTENTS

- ADL8100ACPZN-EVALZ evaluation board that requires external bias tee
- ADL8100ACPZN-EVAL1Z evaluation board that has an on-board bias tee

EQUIPMENT NEEDED

- ▶ RF signal generator
- ▶ RF spectrum analyzer
- ▶ RF network analyzer
- ▶ 5 V, 500 mA power supply
- ▶ External DC block for ADL8100ACPZN-EVALZ
- Marki Microwave BT2-0040 wideband bias tee for ADL8100ACPZN-EVALZ

GENERAL DESCRIPTION

The ADL8100ACPZN-EVALZ and ADL8100ACPZN-EVAL1Z are 2-layer printed circuit boards (PCB) fabricated from 10 mil thick, Rogers 4350B, copper clad, mounted to an aluminum heat spreader. The heat spreader assists in providing thermal relief to the device as well as mechanical support to the PCB. Mounting holes on the heat spreader allow attachment to larger heat sinks for improved thermal management.

The RFIN and RFOUT ports on the ADL8100ACPZN-EVALZ and ADL8100ACPZN-EVAL1Z are populated with 2.9 mm, female coaxial connectors, and the respective RF traces have a 50 Ω characteristic impedance. The ADL8100ACPZN-EVAL2 and ADL8100ACPZN-EVAL1Z are populated with components suitable for use over the entire –40°C to +85°C operating temperature range.

To calibrate out board trace losses, a through calibration path, THRUCAL, is provided between the THRUCAL connectors (J1 and J2). THRUCAL must be populated with RF connectors to use the through calibration path.

The power voltages and ground path are accessed through surface-mounted technology (SMT) test points.

An external wideband bias tee must be connected to RFOUT of the ADL8100ACPZN-EVALZ to provide bias current and AC coupling on RFOUT. The BT2-0040 from Marki Microwave is recommended. The ADL8100ACPZN-EVAL1Z has an on-board SMT bias tee.

For full details on the ADL8100, see the ADL8100 data sheet, which must be consulted in conjunction with this user guide when using the ADL8100ACPZN-EVALZ and ADL8100ACPZN-EVAL1Z.

TABLE OF CONTENTS

Features	1
Evaluation Kit Contents	1
Equipment Needed	1
General Description	1
Evaluation Board Photographs	3
Evaluation Board Hardware	4
Providing DC Bias to ADL8100ACPZN-	
EVALZ Using a Connectorized Bias Tee	4
Recommended Bias Sequencing for	
ADL8100ACPZN-EVALZ and	
ADL8100ACPZN-EVAL1Z	4

REVISION HISTORY

7/2023—Revision 0: Initial Version

Performance Comparison of	
ADL8100ACPZN-EVALZ and	
ADL8100ACPZN-EVAL1Z	4
Through Calibration Path	4
Evaluation Board Schematics and Artwork	6
Ordering Information	8
Bill of Materials	8

EVALUATION BOARD PHOTOGRAPHS





Figure 3. ADL8100ACPZN-EVALZ and ADL8100ACPZN-EVAL1Z Bottom Side

Figure 1. ADL8100ACPZN-EVALZ Component Side (Requires External Bias Tee)




Figure 2. ADL8100ACPZN-EVAL1Z Component Side (Includes On Board Bias Tee)

EVALUATION BOARD HARDWARE

PROVIDING DC BIAS TO ADL8100ACPZN-EVALZ USING A CONNECTORIZED BIAS TEE

A 5 V, 500 mA supply is required to provide the bias to the ADL8100ACPZN when using the ADL8100ACZPN-EVALZ. Connect the 5 V supply through an external bias tee, such as the Marki Microwave BT2-0040, to the RFOUT port (see Figure 4). Connect the same 5 V supply to the VBIAS SMT test point. A connectorized DC blocking capacitor must be connected to the RFIN port because there no AC coupling capacitors on the RF input trace on the ADL8100ACPZN-EVALZ. The R1 value (default value is 560 Ω) sets the total current (I_{DQ}) to 220 mA.




Figure 4. ADL8100ACPZN-EVALZ Operation Using a Connectorized Bias Tee

RECOMMENDED BIAS SEQUENCING FOR ADL8100ACPZN-EVALZ AND ADL8100ACPZN-EVAL1Z

To avoid damaging the device, pay careful attention to the sequencing of the RF input, the bias voltage, and the drain bias voltage. The following power-up sequence is recommended:

- 1. Connect GND.
- 2. Increase the voltage on the VBIAS SMT test point and the external bias tee to 5 V.
- 3. Apply the RF signal.

The following power-down sequence is recommended:

- **1.** Turn off the RF signal.
- 2. Reduce the voltage on the VBIAS SMT test point and the external bias tee to 0 V.

PERFORMANCE COMPARISON OF ADL8100ACPZN-EVALZ AND ADL8100ACPZN-EVAL1Z

Figure 5 and Figure 6 show the return loss of the ADL8100ACPZN-EVALZ and the ADL8100ACPZN-EVAL1Z. The external bias tee of the ADL8100ACPZN-EVALZ has been de-embedded for the performance measurement. The SMT bias tee components on the ADL8100ACPZN-EVAL1Z slightly reduce gain across frequency, as shown in Figure 6.




Figure 5. ADL8100ACPZN-EVALZ Performance (Requires External Bias Tee)




Figure 6. ADL8100ACPZN-EVAL1Z Performance (SMT Bias Tee)

THROUGH CALIBRATION PATH

The ADL8100ACPZN-EVALZ and ADL8100ACPZN-EVAL1Z include a calibration path (see the evaluation board schematic in Figure 9 and Figure 11). THRUCAL (J1 and J2) must be populated with RF connectors to use the through calibration path. In the case of the ADL8100ACPZN-EVAL1Z, the through calibration path includes two AC coupling capacitors (populated) to mimic the AC coupling capacitors in the main signal path. Figure 7 and Figure 8 show the insertion loss, input return loss, and output return loss of the through calibration path for the ADL8100ACPZN-EVALZ and ADL8100ACPZN-EVAL1Z, respectively. Table 1 and Table 2 list the insertion loss of the through calibration paths for the ADL8100ACPZN-EVALZ and ADL8100ACPZN-EVAL1Z, respectively.

EVALUATION BOARD HARDWARE




Figure 7. Insertion Loss and Return Loss (Input and Output) of the Through Calibration Path (ADL8100ACPZN-EVALZ)

Table 1. Insertion Loss of the Through Calibration Path (ADL8100ACPZN-
EVALZ)

Frequency (GHz)	Insertion Loss (dB)
0.01	-0.001
0.20	-0.01
0.5	-0.02
0.70	-0.03
1	-0.05
3	-0.12
5	-0.15
7	-0.17
9	-0.23
11	-0.25
13	-0.37
15	-0.41
17	-0.48
19	-0.59
21	-0.73
23	-0.95
25	-0.94




Figure 8. Insertion Loss and Return Loss (Input and Output) of the Through Calibration Path (ADL8100ACPZN-EVAL1Z)

Table 2. Insertion Loss of the Through Calibration Path (ADL8100ACPZN-
EVAL1Z)

Frequency (GHz)	Insertion Loss (dB)
0.01	-0.02
0.20	-0.02
0.5	-0.03
0.70	-0.06
1	-0.08
3	-0.25
5	-0.49
7	-0.59
9	-0.76
11	-1.20
13	-1.19
15	-1.92
17	-2.28
19	-2.62
21	-2.09
23	-2.79
25	-3.54

EVALUATION BOARD SCHEMATICS AND ARTWORK




Figure 10. ADL8100ACPZN-EVALZ Assembly Drawing (J1 and J2 Not Installed)




Figure 11. ADL8100ACPZN-EVAL1Z Schematic

010

EVALUATION BOARD SCHEMATICS AND ARTWORK




Figure 12. ADL8100ACPZN-EVAL1Z Assembly Drawing (J1 and J2 Not Installed)

ORDERING INFORMATION

BILL OF MATERIALS

Table 3. ADL8100ACPZN-EVALZ Bill of Materials

Reference Designator	Description	Manufacturer	Manufacturer Number
C1	1000 pF capacitor, 0402, do not install (DNI)	MURATA	GRM1555C1H102JA01
R1	560 Ω resistor, surface-mounted device (SMD), 0402	PANASONIC	ERJ-2RKF5600X
/BIAS, GND	Connectors, SMT test points	Keystone Electronics	5016
RFIN, RFOUT	Connectors, K jack edge	SRI Connector Gage Co.	25-146-1000-92
J1, J2	Connectors, K jack edge, DNI	SRI Connector Gage Co.	25-146-1000-92
U1	Wideband, low noise amplifier, single positive supply, 0.01 GHz to 20 GHz	Analog Devices, Inc.	ADL8100ACPZN

Table 4. ADL8100ACPZN-EVAL1Z Bill of Materials

Reference Designator	Description	Manufacturer	Manufacturer Number
C6, C10	Ceramic capacitor, 100 pF, 50 V, 5% C0G, 0402	Yageo	CC0402JRNPO9BN101
C2, C5, C8, C9	Ceramic capacitor, 0.1 $\mu\text{F},$ 16 V, 20% to +25% , 0402	AMERICAN TECHNICAL CERAMICS	ATC560L104YTT
C7	Ceramic capacitor, 0.01 µF, 25 V, 10% X8R, 0402	TDK	C1005X8R1E103K
VBIAS, GND, VDD	Connectors, SMT test points	Keystone Electronics	5016
L1	Inductor fixed unshielded, 1 μ H, 0.5 A, 0.69 Ω 0805	Coilcraft	0805LS-102XJLC
L2, L3	Inductor chip, 56 NH, 5%, 0.061 Ω, DCR, 1.2 A	Coilcraft	0402DF-560XJR
R2	Resistor SMD, 348 Ω, 1%, 1/10 W, 0402	Panasonic	ERJ2RKF3480X
R3	Resistor SMD, 560 Ω 1%, 1/10 W, 0402	Panasonic	ERJ-2RKF5600X
R4	Resistor SMD, 0 Ω jumper, 1/10 W, 0402, DNI	Panasonic	ERJ-2GE0R00X
RFIN, RFOUT	Connectors, K jack edge	SRI Connector Gage Co.	25-146-1000-92
J1, J2	Connectors, K jack edge, DNI	SRI Connector Gage Co.	25-146-1000-92
U1	Wideband, low noise amplifier, single positive supply, 0.01 GHz to 20 GHz	Analog Devices, Inc.	ADL8100ACZPN



ESD Caution

ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

Legal Terms and Conditions

By using the evaluation board discussed herein (together with any tools, components documentation or support materials, the "Evaluation Board"), you are agreeing to be bound by the terms and conditions set forth below ("Agreement") unless you have purchased the Evaluation Board, in which case the Analog Devices Standard Terms and Conditions of Sale shall govern. Do not use the Evaluation Board until you have read and agreed to the Agreement. Your use of the Evaluation Board shall signify your acceptance of the Agreement. This Agreement is made by and between you ("Customer") and Analog Devices, Inc. ("ADI"), with its principal place of business at Subject to the terms and conditions of the Agreement, ADI hereby grants to Customer a free, limited, personal, temporary, non-exclusive, non-sublicensable, non-transferable license to use the Evaluation Board FOR EVALUATION PURPOSES ONLY. Customer understands and agrees that the Evaluation Board is provided for the sole and exclusive purpose referenced above, and agrees not to use the Evaluation Board for any other purpose. Furthermore, the license granted is expressly made subject to the following additional limitations: Customer shall not (i) rent, lease, display, sell, transfer, assign, sublicense, or distribute the Evaluation Board; and (ii) permit any Third Party to access the Evaluation Board. As used herein, the term "Third Party" includes any entity other than ADI, Customer, their employees, affiliates and in-house consultants. The Evaluation Board is NOT sold to Customer; all rights not expressly granted herein, including ownership of the Evaluation Board, are reserved by ADI. CONFIDENTIALITY. This Agreement and the Evaluation Board shall all be considered the confidential and proprietary information of ADI. Customer may not disclose or transfer any portion of the Evaluation Board to any other party for any reason. Upon discontinuation of use of the Evaluation Board or termination of this Agreement, Customer agrees to promptly return the Evaluation Board to ADI. ADDITIONAL RESTRICTIONS. Customer may not disassemble, decompile or reverse engineer chips on the Evaluation Board. Customer shall inform ADI of any occurred damages or any modifications or alterations it makes to the Evaluation Board, including but not limited to soldering or any other activity that affects the material content of the Evaluation Board. Modifications to the Evaluation Board must comply with applicable law, including but not limited to the RoHS Directive. TERMINATION. ADI may terminate this Agreement at any time upon giving written notice to Customer. Customer agrees to return to ADI the Evaluation Board at that time. LIMITATION OF LIABILITY. THE EVALUATION BOARD PROVIDED HEREUNDER IS PROVIDED "AS IS" AND ADI MAKES NO WARRANTIES OR REPRESENTATIONS OF ANY KIND WITH RESPECT TO IT. ADI SPECIFICALLY DISCLAIMS ANY REPRESENTATIONS, ENDORSEMENTS, GUARANTEES, OR WARRANTIES, EXPRESS OR IMPLIED, RELATED TO THE EVALUATION BOARD INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTY OF MERCHANTABILITY, TITLE, FITNESS FOR A PARTICULAR PURPOSE OR NONINFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS. IN NO EVENT WILL ADI AND ITS LICENSORS BE LIABLE FOR ANY INCIDENTAL, SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES RESULTING FROM CUSTOMER'S POSSESSION OR USE OF THE EVALUATION BOARD, INCLUDING BUT NOT LIMITED TO LOST PROFITS, DELAY COSTS, LABOR COSTS OR LOSS OF GOODWILL. ADI'S TOTAL LIABILITY FROM ANY AND ALL CAUSES SHALL BE LIMITED TO THE AMOUNT OF ONE HUNDRED US DOLLARS (\$100.00). EXPORT. Customer agrees that it will not directly or indirectly export the Evaluation Board to another country, and that it will comply with all applicable United States federal laws and regulations relating to exports. GOVERNING LAW. This Agreement shall be governed by and construed in accordance with the substantive laws of the Commonwealth of Massachusetts (excluding conflict of law rules). Any legal action regarding this Agreement will be heard in the state or federal courts having jurisdiction in Suffolk County, Massachusetts, and Customer hereby submits to the personal jurisdiction and venue of such courts. The United Nations Convention on Contracts for the International Sale of Goods shall not apply to this Agreement and is expressly disclaimed.



©2023 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners. One Analog Way, Wilmington, MA 01887-2356, U.S.A.