

GSE10-P4221 G10

**SMALL PHOTOELECTRIC SENSORS** 





## Ordering information

Туре	Part no.
GSE10-P4221	1065906

Other models and accessories → www.sick.com/G10

Illustration may differ



#### Detailed technical data

#### **Features**

Functional principle	Through-beam photoelectric sensor
Dimensions (W x H x D)	20 mm x 50 mm x 39 mm
Housing design (light emission)	Rectangular
Sensing range max.	0 m 40 m
Sensing range	0 m 35 m
Type of light	Infrared light
Light source	LED <sup>1)</sup>
Light spot size (distance)	Ø 433 mm (15 m)
Wave length	850 nm
Adjustment	Potentiometer, 270°

 $<sup>^{1)}</sup>$  Average service life: 100,000 h at  $T_{IJ}$  = +25 °C.

#### Mechanics/electronics

Supply voltage	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Power consumption, sender	≤ 15 mA
Power consumption, receiver	≤ 20 mA
Switching output	PNP
Switching mode	Light/dark switching

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

 $<sup>^{2)}\,\</sup>mbox{May}$  not exceed or fall below  $\mbox{U}_{\mbox{\scriptsize V}}$  tolerances.

 $<sup>^{</sup>m 3)}$  Signal transit time with resistive load.

<sup>4)</sup> With light/dark ratio 1:1.

 $<sup>^{5)}</sup>$  A =  $V_S$  connections reverse-polarity protected.

 $<sup>^{6)}</sup>$  B = inputs and output reverse-polarity protected.

 $<sup>^{7)}</sup>$  C = interference suppression.

 $<sup>^{8)}</sup>$  D = outputs overcurrent and short-circuit protected.

 $<sup>^{9)}</sup>$  Complies with the UL325 standard when used with sturdy protection hood (e.g. BEF-G10WSG, 2071960).

Switching mode selector	Selectable via light/dark selector
Output current I <sub>max.</sub>	≤ 100 mA
Response time	≤ 500 µs <sup>3)</sup>
Switching frequency	1,000 Hz <sup>4)</sup>
Connection type	Male connector M12, 4-pin
Circuit protection	A <sup>5)</sup> B <sup>6)</sup> C <sup>7)</sup> D <sup>8)</sup>
Protection class	III
Weight	70 g
Housing material	Plastic, ABS/PMMA
Enclosure rating	IP67
Electromagnetic compatibility (EMC)	EN 60947-5-2
Test input	Sender OFF at "Test" 0 V
Ambient operating temperature	-30 °C +60 °C
Ambient temperature, storage	-40 °C +70 °C
UL File No.	NRKH.E348498 & NRKH7.E348498
More standards	UL325 <sup>9)</sup>

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

#### Classifications

eCl@ss 5.0	27270901
eCl@ss 5.1.4	27270901
eCl@ss 6.0	27270901
eCl@ss 6.2	27270901
eCl@ss 7.0	27270901
eCl@ss 8.0	27270901
eCl@ss 8.1	27270901
eCl@ss 9.0	27270901
eCl@ss 10.0	27270901
eCl@ss 11.0	27270901
eCl@ss 12.0	27270901
ETIM 5.0	EC002716
ETIM 6.0	EC002716
ETIM 7.0	EC002716

 $<sup>^{2)}</sup>$  May not exceed or fall below  $\mathrm{U}_{\mathrm{V}}$  tolerances.

<sup>3)</sup> Signal transit time with resistive load.

<sup>&</sup>lt;sup>4)</sup> With light/dark ratio 1:1.

 $<sup>^{5)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

 $<sup>^{6)}</sup>$  B = inputs and output reverse-polarity protected.

<sup>7)</sup> C = interference suppression.

<sup>8)</sup> D = outputs overcurrent and short-circuit protected.

<sup>9)</sup> Complies with the UL325 standard when used with sturdy protection hood (e.g. BEF-G10WSG, 2071960).

ETIM 8.0	EC002716
UNSPSC 16.0901	39121528


## Connection diagram

Cd-073

#### Characteristic curve


Operating reserve

Operating reserve




## Light spot size

#### Light spot size




## Sensing range diagram

#### Scanning range




## Adjustments



- 6 Adjustment of sensing range
- ① Light/dark selector
- 8 Sender
- 9 Receiver

#### Dimensional drawing (Dimensions in mm (inch))

GSE10, DC, connector



- ① Center of optical axis, sender
- ② Center of optical axis, receiver
- 3 Mounting hole, Ø 4.2 mm
- 4 LED indicator yellow: Status of received light beam
- ⑤ LED indicator green: power on

#### Recommended accessories

Other models and accessories → www.sick.com/G10

	Brief description	Туре	Part no.	
Universal bar clamp systems				
	Q-Lock, bar clamp system for G10 and reflector P250, Die-cast zinc, steel, zinc coated	BEF-KHSQ12R01	2071260	
Plug connectors and cables				
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YF2A14- 050VB3XLEAX	2096235	
	Head A: male connector, M12, 4-pin, straight Cable: unshielded	STE-1204-G	6009932	

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

