



Digital input module, 16 digital inputs 24 V DC each, pulse-switching, 5.0 ms



Part no. **XN-322-16DI-PD**  
**183173**

<b>General specifications</b>	
Product name	Eaton XN-322 Input module
Part no.	XN-322-16DI-PD
EAN	4015081781065
Product Length/Depth	104.2 millimetre
Product height	16.8 millimetre
Product width	80.3 millimetre
Product weight	0.055 kilogram
Certifications	IEC/EN 61000-6-2 CULus IEC/EN 61131-2 UL File No.: E135462 CE IEC/EN 61000-6-4
Product Tradename	XN-322
Product Type	Input module
Product Sub Type	None
Catalog Notes	The max. heat dissipation is specified as the maximum power produced inside the device's housing.
<b>Features &amp; Functions</b>	
Electric connection type	Plug-in connection
Features	Fieldbus connection over separate bus coupler possible
<b>General information</b>	
Current consumption	None mA (typ.), for +24 V, Power supply - Input 36 mA (typ.), for +5 V power supply (internal), Power supply - Input
Degree of protection	IP20
Mounting method	Rail mounting possible
Number of channels	16
Overvoltage category	III
Pollution degree	3
Product category	XN-322 digital input module
Type	Digital I/O module with sixteen 24 V DC / 3.7 mA (EN61131-2 type 1) inputs with a 0.5 ms input filter. XN300 I/O slice module
Used with	XN-312-... XN300
Voltage type	DC
<b>Ambient conditions, mechanical</b>	
Height of fall (IEC/EN 60068-2-32) - max	1 m
Mounting position	Horizontal
Shock resistance	15 g, Mechanical, Half-sinusoidal shock 11 ms, 18 Impacts
Vibration resistance	5 - 8.4 / 8.4 -150 Hz, 3,5 mm / 1 g
<b>Climatic environmental conditions</b>	
Air pressure	795 - 1080 hPa (operation)
Ambient operating temperature - min	0 °C
Ambient operating temperature - max	60 °C
Ambient storage temperature - min	-20 °C
Ambient storage temperature - max	85 °C
Climatic proofing	Dry heat to IEC 60068-2-2 Damp heat, constant, to IEC 60068-2-3
Environmental conditions	Condensation: prevent with appropriate measures
Relative humidity	0 - 95 % (non-condensing)

<b>Electro magnetic compatibility</b>		
Air discharge		8 kV
Burst impulse		2 kV, Supply cable 1 kV, Signal cable
Contact discharge		4 kV
Electromagnetic fields		10 V/m at 0.08 - 1.0 GHz (according to IEC EN 61000-4-3) 1 V/m at 2 - 2.7 GHz (according to IEC EN 61000-4-3) 3 V/m at 1.4 - 2 GHz (according to IEC EN 61000-4-3)
Emitted interference		47 dB (at 230 - 1000 MHz, Class A, radiated, high frequency) 40 dB (at 30 - 230 MHz, Class A, radiated, high frequency)
Radiated RFI		10 V
Surge rating		0.5/0.5 kV, Supply cable, balanced/unbalanced), EMC 1 kV, Signal cable, unbalanced, EMC
Voltage dips		Voltage dips: 10 ms/Voltage fluctuations: Yes
<b>Terminal capacities</b>		
Terminal capacity		0.2 - 1.5 mm <sup>2</sup> , solid, H07V-U 0.25 - 1.5 mm <sup>2</sup> , with ferrules without plastic collar according to DIN 46228-1 (ferrules crimped gas-tight) 0.25 - 1.5 mm <sup>2</sup> , with ferrules with plastic collar according to DIN 46228-1 (ferrules crimped gas-tight) 24 - 16 AWG 0.2 - 1.5 mm <sup>2</sup> , flexible without ferrule, H07V-K
Gauge pin		A1 (according to IEC/EN 60947-1)
Stripping length (main cable)		10 mm
Insulating material group		I
<b>Electrical rating</b>		
Rated operational voltage		160 V (terminations)
Supply voltage at AC, 50 Hz - min		0 V AC
Supply voltage at AC, 50 Hz - max		0 V AC
Supply voltage at DC - min		18 V DC
Supply voltage at DC - max		30 V DC
<b>Communication</b>		
Connection type		Push-in spring-cage terminal (plug-in connection), Connection design in TOP direction
Protocol		Other bus systems
<b>Input/Output</b>		
Input		Digital inputs (according to EN61131-2 Type 1)
Input current		3.7 mA (Digital inputs) ≥ 2.3 mA (Digital inputs, high level) ≤ 1.1 mA (Digital inputs, low level)
Input current at signal 1		3.7 mA
Input delay		5000 μs (falling edge) 5000 μs (rising edge)
Input voltage		14 - 30 V (Digital inputs, high level) 0 - 8 V (Digital inputs, low level) 24 V DC (Digital inputs)
Load current		Not specified by plug manufacturer
Number of inputs (digital)		16
Number of outputs (digital)		0
Output current		0 A
<b>Safety</b>		
Explosion safety category for dust		None
Explosion safety category for gas		None
Potential isolation		Between Digital inputs: no
<b>Design verification</b>		
Equipment heat dissipation, current-dependent P <sub>vid</sub>		0.2 W
Heat dissipation capacity P <sub>diss</sub>		0 W
Heat dissipation per pole, current-dependent P <sub>vid</sub>		0 W
Rated operational current for specified heat dissipation (I <sub>n</sub> )		0 A
Static heat dissipation, non-current-dependent P <sub>vs</sub>		2.436 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Meets the product standard's requirements.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## Technical data ETIM 9.0

Programmable logic controllers PLC (EG000024) / Fieldbus, decentr. periphery - digital I/O module (EC001599)		
Electric engineering, automation, process control engineering / Control, Process Control System (PCS) / Field bus, decentralized peripheral / Field bus, decentralized peripheral - digital I/O module (ecl@ss13-27-24-26-04 [BAA055019])		
Supply voltage AC 50 Hz	V	0 - 0
Supply voltage AC 60 Hz	V	0 - 0
Supply voltage DC	V	18 - 30
Voltage type (supply voltage)		DC
Number of digital inputs		16
Number of digital outputs		0
Digital inputs configurable		No
Digital outputs configurable		No
Input current at signal 1	mA	3.7
Permitted voltage at input	V	0 - 30
Type of voltage (input voltage)		DC
Type of digital output		None
Output current	A	0
Permitted voltage at output	V	0 - 0
Type of output voltage		DC
Short-circuit protection, outputs available		No
Number of HW-interfaces industrial Ethernet		0
Number of interfaces PROFINET		0
Number of HW-interfaces RS-232		0
Number of HW-interfaces RS-422		0
Number of HW-interfaces RS-485		0
Number of HW-interfaces serial TTY		0
Number of HW-interfaces parallel		0
Number of HW-interfaces wireless		0
Number of HW-interfaces USB		0
Number of HW-interfaces other		1
With optical interface		No
Supporting protocol for EtherCAT		No
Supporting protocol for TCP/IP		No

Supporting protocol for PROFIBUS			No
Supporting protocol for CAN			No
Supporting protocol for INTERBUS			No
Supporting protocol for ASI			No
Supporting protocol for KNX			No
Supporting protocol for Modbus			No
Supporting protocol for Data-Highway			No
Supporting protocol for DeviceNet			No
Supporting protocol for SUCONET			No
Supporting protocol for LON			No
Supporting protocol for PROFINET IO			No
Supporting protocol for PROFINET CBA			No
Supporting protocol for SERCOS			No
Supporting protocol for Foundation Fieldbus			No
Supporting protocol for EtherNet/IP			No
Supporting protocol for AS-Interface Safety at Work			No
Supporting protocol for DeviceNet Safety			No
Supporting protocol for INTERBUS-Safety			No
Supporting protocol for PROFIsafe			No
Supporting protocol for SafetyBUS p			No
Supporting protocol for other bus systems			Yes
Radio standard Bluetooth			No
Radio standard WLAN 802.11			No
Radio standard GPRS			No
Radio standard GSM			No
Radio standard UMTS			No
IO link master			No
System accessory			Yes
Degree of protection (IP)			IP20
Type of electric connection			Plug-in connection
Time delay at signal change		ms	4 - 6
Fieldbus connection over separate bus coupler possible			Yes
Rail mounting possible			Yes
Wall mounting/direct mounting			No
Front built-in possible			No
Rack-assembly possible			No
Suitable for safety functions			No
SIL according to IEC 61508			None
Performance level according to EN ISO 13849-1			None
Appendant operation agent (Ex ia)			No
Appendant operation agent (Ex ib)			No
Explosion safety category for gas			None
Explosion safety category for dust			None
Certified for UL hazardous location class I			No
Certified for UL hazardous location class II			No
Certified for UL hazardous location class III			No
Certified for UL hazardous location division 1			No
Certified for UL hazardous location division 2			No
Certified for UL hazardous location group A (acetylene)			No
Certified for UL hazardous location group B (hydrogen)			No
Certified for UL hazardous location group C (ethylene)			No
Certified for UL hazardous location group D (propane)			No
Certified for UL hazardous location group E (metal dusts)			No
Certified for UL hazardous location group F (carbonaceous dusts)			No
Certified for UL hazardous location group G (non-conductive dusts)			No

Width	mm	80.3
Height	mm	16.8
Depth	mm	104.2