

# VTF180-2N41112

V180-2

CYLINDRICAL PHOTOELECTRIC SENSORS





## **Ordering information**

Туре	Part no.
VTF180-2N41112	6041799

Other models and accessories → www.sick.com/V180-2

Illustration may differ



## Detailed technical data

#### **Features**

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background blanking
Dimensions (W x H x D)	18 mm x 18 mm x 62.5 mm
Housing design (light emission)	Cylindrical
Housing length	62.5 mm
Thread diameter (housing)	M18 x 1
Optical axis	Axial
Sensing range max.	1 mm 140 mm <sup>1)</sup>
Sensing range	1 mm 100 mm <sup>1)</sup>
Type of light	Visible red light
Light source	LED <sup>2)</sup>
Light spot size (distance)	Ø 8 mm (100 mm)
Wave length	645 nm
Adjustment	Potentiometer, 270° (Sensing range)
Special feature	Focused optics

 $<sup>^{1)}</sup>$  Object with 90% remission (based on standard white, DIN 5033).

#### Mechanics/electronics

Supply voltage	10 V DC 30 V DC <sup>1)</sup>
----------------	-------------------------------

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

 $<sup>^{2)}</sup>$  Average service life: 100,000 h at  $T_U$  = +25 °C.

 $<sup>^{2)}\,\</sup>text{May}$  not exceed or fall below  $\text{U}_{\text{V}}$  tolerances.

<sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Control wire open: light switching L.ON.

 $<sup>^{5)}</sup>$  Signal transit time with resistive load.

 $<sup>^{6)}</sup>$  With light/dark ratio 1:1.

<sup>7)</sup> Do not bend below 0 °C.

 $<sup>^{8)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

<sup>9)</sup> B = inputs and output reverse-polarity protected.

 $<sup>^{10)}</sup>$  D = outputs overcurrent and short-circuit protected.

Ripple	± 10 % <sup>2)</sup>
Current consumption	30 mA <sup>3)</sup>
Switching output	NPN <sup>4)</sup>
Switching mode	Light/dark switching <sup>4)</sup>
Switching mode selector	Selectable via L/D control cable
Signal voltage NPN HIGH/LOW	Approx. $V_S$ / < 1.8 V
Output current I <sub>max.</sub>	≤ 100 mA
Response time	≤ 0.5 ms <sup>5)</sup>
Switching frequency	1,000 Hz <sup>6)</sup>
Connection type	Cable, 4-wire, 2 m <sup>7)</sup>
Cable material	PVC
Conductor cross section	0.18 mm <sup>2</sup>
Cable diameter	Ø 3.8 mm
Circuit protection	A <sup>8)</sup> B <sup>9)</sup> D <sup>10)</sup>
Protection class	III
Weight	95 g
Housing material	Metal, Nickel-plated brass and PC
Optics material	Plastic, PMMA
Enclosure rating	IP67
Items supplied	Fastening nuts (2 x)
Special feature	Focused optics
Ambient operating temperature	-25 °C +55 °C
Ambient temperature, storage	-40 °C +70 °C

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

## Safety-related parameters

MTTF <sub>D</sub>	1,889 years
<b>DC</b> <sub>avg</sub>	0 %

#### Classifications

eCl@ss 5.0	27270904
eCl@ss 5.1.4	27270904
eCl@ss 6.0	27270904
eCl@ss 6.2	27270904

 $<sup>^{2)}\,\</sup>mbox{May}$  not exceed or fall below  $\mbox{U}_{\mbox{\scriptsize V}}$  tolerances.

<sup>&</sup>lt;sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Control wire open: light switching L.ON.

<sup>5)</sup> Signal transit time with resistive load.

<sup>6)</sup> With light/dark ratio 1:1.

 $<sup>^{7)}</sup>$  Do not bend below 0 °C.

 $<sup>^{8)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

<sup>9)</sup> B = inputs and output reverse-polarity protected.

<sup>10)</sup> D = outputs overcurrent and short-circuit protected.

# VTF180-2N41112 | V180-2

## CYLINDRICAL PHOTOELECTRIC SENSORS


eCl@ss 7.0	27270904
eCl@ss 8.0	27270904
eCl@ss 8.1	27270904
eCI@ss 9.0	27270904
eCl@ss 10.0	27270904
eCl@ss 11.0	27270904
eCl@ss 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

## Connection type




## Connection diagram

## Cd-089



#### Characteristic curve


VTF180-2, 140 mm, axial



- ① Sensing range on white, 90% remission
- $\ \ \, \mbox{\Large @}$  Sensing range on gray, 18 % remission


## Light spot size

VTF180-2




## Sensing range diagram

VTF180-2, 140 mm, axial



- Sensing range
- Sensing range max.
- ① Sensing range on white, 90% remission
- ② Sensing range on gray, 18 % remission


## Adjustments



- 3 Sensitivity control 270°
- ④ LED indicator orange: switching output active
- ⑤ LED indicator green

## Dimensional drawing (Dimensions in mm (inch))

VTF180-2, VTE180-2, VTB180-2, metal, axial



- ① M12 male device connector, 4-pin
- ② Connection cable 2 m
- ③ Sensitivity control 270°
- ④ LED indicator orange: switching output active
- ⑤ LED indicator green: strength indicator
- 7 Fastening nuts (2x); width across 24, metal

## Recommended accessories

Other models and accessories → www.sick.com/V180-2

	Brief description	Туре	Part no.
Plug connecto	ors and cables		
W/S	Head A: male connector, M12, 4-pin, straight Cable: unshielded	STE-1204-G	6009932

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

