multicomp PRO True RMS Digital Multimeter



Features

•

- 10 Functions
- 6000 Counts Display
- Auto & Manual Ranging
- Bandwidth : 45Hz ~ 1kHz
- Variable Frequency Device (VFD)
 - Duty Cycle : 0.1% ~ 99.9%
- Diode Test: Around 3V
- NCV: ≥ 100Vrms

- Auto Power Off : Around 15 minutes
- Continuity Buzzer Test
- Low Battery Indications: ≤ 2.5V
- Data Hold
- Relative Mode
- LCD Backlight
- Input Protection: 600Vrms
- Input Impedance for DC Voltage: 1GΩ Max.

Electrical Specifications

Parameter	Range	
DC Voltage (V)	60mV/600mV/6V/60V/600V ±(0.5% +2 digits)	
AC Voltage (V)	60mV/600mV/6V/60V/600V ±(0.8% + 3 digits)	
DC Current (A)	600μA/6000μA/60mA/600mA/6A/10A ±(0.7% +2 digits)	
AC Current (A)	600μA/6000μA/60mA/600mA/6A/10A ±(1% +3 digits)	
Resistance (Ω)	600Ω/6kΩ/60kΩ/600kΩ/6MΩ/60MΩ ±(0.8% +2 digits)	
Capacitance (F)	9.999nF/99.99nF/999.9nF/9.999µF/99.99µF/999.9µF/9.999mF/ 99.99mF ±(4%+5 digits)	
Frequency (Hz)	10Hz - 10MHz ±(0.1% +4 digits)	
Temperature (°C)	-40°C to +1000°C ±(1.0% +3 digits)	
Temperature (°F)	-40°F to +1832°F ±(1.5% +5 digits)	

General Characteristics

Safety Rating	: CAT III 600V
Power	: AA1.5 × 2
LCD Size	: 58mm × 36mm
Product Colour	: Orange & Grey
Product Weight	: 370g
Product Size	: 175mm × 81mm × 48.5mm

Accessories

1.5V AA Cells, Test Leads, Temperature Probe and Instruction Manual

Part Number Table

Description	Part Number
True RMS Digital Multimeter, Handheld	72-7780

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the gossibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk