

WTT12L-B2561

PowerProx

MULTITASK PHOTOELECTRIC SENSORS



See to the second secon

Ordering information

Туре	Part no.
WTT12L-B2561	1072611

Other models and accessories → www.sick.com/PowerProx

Illustration may differ



Detailed technical data

Features

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression, Optical time-of-flight
Dimensions (W x H x D)	20 mm x 49.6 mm x 44.2 mm
Housing design (light emission)	Rectangular
Sensing range max.	50 mm 3,800 mm ¹⁾
Sensing range	100 mm 3,800 mm ^{1) 2)}
Type of light	Visible red light
Light source	Laser 3)
Light spot size (distance)	Ø 18 mm (3,800 mm)
Wave length	658 nm
Laser class	1 (IEC 60825-1 / CDRH 21 CFR 1040.10 & 1040.11)
Adjustment	Potentiometer, 4 turns (1 x)

 $^{^{1)}}$ Object with 6 ... 90% remission (based on standard white, DIN 5033).

²⁾ Adjustable.

 $^{^{3)}}$ Average service life: 100,000 h at $\rm T_U$ = +25 °C.

Mechanics/electronics

Supply voltage U _B	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	70 mA ³⁾
Switching output	Push-pull: PNP/NPN ⁴⁾
Number of switching outputs	2 (Q, /Q) ⁴⁾
Switching mode	Light/dark switching ⁴⁾
Output current I _{max.}	≤ 100 mA
Response time	≤ 5 ms ⁵⁾
Switching frequency	100 Hz ⁶⁾
Analog output	-
Input	Sender off
Connection type	Male connector M12, 5-pin
Circuit protection	A ⁷⁾ B ⁸⁾ C ⁹⁾
Protection class	III
Weight	48 g
Housing material	Plastic, VISTAL®
Optics material	Plastic, PMMA
Enclosure rating	IP67
Ambient operating temperature	-35 °C +50 °C ¹⁰⁾
Ambient temperature, storage	-40 °C +70 °C
Warm-up time	< 15 min ¹¹⁾
Initialization time	< 300 ms
UL File No.	NRKH.E181493

 $^{^{1)}}$ Limit values. Operated in short-circuit protected network: max. 8 A.

Safety-related parameters

$MTTF_D$	133 years
DC _{avg}	0 %
T _M (mission time)	20 years

 $^{^{2)}\,\}text{May}$ not exceed or fall below U_{V} tolerances.

 $^{^{3)}}$ Without load. At V_S = 24 V.

 $^{^{4)}}$ Q, /Q = 1 switching threshold, light/dark switching (complementary).

⁵⁾ Signal transit time with resistive load.

⁶⁾ With light/dark ratio 1:1.

 $^{^{7)}}$ A = V_S connections reverse-polarity protected.

 $^{^{8)}}$ B = inputs and output reverse-polarity protected.

 $^{^{9)}}$ C = interference suppression.

 $^{^{10)}}$ As of T_a = 45 °C, a max.load current I_{max} = 50 mA is permitted.

 $^{^{11)}}$ Below T_u = -10 °C a warm-up time is necessary.


WTT12L-B2561 | PowerProx

MULTITASK PHOTOELECTRIC SENSORS

Classifications

eCl@ss 5.0	27270904
eCl@ss 5.1.4	27270904
eCl@ss 6.0	27270904
eCl@ss 6.2	27270904
eCl@ss 7.0	27270904
eCl@ss 8.0	27270904
eCl@ss 8.1	27270904
eCl@ss 9.0	27270904
eCl@ss 10.0	27270904
eCl@ss 11.0	27270904
eCl@ss 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528


Dimensional drawing (Dimensions in mm (inch))




- ① Optical axis, sender
- ② Optical axis, receiver
- 3 LED indicator yellow: Status of received light beam
- 4 LED indicator green: power on
- (5) LED indicator yellow: Status of received light beam
- 6 Mounting hole, Ø 4.2 mm
- ⑦ Connection
- ® Potentiometer
- Single teach-in button

Connection diagram

Cd-282




Characteristic curve



- ① Sensing range on black, 6% remission factor
- ② Sensing range on white, 90% remission factor


Light spot size






- ① Light spot horizontal
- ② Light spot vertical

Repeatability





- $\textcircled{\scriptsize 1}$ 6 % remission, on black
- 2 90 % remission, on white

Recommended accessories

Other models and accessories → www.sick.com/PowerProx

	Brief description	Туре	Part no.	
Mounting bra				
	Mounting brackets	BEF-WTT12L	2078538	
Plug connectors and cables				
	Head A: female connector, M12, 5-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YF2A15- 050VB5XLEAX	2096240	
	Head A: male connector, M12, 5-pin, straight Cable: unshielded For field bus technology	STE-1205-G	6022083	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

