

- Ratings up to 20A, 277V ac
- High in-rush (ON-OFF types)
- Positive switch action
- Distinctive styling
- Illuminated & nonilluminated
- Double pole
- Panel cut out: 30.1 x 22.2mm



European 16(4)A 250Vac T125, 10A 400Vac T125

UL CSA 20A 277Vac, 250Vac 1¹/₂hp, 125Vac 1hp UL 100°C, file E45221, CSA file LR10990


Inrush 150A* to EN61058-1 8(8)A 250Vac T125 5E4 on 6050 only

* applies to non-momentary types



RoHS compliant

3mm contact gap with Positive Break switching. # Call sales for IP details on Twin units. Technical data on pages 4 & 5 (switches), 6 (indicators). Patent app.



BR 2 1197W

ORDER FORMAT

TERMINAL CODE FUNCTION CODE ROCKER CODE BODY CODE

C 6053 A L

BODY ROCKER COLOR

LAMP VOLTAGE IF REQUIRED LEGEND & OPTIONS

					_		302011 0020	
	TERMINAL	FUNCTION						ROCKER
C	Approvals & ratings vary with function ON OFF Switches - ON when pressed over terminals 3 & 6 9.7							A Softline Matt
	6.3 x 0.8	6050	ON - OFF		6060	ON - ON		
		6051	ON - OFF (momentary ON)	† :::	6061	ON - ON (momentary 1 side		
	4.8 x 0.8	6052	ON - OFF (momentary OFF)	+ 	6062 In house tes	2 Circuit ON - ON		A Softline Matt
Н		6053	ON - OFF Lit		6066	ON - ON (Single po	ole) •••••	P Lit Window Matt
		6054	ON - OFF (momentary ON) Lit	t: 1	6067	ON - ON Lit		
		6055	ON - OFF (Single po (momentary ON) Lit	ole)	6068	ON - ON 1pole ON - OFF Lit 1pole		
		6056	ON - OFF (Single po Isolated light	ole) • • •	6090	ON - OFF 1pole ON - OFF Lit 1pole		
S		6057	ON - OFF Isolated light		6091	ON - OFF (momentary ON) Lit	1:1:0	
		6058	ON - OFF (Single po Lit	ole)	6092	ON - OFF 1 pole ON - ON 1 pole Lit		
with	Screw & Clamp N/A for assemblies a 3 terminals in either pole	6059	ON - OFF (Single po (momentary ON) Isolated light	ole)		Circuits are Double unless described oth		Lit Window



Integral Splash Resistance

Current carrying parts are protected from moisture. Droplets which may enter the switch are channelled out through ports in the switch body

For IP65 see options below







. C6053AL



C6053PL



6000/6000AL



6003/60003PL




6003P/6030AL

BODY L Double pole Panel cut-out * Bezel R2.0|< 25.0 22.1/22.2

L Twin units Contact sales for information on splash resistance and IP ratings

Panel cut-out *

Bezel



Cut-outs must be punched in the direction of insertion

OPTIONS

Finish Matt is standard

Color Call factory for custom colors A full range is available for large orders

Legend printing Select from the examples or call factory for custom legends

Lamp voltage Call factory for details

Protective cover (designed to IP65 #) The 6000 series is a water thru design. For a higher level of sealing, a snap on cover is available (add suffix G72). This reduces panel thickness by 1mm.



Panel sealing washer W42 is available but reduces panel thickness by a further 1.00mm. Covers are not suitable for momentary types.


IP Ratings Call the factory for details

Jumper Terminal P1067 connects the poles of a double pole switch or twin unit

Mounting orientation may affect IP rating

For all options call the factory

DIMENSIONS (mm)



Panel thickness

0.75 to 3.0mm

* For cut-out details on momentary switches call sales

Terminal spacing - Poles 10.5 between centres

Examples of our range of legend printing B-Black, W-White, R-Red () is legend color





1197(W)