

## ENDURO SCREWDRIVERS


## ENDURO® SCREWDRIVERS FOR SLOTTED HEADS

## ▼ ACZ FOR SLOTTED HEADS

- Silicon carbon steel.
- Black tipped hardened blades.
- Optimum resilience and performance.
- ● 2 to 3 round blades, mono-material handles.
- ● from 3.5 forged hexagonal blades.

Ref	e x A mm	T mm	Ø1 x L1 mm	Ø2 x L2 mm	L mm	ΔΔ g
ACZ.2X75	0,4 x 2,0	0,2	2,0 x 75	16 x 96	171	20
ACZ.2,5X75	0,4 x 2,5	0,2	2,5 x 75	16 x 96	171	22
ACZ.3X75	0,5 x 3,0	0,3	3,0 x 75	16 x 96	171	25
ACZ.3,5X75	0,6 x 3,5	0,4	3,5 x 75	25 x 100	175	45
ACZ.3,5X100	0,6 x 3,5	0,4	3,5 x 100	25 x 100	200	50
ACZ.4X100	0,8 x 4,0	0,5	4,0 x 100	25 x 100	200	60
ACZ.4X150	0,8 x 4,0	0,5	4,0 x 150	25 x 100	250	70
ACZ.5,5X100	1,0 x 5,5	0,6	5,0 x 100	31 x 108	208	85
ACZ.5,5X150	1,0 x 5,5	0,6	5,0 x 150	31 x 108	258	100
ACZ.6,5X150	1,2 x 6,5	0,7	6,0 x 150	37 x 120	270	150
ACZ.8X150	1,2 x 8,0	0,7	7,0 x 150	37 x 120	270	220
ACZ.8X200	1,2 x 8,0	0,7	7,0 x 200	37 x 120	320	220
ACZ.10X200	1,6 x 10,0	1,0	9,0 x 200	39 x 125	325	255
ACZ.12X250	2,0 x 12,0	1,2	10,0 x 250	39 x 125	375	280

+ Ergonomics




## ▼ ACZH POWER SERIES FOR SLOTTED HEADS

- Forged hexagonal blades with shoulder to take a wrench.
- Silicon carbon steel.
- Black tipped hardened blades.
- Optimum resilience and performance.

Ref	e x A mm	T mm	Ø1 x L1 mm	Ø1 x L2 mm	Ø2 mm	L mm	ΔΔ g
ACZH.5,5X125	1,0 x 5,5	0,6	5 x 125	31 x 108	8	233	90
ACZH.6,5X150	1,2 x 6,5	0,7	6 x 150	37 x 120	10	270	135
ACZH.8X175	1,5 x 8,0	0,7	7 x 175	37 x 120	11	295	160
ACZH.8X175	1,6 x 8,0	0,7	8 x 175	39 x 150	12	300	220
ACZH.10X175	1,6 x 10	0,7	9 x 175	39 x 125	14	300	320
ACZH.12X200	2,0 x 12	1,2	10 x 200	39 x 125	14	325	330

+ Ergonomics



## ENDURO® SCREWDRIVERS FOR SLOTTED HEADS

## ▼ ACZP FOR PHILLIPS® HEADS

- Hexagonal blades except size 0 x 75.
- Silicon carbon steel.
- Black tipped hardened blades.
- Optimum resilience and performance.

Ref	Phillips® no.	Ø1 x L1 mm	Ø2, 1 x L1 mm	Ø2 x L2 mm	L mm	ΔΔ g
ACZP.0X75	PH 0	4 x 75		25 x 100	175	45
ACZP.1X100	PH 1		5 x 100	31 x 108	208	80
ACZP.2X125	PH 2		6 x 125	37 x 120	245	130
ACZP.3X150	PH 3		8 x 150	39 x 125	275	200
ACZP.4X200	PH 4		10 x 150	39 x 125	325	280

+ Ergonomics

