



Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 11

Loctite HY 4090 B LOCTITE 4090 B

SDS No. : 709973

V002.0

Revision: 06.06.2023

printing date: 18.04.2024

Replaces version from: 27.05.2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Loctite HY 4090 B LOCTITE 4090 B

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Epoxy resin

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

SDSinfo.Adhesive@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

|| Skin sensitizer

Category 1

|| H317 May cause an allergic skin reaction.

2.2. Label elements

Label elements (CLP):

|| Hazard pictogram:



Contains

Bis[(3,4-epoxycyclohexyl)methyl] adipate

|| Signal word:

Warning

Hazard statement: H317 May cause an allergic skin reaction.

Precautionary statement: P280 Wear protective gloves.
Prevention

Precautionary statement: P333+P313 If skin irritation or rash occurs: Get medical advice/attention.
Response

2.3. Other hazards

None if used properly.

Following substances are present in a concentration \geq the concentration limit for depiction in Section 3 and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in a concentration \geq the concentration limit for depiction in Section 3 that are assessed to be a PBT, vPvB or ED.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

| Hazardous components CAS-No. EC Number REACH-Reg No. | Concentration | Classification | Specific Conc. Limits, M-factors and ATEs | Add. Information |
|--|---------------|--------------------|---|------------------|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 221-518-5 01-2120769515-45 | 50- 100 % | Skin Sens. 1, H317 | | |

If no ATE values are displayed, please refer to LD/LC50 values in Section 11.

For full text of the H - statements and other abbreviations see section 16 "Other information".

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

SKIN: Rash, Urticaria.

Prolonged or repeated contact may cause eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

water, carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid contact with skin and eyes.

Wear protective equipment.

Ensure adequate ventilation.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Avoid skin and eye contact.

See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Ensure good ventilation/extraction.

Keep container tightly sealed.

Refer to Technical Data Sheet

7.3. Specific end use(s)

Epoxy resin

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

None

Occupational Exposure Limits

Valid for
Ireland

None

Predicted No-Effect Concentration (PNEC):

| Name on list | Environmental Compartment | Exposure period | Value | | | | Remarks |
|--|------------------------------|-----------------|------------|-----|-------------|--------|---------|
| | | | mg/l | ppm | mg/kg | others | |
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | aqua (freshwater) | | 0,004 mg/l | | | | |
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | aqua (marine water) | | 0 mg/l | | | | |
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | sewage treatment plant (STP) | | 32 mg/l | | | | |
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | sediment (freshwater) | | | | 0,166 mg/kg | | |
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | sediment (marine water) | | | | 0,017 mg/kg | | |
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | Soil | | | | 0,031 mg/kg | | |
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | Freshwater - intermittent | | 0,039 mg/l | | | | |
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | Marine water - intermittent | | 0,004 mg/l | | | | |

Derived No-Effect Level (DNEL):

| Name on list | Application Area | Route of Exposure | Health Effect | Exposure Time | Value | Remarks |
|--|------------------|-------------------|---------------------------------------|---------------|------------------------|---------|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | Workers | inhalation | Long term exposure - systemic effects | | 0,09 mg/m ³ | |
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | Workers | dermal | Long term exposure - systemic effects | | 0,05 mg/kg | |

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:
Ensure good ventilation/extraction.

Respiratory protection:
Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Protective eye equipment should conform to EN166.

Skin protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

| | |
|--|---|
| Delivery form | liquid |
| Colour | Off white, to, light yellow |
| Odor | characteristic |
| Physical state | liquid |
| Melting point | Currently under determination |
| Initial boiling point | Currently under determination |
| Flammability | Currently under determination |
| Explosive limits | Currently under determination |
| Flash point | > 110 °C (> 230 °F) |
| Auto-ignition temperature | Currently under determination |
| Decomposition temperature | Currently under determination |
| pH | Product is non-polar/aprotic., Not applicable |
| Viscosity (kinematic) | Currently under determination |
| Viscosity, dynamic (Cone and plate; 25 °C (77 °F); Shear gradient: 20 s ⁻¹) | 20.000 - 40.000 mPa.s LCT STM 740; cone & plate viscosity |
| Solubility (qualitative) (Solvent: Water) | Insoluble |
| Partition coefficient: n-octanol/water | Currently under determination |
| Vapour pressure (50 °C (122 °F)) | < 700 mbar |
| Density () | 1,06 g/cm ³ no method / method unknown |
| Relative vapour density: | Currently under determination |
| Particle characteristics | Currently under determination |

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

Reaction with strong acids.

Reacts with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

carbon oxides.

SECTION 11: Toxicological information**11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008****Acute oral toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

| Hazardous substances CAS-No. | Value type | Value | Species | Method |
|---|---------------|-------------|---------|--|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | LD50 | 5.000 mg/kg | rat | OECD Guideline 401 (Acute Oral Toxicity) |

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

| Hazardous substances CAS-No. | Value type | Value | Species | Method |
|---|---------------|---------------|---------|--|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | LD50 | > 2.000 mg/kg | rabbit | OECD Guideline 402 (Acute Dermal Toxicity) |

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

| Hazardous substances CAS-No. | Result | Exposure time | Species | Method |
|---|----------------|------------------|---------|--|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | not irritating | 4 h | rabbit | OECD Guideline 404 (Acute Dermal Irritation / Corrosion) |

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

| Hazardous substances CAS-No. | Result | Exposure time | Species | Method |
|---|----------------|------------------|---------|---|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | not irritating | 9 d | rabbit | OECD Guideline 405 (Acute Eye Irritation / Corrosion) |

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

| Hazardous substances CAS-No. | Result | Test type | Species | Method |
|---|-------------|------------------------------|------------|---|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | sensitising | Guinea pig maximisation test | guinea pig | OECD Guideline 406 (Skin Sensitisation) |

Germ cell mutagenicity:

No data available.

Carcinogenicity

No data available.

Reproductive toxicity:

No data available.

STOT-single exposure:

No data available.

STOT-repeated exposure:

No data available.

Aspiration hazard:

No data available.

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information

General ecological information:

Do not empty into drains / surface water / ground water.

12.1. Toxicity

Toxicity (Fish):

No data available.

Toxicity (aquatic invertebrates):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

The table below presents the data of the classified substances present in the mixture.

| Hazardous substances CAS-No. | Value type | Value | Exposure time | Species | Method |
|---|---------------|-----------------------------|---------------|---------------|--|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | EC50 | Toxicity > Water solubility | 48 h | Daphnia magna | OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test) |

Chronic toxicity (aquatic invertebrates):

No data available.

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

The table below presents the data of the classified substances present in the mixture.

| Hazardous substances CAS-No. | Value type | Value | Exposure time | Species | Method |
|---|---------------|-----------------------------|---------------|---------------------------------|---|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | EC50 | Toxicity > Water solubility | 72 h | Pseudokirchneriella subcapitata | OECD Guideline 201 (Alga, Growth Inhibition Test) |
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | EC10 | Toxicity > Water solubility | 72 h | Pseudokirchneriella subcapitata | OECD Guideline 201 (Alga, Growth Inhibition Test) |

Toxicity (microorganisms):

No data available.

12.2. Persistence and degradability

The table below presents the data of the classified substances present in the mixture.

| Hazardous substances CAS-No. | Result | Test type | Degradability | Exposure time | Method |
|---|----------------------------|-----------|---------------|---------------|---|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | not readily biodegradable. | aerobic | 62 % | 28 d | OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test) |

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

The table below presents the data of the classified substances present in the mixture.

| Hazardous substances CAS-No. | LogPow | Temperature | Method |
|---|--------|-------------|---|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | 2,98 | 20 °C | OECD Guideline 117 (Partition Coefficient (n-octanol / water), HPLC Method) |

12.5. Results of PBT and vPvB assessment

The table below presents the data of the classified substances present in the mixture.

| Hazardous substances CAS-No. | PBT / vPvB |
|---|---|
| Bis[(3,4-epoxycyclohexyl)methyl] adipate 3130-19-6 | Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria. |

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Do not empty into drains / surface water / ground water.

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 09* waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information**14.1. UN number or ID number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Maritime transport in bulk according to IMO instruments

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

Ozone Depleting Substance (ODS) (Regulation (EC) No 1005/2009): Not applicable

Prior Informed Consent (PIC) (Regulation (EU) No 649/2012): Not applicable

Persistent organic pollutants (Regulation (EU) 2019/1021): Not applicable

VOC content < 3 %
(2010/75/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H317 May cause an allergic skin reaction.

| | |
|-------------|---|
| ED: | Substance identified as having endocrine disrupting properties |
| EU OEL: | Substance with a Union workplace exposure limit |
| EU EXPLD 1: | Substance listed in Annex I, Reg (EC) No. 2019/1148 |
| EU EXPLD 2 | Substance listed in Annex II, Reg (EC) No. 2019/1148 |
| SVHC: | Substance of very high concern (REACH Candidate List) |
| PBT: | Substance fulfilling persistent, bioaccumulative and toxic criteria |
| PBT/vPvB: | Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria |
| vPvB: | Substance fulfilling very persistent and very bioaccumulative criteria |

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (SDSinfo.Adhesive@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.