

according to Regulation (EC) No 1907/2006, Article 31

Printing date 27.02.2024

Version number 6 (replaces version 5)

Revision: 27.02.2024

1 Identification of the substance/mixture and of the company/undertaking**· 1.1 Product identifier****· Trade name: 8341-Liquid****· Other Means of Identification: No Clean Flux Paste****· Related Part Number: 8341-Liquid, 8341-10ML, 8341-10MLCA, 8341B-10ML, 8341-50ML****· UFI: HGH0-205D-2003-EPAT****· 1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.**· Application of the substance / the mixture**

For use with leaded and unleaded solder during soldering process.

· 1.3 Details of the supplier of the safety data sheet M.G. Chemicals Ltd.**· Manufacturer/Supplier:**

MG Chemicals Ltd. (Head Office)

1210 Corporate Drive

Burlington, Ontario L7L 5R6

CANADA

+(1) 800-340-0772

MG Chemicals

Heame House, 23 Bliston Street

Sedgely Dudley DY3 1JA.

UNITED KINGDOM

+(44) 1663 362888 sales@mgchemicals.com

MG Chemicalst Ltd.

Level 2, Vision Exchange, Building Territorials Street,

Zone 1, Central Business, District,

Birkirkara CBD 1070,

MALTA

· Further information obtainable from: sds@mgchemicals.com**· 1.4 Emergency telephone number:**

Verisk 3E (Access code: 335388), +(44) 20 3514787

Other emergency telephone numbers: +(0) 800 680 0425

Members of the public seeking specific information on poisons should contact:

In England and Wales: NHS 111 - dial 111

In Scotland: NHS 24 - dial 111

For hazardous material incidents ONLY (leaks, spills, fires, exposures or accidents)

USA or CANADA-Call Verisk 3E at +1-866-519-4752 or +1-760-476-3962 (Service access code: 335388)

For emergencies involving the transport of dangerous goods; 24/7 service

CANADA-Call CANUTEC collect at +1-613-996-6666 or *666 on cellular phones

GB

(Contd. on page 2)

according to Regulation (EC) No 1907/2006, Article 31

Printing date 27.02.2024

Version number 6 (replaces version 5)

Revision: 27.02.2024

Trade name: 8341-Liquid

(Contd. of page 1)

2 Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS07

Eye Irrit. 2 H319 Causes serious eye irritation.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the GB CLP regulation.
- **Hazard pictograms**



GHS07

- **Signal word** Warning
- **Hazard statements**
H319 Causes serious eye irritation.
- **Precautionary statements**
 - P102 Keep out of reach of children.
 - P261 Avoid breathing mist/vapours/spray.
 - P280 Wear protective gloves/protective clothing/eye protection/face protection.
 - P284 [In case of inadequate ventilation] wear respiratory protection.
 - P302+P352 IF ON SKIN: Wash with plenty of water.
 - P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 - P342+P311 If experiencing respiratory symptoms: Call a doctor.
- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Determination of endocrine-disrupting properties**
95-14-7 benzotriazole: List II

3 Composition/information on ingredients

- **3.2 Mixtures**
- **Description:** Mixture of substances listed below with nonhazardous additions.

- **Dangerous components:**

CAS: 124-04-9	adipic acid	9.0%
EINECS: 204-673-3	Eye Irrit. 2, H319	
CAS: 95-14-7	benzotriazole	1.0%
EINECS: 202-394-1	STOT SE 2, H371; Acute Tox. 4, H302; Acute Tox. 4, H332; Eye Irrit. 2, H319	

- **Non-hazardous components and components below classification threshold**

CAS: 65997-06-0	Rosin, hydrogenated	42.0%
EINECS: 266-041-3		

(Contd. on page 3)

GB

according to Regulation (EC) No 1907/2006, Article 31

Printing date 27.02.2024

Version number 6 (replaces version 5)

Revision: 27.02.2024

Trade name: 8341-Liquid

(Contd. of page 2)

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

4 First aid measures

· **4.1 Description of first aid measures**

· **After inhalation:** Supply fresh air; consult doctor in case of complaints.

· **After skin contact:** Immediately rinse with water.

· **After eye contact:**

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

· **After swallowing:** If symptoms persist consult doctor.

· **4.2 Most important symptoms and effects, both acute and delayed**

No further relevant information available.

· **4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

5 Firefighting measures

· **5.1 Extinguishing media**

· **Suitable extinguishing agents:**

Use fire extinguishing methods suitable to surrounding conditions.

· **5.2 Special hazards arising from the substance or mixture**

Vapors are heavier than air. Vapors may travel to sources of ignition near the ground. They can cause flash fire or ignite explosively.

· **5.3 Advice for firefighters**

· **Protective equipment:** No special measures required.

6 Accidental release measures

· **6.1 Personal precautions, protective equipment and emergency procedures**

Not required.

· **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.

· **6.3 Methods and material for containment and cleaning up:** Ensure adequate ventilation.

· **6.4 Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

7 Handling and storage

· **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.

· **Information about fire - and explosion protection:** No special measures required.

· **7.2 Conditions for safe storage, including any incompatibilities**

· **Storage:**

· **Requirements to be met by storerooms and receptacles:** No special requirements.

· **Information about storage in one common storage facility:** Not required.

· **Further information about storage conditions:** Keep container tightly sealed.

· **7.3 Specific end use(s)** No further relevant information available.

GB

(Contd. on page 4)

according to Regulation (EC) No 1907/2006, Article 31

Printing date 27.02.2024

Version number 6 (replaces version 5)

Revision: 27.02.2024

Trade name: 8341-Liquid

(Contd. of page 3)

8 Exposure controls/personal protection

· 8.1 Control parameters

· **Ingredients with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

· **Additional information:** The lists valid during the making were used as basis.

· 8.2 Exposure controls

· **Appropriate engineering controls** No further data; see section 7.

· **Individual protection measures, such as personal protective equipment**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Avoid contact with the eyes.

Avoid contact with the eyes and skin.

· **Respiratory protection:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Hand protection**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye/face protection**



Tightly sealed goggles

9 Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· **General Information**

· **Physical state**

Solid

· **Colour:**

According to product specification

· **Odour:**

Characteristic

· **Odour threshold:**

Not determined.

(Contd. on page 5)

GB

according to Regulation (EC) No 1907/2006, Article 31

Printing date 27.02.2024

Version number 6 (replaces version 5)

Revision: 27.02.2024

Trade name: 8341-Liquid

(Contd. of page 4)

· Melting point/freezing point:	Undetermined.
· Boiling point or initial boiling point and boiling range	Undetermined.
· Flammability	Not determined.
· Lower and upper explosion limit	
· Lower:	Not determined.
· Upper:	Not determined.
· Flash point:	Not applicable.
· Decomposition temperature:	Not determined.
· pH	Not applicable.
· Viscosity:	
· Kinematic viscosity	Not applicable.
· Dynamic:	Not applicable.
· Solubility	
· water:	Soluble.
· Partition coefficient n-octanol/water (log value)	Not determined.
· Vapour pressure:	Not applicable.
· Density and/or relative density	
· Density at 20 °C:	1 g/cm ³
· Relative density	Not determined.
· Vapour density	Not applicable.
· Particle characteristics	
See section 3.	
· 9.2 Other information	
· Appearance:	
· Form:	Solid
· Important information on protection of health and environment, and on safety.	
· Ignition temperature:	Product is not selfigniting.
· Explosive properties:	Product does not present an explosion hazard.
· Solvent content:	
· Solids content:	100.0 %
· Change in condition	
· Evaporation rate	Not applicable.
· Information with regard to physical hazard classes	
· Explosives	Void
· Flammable gases	Void
· Aerosols	Void
· Oxidising gases	Void
· Gases under pressure	Void
· Flammable liquids	Void
· Flammable solids	Void
· Self-reactive substances and mixtures	Void
· Pyrophoric liquids	Void
· Pyrophoric solids	Void
· Self-heating substances and mixtures	Void
· Substances and mixtures, which emit flammable gases in contact with water	Void
· Oxidising liquids	Void
· Oxidising solids	Void
· Organic peroxides	Void
· Corrosive to metals	Void

(Contd. on page 6)

GB

according to Regulation (EC) No 1907/2006, Article 31

Printing date 27.02.2024

Version number 6 (replaces version 5)

Revision: 27.02.2024

Trade name: 8341-Liquid

· **Desensitised explosives**

Void

(Contd. of page 5)

10 Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
 - **Acute toxicity** Based on available data, the classification criteria are not met.
 - **LD/LC50 values relevant for classification:**
-
- ATE (Acute Toxicity Estimates)**
- Oral LD50 50,000 mg/kg
Inhalative LC50/4 h 150 mg/l
- 124-04-9 adipic acid**
- Oral LD50 11,000 mg/kg (rat)
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
 - **Serious eye damage/irritation** Causes serious eye irritation.
 - **Respiratory or skin sensitisation**
Based on available data, the classification criteria are not met.
 - **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
 - **Carcinogenicity** Based on available data, the classification criteria are not met.
 - **Reproductive toxicity** Based on available data, the classification criteria are not met.
 - **STOT-single exposure** Based on available data, the classification criteria are not met.
 - **STOT-repeated exposure** Based on available data, the classification criteria are not met.
 - **Aspiration hazard** Based on available data, the classification criteria are not met.
 - **11.2 Information on other hazards**
 - **Endocrine disrupting properties**
-
- 95-14-7 benzotriazole: List II

12 Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Endocrine disrupting properties**
For information on endocrine disrupting properties see section 11.

(Contd. on page 7)

GB

according to Regulation (EC) No 1907/2006, Article 31

Printing date 27.02.2024

Version number 6 (replaces version 5)

Revision: 27.02.2024

Trade name: 8341-Liquid

(Contd. of page 6)

· **12.7 Other adverse effects**

· **Additional ecological information:**

· **General notes:**

Water hazard class 3 (German Regulation) (Self-assessment): extremely hazardous for water
Do not allow product to reach ground water, water course or sewage system, even in small quantities.

Danger to drinking water if even extremely small quantities leak into the ground.

13 Disposal considerations

· **13.1 Waste treatment methods**

· **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· **Uncleaned packaging:**

· **Recommendation:** Disposal must be made according to official regulations.

· **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

14 Transport information

· **14.1 UN number or ID number**

· **ADR, IMDG, IATA**

not regulated

· **14.2 UN proper shipping name**

· **ADR, IMDG, IATA**

not regulated

· **14.3 Transport hazard class(es)**

· **ADR, ADN, IMDG, IATA**

· **Class**

not regulated

· **14.4 Packing group**

· **ADR, IMDG, IATA**

not regulated

· **14.5 Environmental hazards:**

Not applicable.

· **14.6 Special precautions for user**

Not applicable.

· **14.7 Maritime transport in bulk according to IMO instruments**

Not applicable.

· **UN "Model Regulation":**

not regulated

15 Regulatory information

· **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

· **Poisons Act**

· **Regulated explosives precursors**

None of the ingredients is listed.

· **Regulated poisons**

None of the ingredients is listed.

· **Reportable explosives precursors**

None of the ingredients is listed.

· **Reportable poisons**

None of the ingredients is listed.

(Contd. on page 8)

according to Regulation (EC) No 1907/2006, Article 31

Printing date 27.02.2024

Version number 6 (replaces version 5)

Revision: 27.02.2024

Trade name: 8341-Liquid

(Contd. of page 7)

- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II**
None of the ingredients is listed.
- **REGULATION (EU) 2019/1148**
- **Annex I - RESTRICTED EXPLOSIVES PRECURSORS (Upper limit value for the purpose of licensing under Article 5(3))**
None of the ingredients is listed.
- **Annex II - REPORTABLE EXPLOSIVES PRECURSORS**
None of the ingredients is listed.
- **Regulation (EC) No 273/2004 on drug precursors**
None of the ingredients is listed.
- **Regulation (EC) No 111/2005 laying down rules for the monitoring of trade between the Community and third countries in drug precursors**
None of the ingredients is listed.
- **15.2 Chemical safety assessment:**
A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
H302 Harmful if swallowed.
H319 Causes serious eye irritation.
H332 Harmful if inhaled.
H371 May cause damage to organs.
- **Department issuing SDS:** Product safety department.
- **Contact:** sds@mgchemicals.com
- **Date of previous version:** 17.01.2024
- **Version number of previous version:** 5
- **Abbreviations and acronyms:**
ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
ATE: Acute toxicity estimate values
Acute Tox. 4: Acute toxicity – Category 4
Eye Irrit. 2: Serious eye damage/eye irritation – Category 2
STOT SE 2: Specific target organ toxicity (single exposure) – Category 2
- *** Data compared to the previous version altered.**