



Connectors > Automotive Connectors > Automotive Housings



Connector System: **Wire-to-Wire**
Number of Positions: **21**
Connector & Housing Type: **Housing for Male Terminals**
Centerline (Pitch): **5 mm [.197 in]**
Sealable: **No**

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Male Terminals
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	21
Number of Rows	3

Body Features

Primary Product Color	Black
Connector & Keying Code	A

Contact Features



Contact Size	2.8mm
Contact Type	Tab
Mating Tab Width	2.8 mm[.011 in]

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	PA GF
Centerline (Pitch)	5 mm[.197 in]

Dimensions

Row-to-Row Spacing	5.5 mm
--------------------	--------

Usage Conditions

Operating Temperature (Max)	120 °C[248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB




TE Part # 2379921-1
21POS,AMP MCP 2.8,REC HSG ASSY, UNSLD


Also in the Series | 1.5/2.8 Connector System




Automotive Connector Caps & Covers (6)




Automotive Housings(27)




Automotive Terminals(53)



Insertion & Extraction Tools(1)




Other Automotive Connector Accessories(1)




PCB Headers & Receptacles(1)




Customers Also Bought




TE Part #1-2393304-1
15POS,AMP MCP 2.8,REC HSG,
UNSLD,COD A




TE Part #1-2445760-1
21POS,2.8X0.8,TAB HSG,UNSLD,COD
A




TE Part #1-2445760-2
21POS,2.8X0.8,TAB HSG,UNSLD,COD
A




TE Part #2-2445760-1
21POS,2.8X0.8,TAB HSG,UNSLD,COD
B




TE Part #2379922-2
21POS,AMP MCP 2.8,TAB HSG,
UNSLD,COD B




TE Part #2379922-3
21POS,AMP MCP 2.8,TAB HSG,
UNSLD,COD C




TE Part #2379922-4
21POS,AMP MCP 2.8,TAB HSG,
UNSLD,COD D



TE Part #2428519-1
COVER,180DEG,NTS26P



TE Part #2428520-1
CVTY PLUG,PIN STAMPED 12,CVTY
DIA,3.0



TE Part #2334198-1
HSD,180REC,180REC CABLE ASSY A/A

Documents

Product Drawings
21POS,AMP MCP 2.8,TAB HSG,UNSLD,COD A
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2379922-1_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_2379922-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_2379922-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages
Unsealed Interconnection System I&C Tran
English

Product Specifications
Product Specification
English