

WL24-2R538 W24

COMPACT PHOTOELECTRIC SENSORS

SICKSensor Intelligence.



Ordering information

Туре	Part no.
WL24-2R538	1018313

Other models and accessories → www.sick.com/W24

Illustration may differ



Detailed technical data

Features

Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	Dual lens
Dimensions (W x H x D)	27 mm x 87.5 mm x 65 mm
Housing design (light emission)	Rectangular
Sensing range max.	0 m 22 m ¹⁾
Sensing range	0 m 15 m ¹⁾
Type of light	Visible red light
Light source	LED ²⁾
Light spot size (distance)	Ø 250 mm (15 m)
Adjustment	Potentiometer

¹⁾ Reflector PL80A.

Mechanics/electronics

Supply voltage \mathbf{U}_{B}	20 V AC/DC 250 V AC/DC
Power consumption	< 2 VA
Switching output	Relay
Output function	Change-over contacts
Switching mode	Light/dark switching
Switching mode selector	Selectable via light/dark selector
Switching current (switching voltage)	2,5 A @ 250 V AC, 2,5 A @ 24 V DC, 0,125 A @ 250 V DC
Response time	≤ 10 ms

 $^{^{1)}}$ With light/dark ratio 1:1.

 $^{^{2)}}$ Average service life: 100,000 h at $\rm T_U$ = +25 $^{\circ}\rm C.$

 $^{^{2)}}$ A = V_S connections reverse-polarity protected.

 $^{^{3)}}$ C = interference suppression.

⁴⁾ Rated voltage: 250 V AC/DC.

Switching frequency	10 Hz ¹⁾
Connection type	Mini connector 7/8", 5-pin
Circuit protection	A ²⁾ C ³⁾
Protection class	II ⁴⁾
Weight	330 g
Polarisation filter	✓
Housing material	Metal, zinc diecast
Optics material	Plastic, PMMA
Enclosure rating	IP67
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493

 $^{^{1)}}$ With light/dark ratio 1:1.

Safety-related parameters

MTTF _D	478 years
DC _{avg}	0 %
T _M (mission time)	20 years

Classifications

ECLASS 5.0	27270902
ECLASS 5.1.4	27270902
ECLASS 6.0	27270902
ECLASS 6.2	27270902
ECLASS 7.0	27270902
ECLASS 8.0	27270902
ECLASS 8.1	27270902
ECLASS 9.0	27270902
ECLASS 10.0	27270902
ECLASS 11.0	27270902
ECLASS 12.0	27270902
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528


 $^{^{2)}}$ A = V_S connections reverse-polarity protected.

³⁾ C = interference suppression.

⁴⁾ Rated voltage: 250 V AC/DC.

Adjustments


WT24-2, WL24-2, WS/WE24-2, AC/DC




- ② LED signal strength indicator
- Adjustment sensing range (WT) / sensitivity (WL, WS/WE)
 Light/dark selector

Connection diagram

Cd-350




Characteristic curve



- ① Reflector PL80A
- ② Reflector PL50A
- 3 Reflector PL40A
- ④ Reflector PL30A
- ⑤ Reflector PL20A
- ® Reflective tape Diamond Grade
- ⑦ Reflector C110A


Sensing range diagram



- Sensing range
- Sensing range max.
- ① Reflector PL80A
- ② Reflector PL50A
- 3 Reflector PL40A
- Reflector PL30A
- ⑤ Reflector PL20A
- ® Reflective tape Diamond Grade
- 7 Reflector C110A

Dimensional drawing (Dimensions in mm (inch))

WL24-2



- ① Alignment sight
- ② LED signal strength indicator
- 3 Center of optical axis, sender
- ④ Center of optical axis, receiver
- ⑤ M5 threaded mounting hole, 6 mm deep
- M5 threaded mounting hole, through-hole
- ⑦ M16 screw fixing and plug rotatable by 90°

Recommended accessories

Other models and accessories → www.sick.com/W24

	Brief description	Туре	Part no.	
Mounting brackets and plates				
1	Mounting bracket, large, stainless steel, without mounting hardware for the sensor	BEF-WG-W24	4026324	
	Universal mounting bracket for reflectors, steel, zinc coated	BEF-WN-REFX	2064574	
Reflectors				
	Rectangular, screw connection, 84 mm x 84 mm, PMMA/ABS, Screw-on, 2 hole mounting	PL80A	1003865	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

