## 2mm Banana Jack w/ 10mm Round Nut M3 Threaded Stud and Hex Nuts





## **Applications**

General purpose electric and electronic testing, controlling and measuring.

## **Specifications**

Connector Type : 2mm Banana Jack
Connector Mounting : Panel Mount

Termination Type : M3 Threaded Stud & Hex Nut

Voltage Rating : CAT II 600V

Current Rating : 10AResistance :  $< 5m\Omega$ 

Contact Material : Brass, Nickel Plating

Insulator Material : Polyamide Connector Diameter : 10mm

Terminal Dimension : M3 × 8.3mm

Connector Colour : Blue, Yellow, Black, Red and Green

## **Part Number Table**

Description	Insulator Colour	Part Number
2mm Banana Jack w/ 10mm Round Nut, M3 Threaded Stud and Hex Nuts, Panel, 600V, 10A	Blue	72-13970
	Yellow	72-13972
	Black	72-13974
	Red	72-13976
	Green	72-13978

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

