




TE Internal #: 2441517-1
2.92mm Series RF Interface, Plug, 50 Ω , Screw, 0 – 40 GHz
Operating Frequency, 1 Position, -40 – 85 °C [-104 – 257 °F],
Straight, Stainless Steel
[View on TE.com >](#)

Connectors > RF Connectors > Coax Connectors



RF Interface: **2.92mm Series**
RF Connector Style: **Plug**
Impedance: **50 Ω**
RF Connector Coupling Mechanism: **Screw**
Operating Frequency: **0 – 40 GHz**

Features

Product Type Features

RF Interface	2.92mm Series
RF Connector Style	Plug
Sealable	No

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	-------------

Body Features

Cable Connector Orientation	Straight
Body Material	Stainless Steel
Body Material Finish	Passivated

Contact Features

RF Connector Center Contact Plating Material	Gold
----------------------------------------------	------



RF Connector Center Contact Material

Beryllium Copper

Mechanical Attachment

RF Connector Coupling Mechanism

Screw

RF Contact Captivation Method

Mechanical

Detent

Without

Usage Conditions

Operating Temperature Range

-40 – 85 °C[-104 – 257 °F]

Operation/Application

Operating Frequency

0 – 40 GHz

Packaging Features

Packaging Method

Bag & Box

Other

Dielectric Material

Polyetherimide (PEI)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2024 (240)
Candidate List Declared Against: JUNE 2023 (235)
SVHC > Threshold:
Pb (4.35% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 2441539-1
2.92MM F TO 2.92MM M SLIDE ON
ADAP BMRF



TE Part # 2441546-1
2.92MM F ST FIELD REPLACEABLE
RFSC



TE Part # 2441873-1
2.92MM F ST CONNECTOR W END
LAUNCH RFSC

Documents

Product Drawings

2.92 MALE TERMINATOR.STR,40G RFT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2441517-1_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2441517-1_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2441517-1_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

dnd-flyer-rf-connector-ca-tm-en

English

dnd-fly-rf-connector-catm-cn-0224

Product Specifications

Product Specification



English