

RT-N2427

ZoneControl

MULTITASK PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
RT-N2427	1063154

Other models and accessories → www.sick.com/ZoneControl

Illustration may differ



Detailed technical data

Features

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression
Dimensions (W x H x D)	20.6 mm x 99.2 mm x 48.9 mm
Sensing range max.	60 mm 900 mm
Sensing range	60 mm 900 mm
Focus	7°
Type of light	Infrared light
Light source	LED ¹⁾
Light spot size (distance)	Ø 20 mm (500 mm)
Angle of dispersion	7°
Adjustment	Potentiometer, 9 turns
Special applications	ZoneControl

 $^{^{1)}}$ Average service life: 100,000 h at T_{U} = +25 °C.

Mechanics/electronics

Supply voltage U _B	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	20 mA ³⁾

¹⁾ Limit values

 $^{^{2)}\,\}mbox{May}$ not exceed or fall below $\mbox{U}_{\mbox{\scriptsize V}}$ tolerances.

 $^{^{}m 3)}$ Without load and valve deenergized.

 $^{^{4)}}$ Do not bend below 0 °C.

 $^{^{5)}}$ A = $\rm V_{S}$ connections reverse-polarity protected.

⁶⁾ C = interference suppression.

 $^{^{7)}}$ D = outputs overcurrent and short-circuit protected.

Switching output	NPN
Switching mode	Dark switching
Signal voltage PNP HIGH/LOW	Approx. $V_S - 0.5 V / 0 V$
Output current I _{max.}	≤ 100 mA
Response time	2 ms
Switching frequency	250 Hz
Connection type	Cable with M8 male connector, 4-pin, 2 m ⁴⁾
Circuit protection	A ⁵⁾ C ⁶⁾ D ⁷⁾
Protection class	III
Weight	175 g
Housing material	Plastic, ABS
Enclosure rating	IP67
Shock and vibration resistance	According to IEC 68
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E189383 & NRKH7.E189383

¹⁾ Limit values.

Safety-related parameters

MTTF _D	1,525 years
DC _{avg}	0 %

Classifications

ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904
ECLASS 7.0	27270904
ECLASS 8.0	27270904
ECLASS 8.1	27270904
ECLASS 9.0	27270904
ECLASS 10.0	27270904
ECLASS 11.0	27270904
ECLASS 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.

 $^{^{}m 3)}$ Without load and valve deenergized.

 $^{^{4)}}$ Do not bend below 0 °C. $^{5)}$ A = V_S connections reverse-polarity protected.


⁶⁾ C = interference suppression.

⁷⁾ D = outputs overcurrent and short-circuit protected.

ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528


Connection diagram

PIN assignment




	Rx-(<u>P / N</u>)Y22x Rx-(<u>P / N</u>)Y32x Rx-(<u>P / N</u>)Y42x	<u>P</u> = PNP <u>N</u> = NPN	Rx-(<u>P / N</u>)Y23x Rx-(<u>P / N</u>)Y33x Rx-(<u>P / N</u>)Y43x	<u>P</u> = PNP <u>N</u> = NPN	Rx-BY22x Rx-BY32x Rx-BY42x	$\underline{B} = PNP / NPN$
Y	PIN4	PIN2	PIN4	PIN2	PIN4	PIN2
1	Q _{LD}	not connected	not connected	Q _{LO}	QP_{LO}	QN _{LO}
2	Q_{oo}	not connected	not connected	Q_{oo}	QP_{DD}	QN_{po}
3	Q _{LD}	Q_{to}	Q_{oo}	Q _{LO}		
4	Q _{LD}	Alarm	Alarm	Q _{LO}		
5	Q _{LD}	Health	Health	Q _{LO}		
6	Qoo	Alarm	Alarm	Q _{DO}		
7	Q _{oo}	Health	Health	Q _{po}	-	-

Cd-254




Characteristic curve



Light spot size






Distance in mm (inch)

Dimensional drawing (Dimensions in mm (inch))

R cable





- ① LED
- ② Potentiometer
- ③ Fixing hole
- 4 Cable
- ⑤ Center of optical axis, sender
- © Center of optical axis, receiver

Recommended accessories

Other models and accessories → www.sick.com/ZoneControl

	Brief description	Туре	Part no.			
Mounting brackets and plates						
0 0	Mounting bracket, steel, zinc coated, mounting hardware included	BEF-WK-WTR	2051786			
		BEF-WN-RT/IRT	2074621			
Plug connecto	Plug connectors and cables					
	 Connection type head A: Female connector, M8, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF8U14- 050VA3XLEAX	2095889			
	 Connection type head A: Male connector, M8, 4-pin, straight Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² 0.5 mm² 	STE-0804-G	6037323			

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

