


High-Precision Current Sense Resistor Surface Mount Metal Strip Power Resistors



RoHS*
COMPLIANT

FEATURES

- Temperature coefficient of resistance to ± 50 ppm/ $^{\circ}\text{C}$ max. (-55 $^{\circ}\text{C}$ to +170 $^{\circ}\text{C}$)
- Power rating: to 6 W
- Resistance tolerance: to $\pm 0.5\%$
- Resistance range: 2 m Ω to 5 m Ω
- Short time overload: $\pm 0.5\%$ Max.
- Maximum current: up to 54 A
- AEC-Q200 qualified
- Low Inductance: < 3nH
- Proprietary processing techniques produce low resistance values and improved TCR
- Working Temperature -55 $^{\circ}\text{C}$ to +170 $^{\circ}\text{C}$
- Solderable terminations



KEY APPLICATIONS

- Switching and linear power supplies
- Precision current-sensing
- Power management systems
- Automotive
- Power amplifiers
- Measurement instrumentation
- Testing & Measurement Equipment
- Medical and automatic test equipment
- DC low and high frequency sampling circuits
- Communication systems
- High current applications for the automotive market

Figure 1 – Power Derating Curve




Table 1 – Specifications


PARAMETER	CSM3920R5
Resistance Range	2 m Ω to 5 m Ω
Power Rating at 70 $^{\circ}\text{C}$	6 W (2 m Ω) 5 W (3 m Ω) 4 W (4 m Ω) 3 W (5 m Ω)
Maximum Current ⁽¹⁾	54 A
Tolerance	$\pm 0.5\%$, $\pm 1\%$, $\pm 5\%$
Temperature Coefficient Max. (-55 $^{\circ}\text{C}$ to +170 $^{\circ}\text{C}$)	± 50 ppm/ $^{\circ}\text{C}$
Operating Temperature Range	-55 $^{\circ}\text{C}$ to +170 $^{\circ}\text{C}$
Maximum Working Voltage	$(P \times R)^{1/2}$

Notes


⁽¹⁾ Maximum current for a given resistance value is calculated using $I = \sqrt{P/R}$

Figure 2 – Mechanical Dimensions in millimeters

CSM3920R5 DIMENSIONS



CSM3920R5 LAND PATTERN



Dimensions in millimeters

MODEL	RESISTANCE RANGE (mΩ)	L	A	W	D	T
CSM3920R5	2	10 ± 0.3	2.0 ± 0.3	5.2 ± 0.3	0.5 ± 0.2	0.6 ± 0.2
	3	10 ± 0.3	2.0 ± 0.3	5.2 ± 0.3	0.5 ± 0.2	0.4 ± 0.2
	4	10 ± 0.3	2.0 ± 0.3	5.2 ± 0.3	0.5 ± 0.2	0.33 ± 0.2
	5	10 ± 0.3	2.0 ± 0.3	5.2 ± 0.3	0.5 ± 0.2	0.25 ± 0.2


Land Pattern Dimensions in millimeters

MODEL	RESISTANCE RANGE (mΩ)	a	c	b
CSM3920R5	2 to 5	5.6 ± 0.1	2.7 ± 0.2	6.2 ± 0.2

Table 2 - PERFORMANCE SPECIFICATIONS

Test	Test Method	Standards	Typical	Max.
High Temperature Storage	1000h @ +170°C, unpowered	AEC-Q200 TEST 3 MIL-STD-202 Method 108	$\Delta R \leq \pm 0.5\%$	$\Delta R \leq \pm 1.0\%$
Thermal Shock	-55°C, 15min~ambient temperature < 20s ~ +155°C, 15min, 1000 cycles	AEC-Q200 TEST 16 MIL-STD-202 Method 107	$\Delta R \leq \pm 0.1\%$	$\Delta R \leq \pm 0.5\%$
Bias Humidity	+85°C, 85%RH, powered no less than 10% rated power for 1000h	AEC-Q200 TEST 7 MIL-STD-202 Method 103	$\Delta R \leq \pm 0.2\%$	$\Delta R \leq \pm 0.5\%$
Load Life	2000h @ +70°C, rated power, 90min on, 30min off +70°C refers to terminal temperature	AEC-Q200 TEST 8 MIL-STD-202 Method 108	$\Delta R \leq \pm 0.5\%$	$\Delta R \leq \pm 1.0\%$
Resistance to Solvent	Immerse in solvent for 3 min and wipe 10 times. Three cycles of three solvents. Dry at ambient temperature after cleaning	AEC-Q200 TEST 12 MIL-STD-202 Method 215	Clear marking. No visible damage	
Mechanical shock	Half Sine Wave, peak acceleration 100g's, pulse duration 6ms, 3 times in each of six directions, on three different axes	AEC-Q200 TEST 13 MIL-STD-202 Method 213	$\Delta R \leq \pm 0.05\%$	$\Delta R \leq \pm 0.2\%$
Vibration	10-2KHz, 5g's, 20min/cycle, 12 cycles in each directions of X Y Z	AEC-Q200 TEST 14 MIL-STD-202 Method 204	$\Delta R \leq \pm 0.05\%$	$\Delta R \leq \pm 0.2\%$
Resistance to Solder Heat	+260°C tin bath for 10s	AEC-Q200 TEST 15 MIL-STD-202 Method 210	$\Delta R \leq \pm 0.2\%$	$\Delta R \leq \pm 0.5\%$
Solderability	+245°C tin bath for 3s	AEC-Q200 TEST 18 IEC 60115-1 4.17	No visible damage 95% minimum coverage	
TCR	-55°C and +170°C, +20°C Ref.	AEC-Q200 TEST 19 IEC 60115-1 4.8	Max. value $\pm 50\text{ppm}/^\circ\text{C}$	
Substrate Bending	2mm. Duration: 60s	AEC-Q200 TEST 21 AEC-Q200-005	$\Delta R \leq \pm 0.01\%$	$\Delta R \leq \pm 0.1\%$
Short time Overload	5x rated voltage, 5s	IEC 60115-1 4.13	$\Delta R \leq \pm 0.1\%$	$\Delta R \leq \pm 0.5\%$
Low Temperature Storage	-55°C for 96h, unpowered	IEC 60068-2-1	$\Delta R \leq \pm 0.1\%$	$\Delta R \leq \pm 0.5\%$
Moisture Resistance	Apply T=24 h/cycle, zero power, method 7a and 7b are not required	MIL-STD-202 Method 106	$\Delta R \leq \pm 0.1\%$	$\Delta R \leq \pm 0.5\%$

Figure 3 –Part Number Information





Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. **To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.**

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.