



Main

Range	TeSys
Device short name	LA1SK
Product or component type	Auxiliary contact block
Product compatibility	LC1SK
Auxiliary contacts operation	Instantaneous
Pole contact composition	2 NC
Connections - terminals	Screw clamp terminals 1 0.00...0.01 in ² (1.5... 6 mm ²)solid Screw clamp terminals 2 0.00...0.01 in ² (1.5... 4 mm ²)solid Screw clamp terminals 1 0.00...0.01 in ² (0.5... 6 mm ²)flexible with cable end Screw clamp terminals 2 0.00...0.00 in ² (0.35... 2.5 mm ²)flexible with cable end Screw clamp terminals 1 0.00...0.01 in ² (0.35... 6 mm ²)flexible without cable end Screw clamp terminals 2 0.00...0.00 in ² (0.35... 1.5 mm ²)flexible without cable end

Complementary

Mounting location	Front side
[Ui] rated insulation voltage	690 V IEC 60947 690 V BS 5424 690 V VDE 0110 group C 690 V CSA C22.2 No 14
[Ue] rated operational voltage	690 V AC <= 400 Hz
[Ith] conventional free air thermal current	10 A 131 °F (55 °C)
Associated fuse rating	10 A gL IEC 60947 10 A gL VDE 0660
Tightening torque	7.08 lbf.in (0.8 N.m) screw clamp terminals
Width	1.06 in (27 mm)
Net weight	0.05 lb(US) (0.022 kg)

Environment

Standards	VDE 0660 BS 5424 NF C 63-110 IEC 60947
Product certifications	CSA UL
IP degree of protection	IP2x
Protective treatment	TC IEC 60068
Ambient air temperature for operation	-4...122 °F (-20...50 °C)
Ambient air temperature for storage	-58...158 °F (-50...70 °C)
Operating altitude	6561.68 ft (2000 m) without

Ordering and shipping details

Category	22371 - RELAYS, CONTROL
Discount Schedule	I12
GTIN	00785901866763
Returnability	Yes
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------