# 4W T5 LED Linkable Light Fixture







## **Description**

LED light fixture that provides exceptional light levels whilst being very energy efficient.

#### **Features**

- High output of over 100 lumens per Watt
- · Polycarbonate construction
- · Ideal for commercial, retail or domestic applications.
- Multiple lights can be linked together with the supplied 130mm interconnection lead.
- Not dimmable
- 1m Mains lead supplied

## **Specifications**

Input Voltage	AC220-240V 50Hz
Input Current	40mA (Max.)
Input Power	4W
PF	>0.5
DF	>0.7
Output Voltage	74V
Output Current	47mA
ССТ	3000K/4000K/6500K
CRI	>80
Lumen of Whole Fixture	400lm
Efficiency of Whole Fixture	100lm/w
Lumen of Led Light Source	460lm 3000K 480lm 4000/6500K
Efficiency of Led Light Source	115lm/W 3000K 120lm/w 4000/6500K
Energy Efficiency Class	E
Lumen Maintenance	3000H@96%, 6000H@92%
Led Chip Brand	SANAN
Led Type	2835 (24-26lm)
Led Quantity	26PCS (26S1P)
Light Transmittance	90%
Beam Angle	150 Deg.
Body Material	PC

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands





# 4W T5 LED Linkable Light Fixture



Packing Size	360mm×245mm×335mm / 30PCS
Lifetime	30000 Hours
IP	IP20
Working Temperature	-20°C to +45°C
Working Humidity	≤80%RH
Stock Humidity	-20°C to +65°C @ ≤95%RH

### **Diagram**





#### **Part Number Table**

Description	Part Number
4W T5 LED Linkable Light Fixture, 400lm, 3000K, 313mm	PEL01618-E

Dimensions: Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands



22/03/24 V1.0