


Part Number	ØM	H	W	D Length
RP0000381161	M6-1.0	4.0 ±0.15	10.0 +0/-0.22	6
RP0000381163				8
RP0000381165				10
RP0000381168				12
RP0000381153				16
RP0000381154				20
RP0000381155				25
RP0000381156				30
RP0000381146				40
RP0000381169	M8-1.25	5.3 ±0.15	13.0 +0/-0.27	10
RP0000381170				12
RP0000381172				16
RP0000381171				20
RP0000381173				25
RP0000381177				30
RP0000381174				35
RP0000381175				40
RP0000381305				50

REVISION	
A	INITIAL DRAWING 02.02.2024



NOTES: DO NOT SCALE DRAWING
TOLERANCE OF "L" CONFORMS TO DIN EN ISO 4017
Male (M6) Torques: $\cong 0.8$ Nm;
Male (M8) Torques: $\cong 2.5$ Nm;



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MM (MILLIMETERS).
TOLERANCES: L ≤ 4: ±0.1
4 < L ≤ 15: ±0.2
15 < L ≤ 50: ±0.3
50 < L ≤ 100: ±0.4

	NAME	DATE
DRAWN	Andrew Fletcher	02.02.24
CHK'D		
APPV'D		

MATERIAL: NYLON 6,6 (UL94V-2)
HEAT TREATMENT: N/A

TITLE: Hexagon Head Set Screw

DESIGN RIGHT. TR FASTENINGS LTD, 2024
UNDER NO CIRCUMSTANCES MUST THIS DRAWING BE COPIED
OR DISCLOSED WITHOUT FIRST OBTAINING WRITTEN
AUTHORITY.

CUSTOMER PART NUMBER:
N/A

FINISH/COLOUR: NATURAL

DRAWING NUMBER: N/A