

ADP-BNCF-BNCF-B

✓ ACTIVE

TE Internal #: ADP-BNCF-BNCF-B
In-Series Adapter, Straight, BNC, Jack Side A, BNC, Jack Side B, 2
Position
[View on TE.com >](#)



Connectors > Connector Accessories > Connector Adapters & Connector Savers



Connector Interface Adapter Type: **In-Series Adapter**
Body Orientation: **Straight**
Side A Interface: **BNC**
Side A Gender: **Jack**
Side B Interface: **BNC**

Features

Product Type Features

Connector Interface Adapter Type	In-Series Adapter
Side A Interface	BNC
Side A Gender	Jack
Side B Interface	BNC
Side B Gender	Jack
Connector System	Cable-to-Cable
Sealable	No

Configuration Features

Number of Positions	2
---------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Hermetically Sealed	No
Body Plating Material	Nickel
Body Material	Brass

Contact Features

Contact Mating Area Plating Material	Gold
--------------------------------------	------

Mechanical Attachment

--	--



RF Contact Captivation Method	Mechanical
Connector Mounting Type	Panel Mount

Housing Features

Body Orientation	Straight
------------------	----------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (3.34% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-076-BNCJKISG50
BNC RF Connector: Jack Assembly,
Isolated Ground Protection, 50 Ohm

TE Part # 5227671-1
BNC PCB VERTICAL W/PINS

Customers Also Bought

TE Part #1-1462038-1
IM01NS=IM RELAY 140mW 3V

TE Part #1658544-3
CONT,PIN,PLATED,20DF,STRIP,#22

TE Part #6-103166-5
34 MODII HDR DRRRA SHRD LF

TE Part #5103311-7
A/L LOW PRO HDR 34P RA BLACK

TE Part #1658623-8
34 NOVO MIL 30DP, LEAD FREE

TE Part #3-87631-0
34 MODIV HSG DR MRKD .100 POL

TE Part #60422-3
RING 22-20 AWG NPBR

TE Part #625380-000
D-110-0101

TE Part #ADP-SMAM-SMAF-T-G
SMA Plug to SMA Jack (2) Tee

Documents

Product Drawings
BNC Jack to BNC Jack Bulkhead
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_ADP-BNCF-BNCF-B_A.2d_dxf.zip



English

Customer View Model

ENG_CVM_CVM_ADP-BNCF-BNCF-B_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_ADP-BNCF-BNCF-B_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BNC Jack to BNC Jack Adapter

English

The FCC Road Part 15 From Concept to Approval

English

RF Coaxial Connector Gender Naming

English

RF 101 Information for the RF Challenged

English