

# Product data sheet

Specifications



Electronic alarm, Harmony XVS, black, NPN, mounting support DIN 72, 0...90dB, 16tones, 4 channels, 12...24V AC DC

XVS72BMBN

Product availability : Stock - Normally stocked in distribution facility

## Main

Range of Product	Harmony XVS
Product or Component Type	Electronic alarm
Device short name	XVS

## Complementary

Color	Black
Material	ABS (acrylonitrile butadiene-styrene) body PC (polycarbonate) terminal cover
Marking	CE
Overvoltage category	Class II EN/IEC 61140
Mounting Support	72 mm DIN rail
[Us] rated supply voltage	12...24 V DC
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	117 mA 12 V 125 mA 24 V 158 mA 12 V 200 mA 24 V
Clamping Connection Capacity	<= 1 x 1.5 mm²
Width	2.83 in (72 mm)
Height	2.83 in (72 mm)
Depth	2.73 in (69.3 mm)
Net Weight	0.40 lb(US) (0.18 kg)

## Environment

Discrete output type	NPN
Signalling type	16 tones alarm
Standards	UL 464 EN/IEC 61000-6-3 EN/IEC 61000-6-2
Product Certifications	UR

Protective treatment	TC
Ambient Air Temperature for Storage	-31...158 °F (-35...70 °C)
Ambient Air Temperature for Operation	14...122 °F (-10...50 °C)
IP degree of protection	Panel mounted IP54 EN/IEC 60529
Noise level	0...90 dB continuous or intermittent tone)1 m

## Ordering and shipping details

Category	22617-XVC TOWER LIGHTS
Discount Schedule	XV
GTIN	3606480032929
Returnability	Yes
Country of origin	ID

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.70 in (9.4 cm)
Package 1 Width	3.70 in (9.4 cm)
Package 1 Length	4.10 in (10.41 cm)
Package 1 Weight	0.60 lb(US) (0.27 kg)
Unit Type of Package 2	S03
Number of Units in Package 2	16
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	11.28 lb(US) (5.118 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	128
Package 3 Height	23.62 in (60 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	50.39 in (128 cm)
Package 3 Weight	76.19 lb(US) (34.56 kg)


## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a>
RoHS exemption information	<a href="#">Yes</a>

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
<b>Contractual warranty</b>	
Warranty	18 months

Electronic Alarm

Dimensions



Recommended replacement(s)