

R2016A-27.120-10-F-1010-X1-TR

- IATF 16949 Production Line Certified
- Reliability Testing per AEC-Q200


• SPECIFICATIONS

PARAMETER	VALUE
NOMINAL FREQUENCY	27.120 MHz
MODE OF OSCILLATION	Fundamental
FREQUENCY TOLERANCE AT 25°C	±10 ppm max
FREQUENCY STABILITY OVER TEMPERATURE	±10 ppm max
OPERATING TEMPERATURE RANGE	-40°C to +125°C
OPERABLE TEMPERATURE RANGE	-40°C to +100°C
STORAGE TEMPERATURE RANGE	-55°C to +125°C
AGING	±2 ppm first year max
LOAD CAPACITANCE	10 pF
EQUIVALENT SERIES RESISTANCE	100 Ω max
SHUNT CAPACITANCE	3.5 pF max
DRIVE LEVEL	50 μW typ, 200 μw max
INSULATION RESISTANCE	500 MΩ min @ DC 100V




Photo is not actual part

MECHANICAL SPECIFICATION



• CARRIER TAPE DIMENSIONS



NOTE: REFER TO EIA-481 FOR DIMENSIONS

PACKAGING


178 mm REEL DIAMETER 8 mm TAPE WIDTH, 4 mm PITCH QUANTITY: 3000 PIECES PER REEL

IN ACCORDANCE WITH EIA-481



R2016A-27.120-10-F-1010-X1-TR

• REFLOW PROFILE



Reflow profile			
Temperature Min Preheat	T _{SMIN}	150°C	
Temperature Max Preheat	T _{SMAX}	200°C	
Time (T _{SMIN} to T _{SMAX})	ts	60-180 sec	
Temperature	TL	217°C	
Peak Temperature	T _P	260°C	
Ramp-up rate	R _{UP}	3°C/s max	
Ramp-down rate	R _{DOWN}	6°C/s max	
Time within 5°C of Peak Temperature	tP	10 sec	
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec	
Time	tL	60-150 sec	

ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	Compliant
REACH SVHC	Compliant
HALOGEN-FREE	Compliant
ESD CLASSIFICATION LEVEL	N/A
TERMINATION FINISH	Au





AUTOMOTIVE GRADE SURFACE MOUNT CRYSTAL Page 3 of 4

R2016A-27.120-10-F-1010-X1-TR

MARKING

R27.12 xKEyw

- x 1 or 2 digits as Internal Production ID code
- y Year code

w – Week code

YEAR CODE		
Year Code		
2018	8	
2019	9	
2020	0	
2021	1	
2022	2	
2023	3	
2024	4	
2025	5	
2026	6	
2027	7	
2028	8	
2029	9	

	ALPHA WEEK CODE TABLE				
Week	Code	Week	Code	Week	Code
1	а	19	s	37	K
2	b	20	t	38	L
3	с	21	u	39	М
4	d	22	v	40	Ν
5	e	23	w	41	0
6	f	24	х	42	Р
7	g	25	У	43	Q
8	h	26	z	44	R
9	i	27	А	45	S
10	j	28	В	46	Т
11	k	29	С	47	U
12	1	30	D	48	V
13	m	31	E	49	W
14	n	32	F	50	Х
15	0	33	G	51	Y
16	р	34	Н	52	Z
17	q	35	Ι		
18	r	36	J		

APPROVAL

DRAWN BY:	KJ, March 21, 2024
APPROVED BY:	JI, March 21, 2024
REVISION:	A, Initial Release

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is accurate, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time without notice. Raltron/RAMI Tech has made expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, harmless against all damages.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.



AUTOMOTIVE GRADE SURFACE MOUNT CRYSTAL

Page 4 of 4

R2016A-27.120-10-F-1010-X1-TR

The process of manufacturing R2016A series of Automotive Grade Surface Mount Microprocessor Crystals is performed by using **Advanced Product Quality Planning (APQP)**. This technique defines and establishes the following actions:

• AEC-Q200 Qualified.

• Product design activities communicating special characteristics to the process design activity, prior to design release, linking the DFMEA to PFMEA.

• Plan, acquire and install appropriate process equipment and tooling based on design tolerances provided by the customer. – CPPD (Collaborative Product Process Design)

• Assembly personnel communicating suggestions on better ways to assemble a product prior to the completion of the design of the product. – DFA/M (Design for Assembly and Manufacturing)

• Manufacturing or Process Engineering establishing adequate Quality Controls for features of a product or parameters of a process, which still risk potential failure. – Control Plan Methodology

• Performing Stability and Capability studies on special characteristics to understand the variation present and predict future performance. – SPC (Statistical Process Control and Process Capability)

Request for **Production Part Approval Process (PPAP)** documentation must be requested at time of order placement. Requests for part approval will be supported in official PPAP format and with documented results as requested at time of order placement. Actual measurements are taken of the parts produced and are used to complete the various test sheets of PPAP.

• NOTICE

If you intend to use our product referenced above in an automotive application that may result in loss of life or assets, please do not fail to advise us of your intention beforehand. The use of the listed part in those applications is not covered by warranty, and we will not be held accountable for any liability claims. We reserve the right to not supply parts in those circumstances.