

R2520-20.000-8-2030-EXT1-TR-NS1


SPECIFICATIONS

PARAMETER	VALUE	
NOMINAL FREQUENCY	20.000 MHz	
MODE OF OSCILLATION	Fundamental	
FREQUENCY TOLERANCE AT 25°C	±20 ppm max	
FREQUENCY STABILITY OVER TEMPERATURE	±30 ppm max	
OPERATING TEMPERATURE RANGE	-40°C to +125°C	
STORAGE TEMPERATURE RANGE	-40°C to +125°C	
AGING	±2 ppm first year max	
LOAD CAPACITANCE	8 pF	
EQUIVALENT SERIES RESISTANCE	60 Ω max	
MOTIONAL CAPACITANCE	3.5 pF max	
DRIVE LEVEL	100 μW max	
INSULATION RESISTANCE @ 100 VDC	500 MΩ min	




Photo is not actual pa

MECHANICAL SPECIFICATION



CARRIER TAPE DIMENSIONS



NOTE: REFER TO EIA-481 FOR DIMENSIONS

PACKAGING


178 mm REEL DIAMETER 8 mm TAPE WIDTH, 4 mm PITCH QUANTITY: 3000 PIECES PER REEL

IN ACCORDANCE WITH EIA-481



REFLOW PROFILE

R2520-20.000-8-2030-EXT1-TR-NS1



Reflow profile				
Temperature Min Preheat	T _{SMIN}	150°C		
Temperature Max Preheat	T _{SMAX}	200°C		
Time (T _{SMIN} to T _{SMAX})	t _S	60-180 sec.		
Temperature	T∟	217°C		
Peak Temperature	T _P	260°C		
Ramp-up rate	R _{UP}	3°C/sec max.		
Ramp-down rate	R _{DOWN}	6°C/sec max.		
Time within 5°C of Peak Temperature	t _P	10 sec.		
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.		
Time	t _L	60-150 sec.		

ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	Compliant
REACH SVHC	Compliant
HALOGEN-FREE	Compliant
ESD CLASSIFICATION LEVEL	N/A
TERMINATION FINISH	Au







Page 3 of 3

MARKING

R2520-20.000-8-2030-EXT1-TR-NS1

R20.000 xx8Dyw

xx - Internal Production ID code

y – Year code

w - Week code

YEAR CODE		
Year	Code	
2019	9	
2020	0	
2021	1	
2022	2	
2023	3	
2024	4	
2025	5	
2026	6	
2027	7	
2029	8	
2029	9	

ALPHA WEEK CODE TABLE					
Week	Code	Week	Code	Week	Code
1	a	19	s	37	K
2	b	20	t	38	L
3	c	21	u	39	M
4	d	22	v	40	N
5	e	23	w	41	О
6	f	24	x	42	P
7	g	25	у	43	Q
8	h	26	Z	44	R
9	i	27	Α	45	S
10	j	28	В	46	T
11	k	29	C	47	U
12	1	30	D	48	V
13	m	31	E	49	W
14	n	32	F	50	X
15	O	33	G	51	Y
16	p	34	Н	52	Z
17	q	35	I		
18	r	36	J		

APPROVAL

DRAWN BY	KJ, March 21, 2024
APPROVED BY	JI, March 21, 2024
REVISION	A, Initial Release

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is accurate, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time without notice. Raltron/RAMI Tech does not assume any liability arising out of an application or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, harmless against all damages.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.