



Main

Range	TeSys
Device short name	VZ
Product or component type	Additional earthing block
Performance level	High performance
Contacts type and composition	Without
Product compatibility	V5 V6
Network type	AC DC
Network frequency	50/60 Hz

Complementary

Mounting location	Left Right
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
[Ith] conventional free air thermal current	175 A
Connections - terminals	Screw clamp terminals
Height	4.92 in (125 mm)
Width	1.18 in (30 mm)
Depth	2.48 in (63 mm)
Net weight	0.55 lb(US) (0.25 kg)

Environment

Standards	IEC 60947-3
Product certifications	GL CSA UL
Protective treatment	TC
IP degree of protection	IP20 IEC 60529
Mechanical robustness	Vibrations 10...150 Hz 5 gn) IEC 60068-2-6 Shocks 11 ms 15 gn) IEC 60068-2-27
Ambient air temperature for operation	-4...122 °F (-20...50 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-1

Ordering and shipping details

Category	21730 - V VARIO SWITCH
Discount Schedule	CP1
GTIN	00785901626893
Returnability	No
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------