



Main

Range	TeSys
Product name	TeSys VARIO
Device short name	VCD
Product or component type	Emergency stop switch disconnecter
Performance level	High performance
Poles description	3P
Contacts type and composition	3 NO
Network type	DC AC
Control type	Rotary handle
Rotary handle mounting style	Direct
Handle colour	Red
Handle front plate colour	Yellow
Suitability for isolation	Yes

Complementary

Rotary handle padlocking	1 to 3 padlocks 0.16...0.31 in (4...8 mm)
Marking	0 - 1
Mounting support	Handle door Switch door
Fixing mode	Hole 0.89 in (22.5 mm) handle
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	12 A
[Ithe] conventional enclosed thermal current	10 A
[Ie] rated operational current	8.1 A AC-23 Ue: 400 V
Rated operational power in W	3 KW 400...415 V AC-3) 4 KW 500 V AC-3) 1.5 KW 230...240 V AC-3) 5.5 KW 500 V AC-23A) 5.5 KW 690 V AC-3) 7.5 KW 690 V AC-23A) 3 KW 230...240 V AC-23A) 4 kW 400...415 V AC-23A)
Intermittent duty class	30
Making capacity (I Rms)	120 A 400 V AC-21A 120 A 400 V AC-22A 120 A 400 V AC-23A
[Icm] rated short-circuit making capacity	1 kA 400 V at Ipeak
[Icw] rated short-time withstand Rms current	300 A 400 V 1 s
Rated conditional short-circuit current	10 KA 400 V 12 A aM 10 kA 400 V 12 A gG
Breaking capacity	120 A 400 V AC-21A) 120 A 400 V AC-22A) 120 A 400 V AC-23A)
Device composition	Switch Handle
Mechanical durability	100000 cycles

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Electrical durability	100000 Cycles AC-21 30000 Cycles DC-1 30000 Cycles DC-2 30000 Cycles DC-3 30000 Cycles DC-4 30000 cycles DC-5
Connections - terminals	Power circuit screw clamp terminals 0.02 in ² (10 mm ²) solid Power circuit screw clamp terminals 0.01 in ² (6 mm ²) flexible - with cable end
Tightening torque	Power circuit 18.59 lbf.in (2.1 N.m) screw clamp terminals
Handle front plate dimension	60 x 60 mm
Height	2.91 in (74 mm)
Width	2.36 in (60 mm)
Net weight	0.47 lb(US) (0.215 kg)

Environment

Standards	IEC 60947-3
Product certifications	CSA UL GL CCC
Protective treatment	TC
IP degree of protection	IP20 IEC 60529 IP65
Mechanical robustness	Vibrations 10...150 Hz 1 gn) IEC 60068-2-6 Shocks 11 ms 30 Gn) IEC 60068-2-27
Ambient air temperature for operation	-4...122 °F (-20...50 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-1

Ordering and shipping details

Category	21730 - V VARIO SWITCH
Discount Schedule	CP1
GTIN	00785901431916
Returnability	No
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide which is known to the State of California to cause Carcinogen harm. For more information go to www.p65warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------