# **Product datasheet**

Specifications





# Spacial SM door switch 10 A/500 V - M20 connection

NSYMDCM20

### Main

Range	Spacial
Product Or Component Type	Door switch
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Range Compatibility	Spacial SM enclosure
Device Composition	Fixing elements 1 x switch/commutator unit
Quantity Per Set	Set of 1

# Complementary

Fixing Mode	Direct fixing - enclosure location
Input Type	NC + NO
Absolute Maximum Input	3 A/240 V

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	9.500 cm
Package 1 Length	17.500 cm
Package 1 Weight	361.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	11
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.391 kg

## **Contractual warranty**

Apr 5, 2024

Warranty 18 months

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations