



Main

Range	TeSys
Product name	TeSys LRD
Product or component type	Differential thermal overload relay
Device short name	LRD
Relay application	Motor protection
Product compatibility	LC1D40A LC1D65A LC1D50A
Network type	AC DC
Thermal protection adjustment range	17...25 A
[Ui] rated insulation voltage	Power circuit 600 V CSA Power circuit 600 V UL Power circuit 690 V IEC 60947-4-1

Complementary

Network frequency	0...400 Hz
Mounting support	Plate, with specific accessories Rail, with specific accessories Under contactor
Tripping threshold	1.14 +/- 0.06 Ir IEC 60947-4-1
[Ith] conventional free air thermal current	5 A signalling circuit
Permissible current	3 A 120 V AC-15 signalling circuit 0.22 A 125 V DC-13 signalling circuit
[Ue] rated operational voltage	690 V AC 0...400 Hz
[Uimp] rated impulse withstand voltage	6 kV
Phase failure sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control type	Red push-button stop Blue push-button reset
Temperature compensation	-4...140 °F (-20...60 °C)
Connections - terminals	Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) flexible without cable end Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) flexible with cable end Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) solid without cable end Power circuit EverLink BTR screw connectors 1 0.00...0.05 in ² (1...35 mm ²) flexible without cable end Power circuit EverLink BTR screw connectors 1 0.00...0.05 in ² (1...35 mm ²) flexible with cable end Power circuit EverLink BTR screw connectors 1 0.00...0.05 in ² (1...35 mm ²) solid without cable end
Tightening torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 44.25 lbf.in (5 N.m) EverLink BTR screw connectors
Height	2.76 in (70 mm)
Width	2.17 in (55 mm)
Depth	4.84 in (123 mm)
Net weight	0.83 lb(US) (0.375 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. This information is not intended to be used as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Protective treatment	TH IEC 60068
IP degree of protection	IP20 IEC 60529
Ambient air temperature for operation	-4...140 °F (-20...60 °C) without derating IEC 60947-4-1
Ambient air temperature for storage	-76...158 °F (-60...70 °C)
Flame retardance	V1 UL 94
Mechanical robustness	Shocks15 Gn for 11 ms IEC 60068-2-7 Vibrations4 gn IEC 60068-2-6
Dielectric strength	6 kV 50 Hz IEC 60255-5
Standards	UL 508 ATEX D 94/9/CE EN 60947-4-1 IEC 60947-5-1 CSA C22.2 No 14 IEC 60947-4-1 EN 60947-5-1
Product certifications	ABS UL ATEX INERIS CSA EAC

Ordering and shipping details

Category	22347 - CONTACTOR,D-LINE,OVERLOADS-NEW
Discount Schedule	I12
GTIN	00785901952473
Returnability	Yes
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------