

i150-RP224 i150RP

SAFETY COMMAND DEVICES





Ordering information

Туре	Part no.
i150-RP224	1064511

Other models and accessories → www.sick.com/i150RP



Detailed technical data

Features

Number of positive action N/C contacts	2
Number of N/O contacts	0
Actuation force (deflection)	≤ 125 N (300 mm)
Actuation frequency	≤ 3,600 /h
Actuation directions	1
Cord length	≤ 75 m

Safety-related parameters

B _{10d} parameter	2 x 10 ⁶ switching cycles (with small load)	
Safe state in the event of a fault	The switch has no internal fault detection and is unable to assume a safe state in the event of a fault. Fault detection is performed by the connected safety-related logic unit.	

Functions

Safe series connection With Flexi Loop (with diagnostics)	
---	--

Interfaces

Connection type	Plug connector, M12, 4-pin
Coupling nut material	Nickel-plated brass


Electrical data

Switching principle	Slow action switching element	
Number of positive action N/C contacts	2	
Number of N/O contacts	0	
Usage category	DC-13 (IEC 60947-5-1)	
Rated operating current (voltage)	2 A (24 V DC)	
Rated insulation voltage U _i	32 V	
Rated impulse with stand voltage $\mathbf{U}_{\mathrm{imp}}$	1,500 V	
Short-circuit protection	2 A	
Switching voltage	≥ 5 V DC	

≥ 5 mA (5 V DC)		
69 mm x 203 mm x 85 mm		
+ 0.84 kg		
Die cast lightweight metal		
Varnished		
1 x 10 ⁶ switching cycles		
Ambient data		
IP65 (IEC 60529)		
-25 °C +80 °C		
-25 °C +80 °C		
Classifications		
27270601		
27270690		
27270607		
27270607		

eCl@ss 7.0 27270607 eCl@ss 8.0 27270607 eCl@ss 8.1 27270607 eCl@ss 9.0 27270607 eCl@ss 10.0 27270607 eCl@ss 11.0 27270607 eCl@ss 12.0 27270607 **ETIM 5.0** EC002033 **ETIM 6.0** EC002033 **ETIM 7.0** EC002033 EC002033 **ETIM 8.0** UNSPSC 16.0901 39121545

Dimensional drawing (Dimensions in mm (inch))



Pin assignment





1	positive action N	
2	contacts 11/12	

3 positive action N/C contacts 21/22

Actuator travel diagram

Contact action over the entire actuator withdrawl distance (full insertion = 0 mm)





☐ Contacts open

Contacts closed

Switching elements

		5	
	Rope stack	Rope tensioned	Rope pulled
	<u> </u>		\sim
Switching element 22	Ŷ 43 0 0 44 33 0 0 34 ⊖ 21 0 0 22 ⊖ 11 0 0 12	43 0 0 44 33 0 0 34 21 0 0 22 11 0 0 12	9 43 o o 44 33 o o 34 21 o o 22 11 o o 12
Switching element 31	Ŷ 43 o o o o 44 ⊖ 31 o o o 32 ⊖ 21 o o o 22 ⊖ 11 o o o 12	43 0 0 44 31 ala 32 21 ala 22 11 ala 12	9 43 0 0 44 31 0 0 32 21 0 0 22 11 0 0 12

Switching element 22:

2 postive action N/C contacts + 2 N/O contact

Switching element 31:

3 postive action N/C contacts + 1 N/O contact

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

