



OLS20-BB1114142 ols

CONTRAST SENSORS





Ordering information

Туре	Part no.
OLS20-BB1114142	1095594

Other models and accessories → www.sick.com/OLS

Illustration may differ



Detailed technical data

Features

Dimensions (W x H x D)	31 mm x 62 mm x 52.5 mm
Sensing distance	≤ 100 mm
Sensing distance tolerance	± 10 mm
Housing design	Rectangular
Working range	90 mm 110 mm
Light source	LED, blue ¹⁾
Wave length	450 nm
Light spot size	180 mm x 9 mm ²⁾
Receiving filters	RG 610
Bar code types	Interleaved 2 of 5
Module width (min.)	≥ 1.5 mm
Line radius (min.)	≥ 0.5 m
Track color	Orange

 $^{^{1)}}$ Average service life: 100,000 h at T_{U} = +25 °C.

Mechanics/electronics

Supply voltage	18 V DC 30 V DC ¹⁾
Ripple	\leq 5 $V_{pp}^{2)}$

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A.

 $^{^{2)}}$ Field of view line +-90mm, field of view code +-50mm.

 $^{^{2)}\,\}mathrm{May}$ not exceed or fall below U_{V} tolerances.

³⁾ Without load.

Power consumption	< 3 W ³⁾
Sampling rate	5 ms
Accuracy optical center	± 1 mm
Switching output	Push-pull: PNP/NPN
Switching output (voltage)	Push-pull: PNP/NPN HIGH = U_V - 3 V/LOW \leq 3 V
Output current I _{max.}	< 100 mA
Connection type	Male connector M12, 5-pin
Protection class	III
Circuit protection	U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression
Enclosure rating	IP67
LED risk group	2 (IEC 62471)
Weight	250 g
Housing material	Metal, zinc diecast

 $^{^{1)}\,\}mathrm{Limit}$ values when operated in short-circuit protected network: max. 8 A.

Communication interface

IO-Link	√ , COM3 (230,4 kBaud)
Cycle time	5 ms
Process data length	21 Byte Process Data In
CANopen	✓
Digital output	Q_1
Number	1

Ambient data

Ambient operating temperature	-10 °C +55 °C
Ambient temperature, storage	-25 °C +75 °C
Ambient light immunity	50,000 lx
Shock load	According to IEC 60068
UL File No.	NRKH.E181493 & NRKH7.E181493

Classifications


ECLASS 5.0	27270906
ECLASS 5.1.4	27270906
ECLASS 6.0	27270906
ECLASS 6.2	27270906
ECLASS 7.0	27270906
ECLASS 8.0	27270906
ECLASS 8.1	27270906
ECLASS 9.0	27270906
ECLASS 10.0	27270906

 $^{^{2)}\,\}mbox{May}$ not exceed or fall below $\mbox{U}_{\mbox{\scriptsize V}}$ tolerances.

³⁾ Without load.


ECLASS 11.0	27270906
ECLASS 12.0	27270906
ETIM 5.0	EC001820
ETIM 6.0	EC001820
ETIM 7.0	EC001820
ETIM 8.0	EC001820
UNSPSC 16.0901	39121528

Dimensional drawing (Dimensions in mm (inch))



- ① Optical axis
- ② Field of view
- 3 Mounting hole, Ø 4.1 mm
- Connector M12 (rotatable up to 180°)


Adjustments



① Indicator lamps

Connection diagram

Cd-422



Recommended accessories

Other models and accessories → www.sick.com/OLS

	Brief description	Туре	Part no.	
Connection m	Connection modules			
	IO-Link V1.1 Class A port, USB2.0 port, optional external power supply 24V $/$ 1A	IOLA2US-01101 (SiLink2 Master)	1061790	
Universal bar	clamp systems			
	Plate NO4 for universal clamp, steel, Zinc plated steel (sheet), Zinc die cast (clamping bracket), Universal clamp (5322626), mounting hardware	BEF-KHS-N04	2051610	
	Mounting bar, straight, 200 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12G-A	4056054	
	Mounting bar, L-shaped, 250 x 250 mm, steel, steel, zinc coated, without mounting hardware	BEF-MS12L-B	4056053	
Codes				
	Luminescent duct tape for easy application to all types of flooring, width 2.5 cm, length 25 m, neon orange	ADHESIVE TAPE, FABRIC	5337868	
	1D bar codes in $2/5$ interleaved format, set of 108 bar codes, 9 A4 sheets of 12 bar codes each, luminescent PVC base material with protective film, codes 0001 0108, neon orange	BARCODE 7510- 038-0001-0108	5338408	
ATTENNA OF THE PROPERTY OF THE	Scope of delivery: $1 \times 90^\circ$ arc, protective film for adhesive tape, slip resistance class R10, protection against abrasion and moisture, prepared as 90° arc with a radius of 1,000 mm	TAPE 250AS-100-35	5338390	
6	Protective film for adhesive tape, slip resistance class R10, protection against abrasion and moisture, width 3,5 cm, length 50 m $$	TAPE 250AS-35-50	5338386	
	Scope of delivery: $1 \times 90^\circ$ arc, protective film for adhesive tape, slip resistance class R10, protection against abrasion and moisture, prepared as 90° arc with a radius of 500 mm	TAPE 250AS-500-35	5338389	
	Scope of delivery: $1x90^\circ$ arc, luminescent rugged PVC adhesive tape, prepared as 90° arc with a radius of 1,000 mm, neon orange	TAPE 7510- 038-1000	5338388	

OLS20-BB1114142 | OLS

CONTRAST SENSORS

	Brief description	Туре	Part no.
Q	Luminescent rugged PVC adhesive tape for easy application to all types of flooring, width 2 cm, length 25 m, neon orange	TAPE 7510- 038-20-25	5338378
	Scope of delivery: 1 x 90 $^{\circ}$ arc: luminescent rugged PVC adhesive tape, prepared as 90 $^{\circ}$ arc with a radius of 500 mm, neon orange	TAPE 7510-038-500	5338387
Plug connecto	ors and cables		
	 Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 5-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A15- 050VB5XLEAX	2096240
	Connection type head A: Male connector, M12, 5-pin, straight Description: Unshielded, Head A: male connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: - Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² Note: For field bus technology	STE-1205-G	6022083

Recommended services

Additional services → www.sick.com/OLS

	Туре	Part no.
Pre-configuration		
 Product area: OLS Voraussetzungen: SOPAS ET file or sensor app which contains the necessary configuration and is coordinated to the customer application, Uploading of the configuration or the SOPAS ET file or sensor app Range of services: Production and delivery of one or several personalized SICK products with the configuration uploaded by the customer and selected in the web ordering process Documentation: Additional label on the SICK product and its packaging with the configuration name specified by the customer and a unique configuration ID Duration: The delivery time of the pre-configured and customer-specific SICK product is identical, or in the case of temporary storage, a few days longer than with a standard SICK product 	Pre-configuration OLS20	1615148

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

