





Note:
- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:
LR3D22

Schneider Electric
Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone: +1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:	
Termination Method:	Screw Clamp
UL File/CCN:	E164353 / NKCR
CSA File:	LR43364 3211 03
Meets Standard:	IEC 60947-1
CE:	Yes
RoHS:	Yes
Weight:	0.12 lb (0.27 kg)
Power Wire Size :	#6 - #14 AWG
Control Wire Size:	#10 - #18 AWG
Power Terminal Torque:	20 lb-in (2.5 Nm)
Control Terminal Torque:	15 lb-in (1.7 Nm)
Mtg. Directly to Contactor:	Yes
Mtg. Separate from Contactor:	LAD7B10

Specification:	
Description:	TeSys D IEC Overload Relays, Amb. Comp. Bimetallic Class 10 wo Single Phase Sensitivity
Type:	TeSys D IEC Bi-Metallic Overload Relay 600V 24A
Ambient Comp. Bimetallic:	Yes
Solid State:	No
Class 10:	Yes
Class 20:	No
Single Phase Sensitivity:	No
For Use with Contactors:	LC1D25 thru LC1D32
Current Setting Range:	16A to 24A