



Main

Range	TeSys
Product or component type	Specific contactor coil
Device short name	LX9FG
Range compatibility	TeSys F LC1F contactor
Product compatibility	LC1F185 LC1F225
Control circuit type	AC 40...400 Hz low consumption
[Uc] control circuit voltage	110...115 V AC 40...400 Hz
Average resistance	10.4 Ohm inrush 68 °F (20 °C) 411 Ohm holding 68 °F (20 °C)
Inductance of closed circuit	1.46 H
Operating time	130 ms opening 35 ms closing
Mechanical durability	10 Mcycles
Maximum operating rate	2400 cyc/h 131 °F (55 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Operational 0.85...1.1 Uc 131 °F (55 °C) Drop-out 0.35...0.55 Uc 131 °F (55 °C)
Inrush power in VA	950...1180 VA 40...400 Hz 68 °F (20 °C)
Hold-in power consumption in VA	8.9...10.9 VA 40...400 Hz 68 °F (20 °C)
Heat dissipation	8...9.8 W

Environment

Ambient air temperature for operation	23...131 °F (-5...55 °C)
Net weight	1.21 lb(US) (0.55 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901441861
Returnability	Yes
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------