


Data Sheet AS07008MO-R


Specifications

| Parameters | Values | Units |
|---------------------------------|---|-------|
| Rated Input Power | 2 | Watts |
| Max Input Power | 5 | Watts |
| Impedance | 8 ± 15% | Ohms |
| SPL @ 1W/0.5m | | |
| (Average 0.8, 1.0, 1.2, 1.5kHz) | 81 ± 3 | dB |
| Resonant Frequency | 300 ± 20% | Hz |
| Frequency Range (-10 dB) | Fo ~ 10,000 | Hz |
| THD (1kHz, 0.1W) | <5% | |
| Frame Material | Stamped Steel | - |
| Diaphragm Material | Rubber + PP | |
| Magnet Material | NdFeB | - |
| Weight | 36 | Grams |
| Ingress Protection Rating | IP55 | - |
| Acceptable Soldering Methods | Hand Solder | - |
| Buzz, Rattle, etc. | Should not be audible with 4V sine wave from Fo to 4k Hz | - |
| Environmental Compliances | ROHS/REACH | - |
| Polarity | Cone shall move forward when a positive voltage is applied to the positive terminal | - |
| Operating Temperature | -20 ~ +60 | °C |
| Storage Temperature | -30 ~ +70 | °C |


Measurement Method (1W, 50cm)



Typical Frequency Response



Total Harmonic Distortion (0.1W, 50cm)



©2023, PUI Audio Inc.


Reliability Testing

| Type of Test | Test Specifications | | |
|---------------------------|---|--|--|
| High Temperature Test | 96 hours at +70°C ± 2°C followed by three hours in normal room temperature | | |
| Low Temperature Test | 96 hours at -30°C ± 3°C followed by three hours in normal room temperature | | |
| Humidity Test | 96 hours at +30°C ± 2°C with relative humidity between 90% and 95% followed by 6 hours in normal room temperature | | |
| Temperature Cycle Testing | 5 cycles according to the test below: +60°C +25°C -20°C 2hrs hr 1hr 2hrs 6hrs 6hrs | | |
| Vibration Test | Frequency 10~55~10 Hz, Amplitude 1.5 mm for 2 Hours in each axis, X, Y, and Z. | | |
| Drop Test | 75 cm free falling onto 40mm thick wooden board, 10 times. | | |
| Load Test | Speaker should not fail after applying white noise at rated power for 96 hours. | | |

After each test, SPL shall not deviate by more than ±3 dB from pre-test measurement.


©2023, PUI Audio Inc.


Dimensions



©2023, PUI Audio Inc.

Packaging





Specifications Revisions

| Revision | Description | |
|----------|--|-----------|
| - | Released from Engineering | 1/3/2020 |
| A | Revised SPL, Resonant Frequency and Frequency Response | 6/4/2020 |
| В | Revised Gasket Thickness and Tolerance | 7/7/2020 |
| С | Revised Drawing Dimensions | 8/24/2021 |

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.
- 2. Specifications subject to change or withdrawal without notice.