

COAXIAL ATTENUATORS

BNC

2 WATTS

Part Number	Frequency range (GHz)	ATTENUATION (dB)			V.S.W.R.		Power (W)		Fig.
		Nom.	DEVIATION		DC - 4	4 - 8	avg.	peak	
			DC - 4	4 - 8					
R414400000	DC - 8	0	+ 0.30	+ 0.50	≤ 1.20	≤ 1.25	2	100	1
R414401000		1	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414402000		2	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414403000		3	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414404000		4	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414405000		5	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414406000		6	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414407000		7	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414408000		8	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414409000		9	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414410000		10	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414411000		11	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414412000		12	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414413000		13	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414414000		14	± 0.30	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414415000		15	± 0.50	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414420000		20	± 0.50	± 0.50	≤ 1.20	≤ 1.25	2	100	1
R414425000		25	± 0.50	± 0.50	≤ 1.20	≤ 1.25	2	100	2
R414430000		30	± 0.80	± 0.80	≤ 1.20	≤ 1.25	2	100	2
R414440000		40	± 0.80	± 0.80	≤ 1.20	≤ 1.25	2	100	2
R414450000		50	± 1.00	± 1.00	≤ 1.20	≤ 1.25	2	100	2
R414460000		60	± 1.00	± 1.00	≤ 1.20	≤ 1.25	2	100	2





Figure	A inch (mm)	B inch (mm)	Weight (g)
1	1.83" (46.5)	.51" (13)	30
2	2.25" (57.1)		40

10 to 15 WATTS MEDIUM POWER

Part Number	Frequency range (GHz)	ATTENUATION (dB)		V.S.W.R.	Power (W)		Weight (Max) (g)
		Nominal	DEVIATION		avg.	peak	
			DC - 4				
R415403000	DC - 4	3	± 0.50	≤ 1.30	15	250	70
R415406000		6	± 0.50	≤ 1.30	12	250	70
R415410000		10	± 0.50	≤ 1.30	10	250	70
R415420000		20	± 0.50	≤ 1.30	10	250	70

