

# DBS60E-RJFK04096

DBS60

**INCREMENTAL ENCODERS** 





## Ordering information

Туре	Part no.
DBS60E-RJFK04096	1077534

Other models and accessories → www.sick.com/DBS60

Illustration may differ



#### Detailed technical data

#### Performance

Pulses per revolution	4,096
Measuring step	≤ 90°, electric/pulses per revolution
Measuring step deviation	± 36° / pulses per revolution
Error limits	Measuring step deviation x 3
Duty cycle	≤ 0.5 ± 10 %

#### Interfaces

Communication interface	Incremental
Communication Interface detail	$TTL /  HTL^{ 1)}$
Number of signal channels	6-channel
Initialization time	< 5 ms <sup>2)</sup>
Output frequency	+ 300 kHz <sup>3)</sup>
Load current	≤ 30 mA, per channel
Power consumption	≤ 0.5 W (without load)

 $<sup>^{1)}</sup>$  Output level depends on the supply voltage.

### Electrical data

Connection type	Cable, 8-wire, universal, 1.5 m <sup>1)</sup>
Supply voltage	4.5 30 V
Reference signal, number	1
Reference signal, position	90°, electric, logically gated with A and B
Reverse polarity protection	✓
Short-circuit protection of the outputs	<b>✓</b> <sup>2)</sup>

<sup>1)</sup> The universal cable connection is positioned so that it is possible to lay it without bends in a radial or axial direction.

 $<sup>^{\</sup>rm 2)}\,{\rm Valid}$  signals can be read once this time has elapsed.

 $<sup>^{3)}</sup>$  Up to 450 kHz on request.

 $<sup>^{2)}\,\</sup>mbox{Short-circuit}$  opposite to another channel, US or GND permissable for maximum 30 s.

<sup>3)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

MTTFd: mean time to dangerous failure

500 years (EN ISO 13849-1) 3)

#### Mechanical data

Mechanical design	Through hollow shaft, rear clamping	
Shaft diameter	5/8"	
Flange type / stator coupling	2-sided stator coupling, slot, screw hole circle 63–83 mm	
Weight	+ 0.25 kg <sup>1)</sup>	
Shaft material	Stainless steel	
Flange material	Aluminum	
Housing material	Aluminum	
Material, cable	PVC	
Start up torque	+ 0.5 Ncm (+20 °C)	
Operating torque	0.4 Ncm (+20 °C)	
Permissible movement static	$\pm$ 0.3 mm (radial) $\pm$ 0.5 mm (axial) <sup>2)</sup>	
Permissible movement dynamic	$\pm$ 0.1 mm (radial) $\pm$ 0.2 mm (axial) <sup>2)</sup>	
Operating speed	6,000 min <sup>-1 3)</sup>	
Maximum operating speed	9,000 min <sup>-1</sup> <sup>4)</sup>	
Moment of inertia of the rotor	50 gcm <sup>2</sup>	
Bearing lifetime	3.6 x 10 <sup>9</sup> revolutions	
Angular acceleration	≤ 500,000 rad/s²	

 $<sup>^{1)}\,\</sup>mathrm{Based}$  on encoder with male connector or cable with male connector.

#### Ambient data

EMC	According to EN 61000-6-2 and EN 61000-6-3
Enclosure rating	IP65, housing side (IEC 60529) IP65, shaft side (IEC 60529)
Permissible relative humidity 90 % (Condensation not permitted)	
Operating temperature range	–30 °C +85 °C, at more than 3,000 pulses per revolution $^{1)}$
Storage temperature range	-40 °C +100 °C, without package
Resistance to shocks	250 g, 3 ms (EN 60068-2-27)
Resistance to vibration	30 g, 10 Hz 2,000 Hz (EN 60068-2-6)

 $<sup>^{1)}</sup>$  These values relate to all mechanical versions including recommended accessories unless otherwise noted.

#### Classifications

eCl@ss 5.0	27270501
------------	----------

<sup>1)</sup> The universal cable connection is positioned so that it is possible to lay it without bends in a radial or axial direction.

 $<sup>^{2)}\,\</sup>mbox{Short-circuit}$  opposite to another channel, US or GND permissable for maximum 30 s.

<sup>&</sup>lt;sup>3)</sup> This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40°C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.


 $<sup>^{2)}\,\</sup>mathrm{Not}$  apllicable for stator coupling type C and K.

 $<sup>^{</sup>m 3)}$  Allow for self-heating of 2.6 K per 1,000 rpm when designing the operating temperature range.

<sup>&</sup>lt;sup>4)</sup> Maximum speed which does not cause mechanical damage to the encoder. Impact on the service life and signal quality is possible. Please note the maximum output frequency.

eCl@ss 5.1.4	27270501
eCl@ss 6.0	27270590
eCl@ss 6.2	27270590
eCl@ss 7.0	27270501
eCl@ss 8.0	27270501
eCl@ss 8.1	27270501
eCl@ss 9.0	27270501
eCl@ss 10.0	27270501
eCl@ss 11.0	27270501
eCl@ss 12.0	27270501
ETIM 5.0	EC001486
ETIM 6.0	EC001486
ETIM 7.0	EC001486
ETIM 8.0	EC001486
UNSPSC 16.0901	41112113

## Dimensional drawing (Dimensions in mm (inch))




- XF7 values see shaft diameter table for through hollow shaft, clamping at the back
- ① Zero pulse mark on housing
- ② Zero pulse mark on flange under stator coupling

Type Through hollow shaft with rear clamping	Shaft diameter XF7
DBS60x-RAxxxxxxxx DBS60x-R1xxxxxxxx	6 mm
DBS60x-RBxxxxxxxx DBS60x-R2xxxxxxxx	8 mm
DBS60x-RCxxxxxxxx DBS60x-R3xxxxxxxx	3/8"

Type Through hollow shaft with rear clamping	Shaft diameter XF7
DBS60x-RDxxxxxxxx DBS60x-R4xxxxxxxx	10 mm
DBS60x-RExxxxxxxx DBS60x-R5xxxxxxxxx	12 mm
DBS60x-RFxxxxxxxx DBS60x-R6xxxxxxxx	1/2"
DBS60x-RGxxxxxxxx DBS60x-R7xxxxxxxxx	14 mm
DBS60x-RHxxxxxxxx DBS60x-R8xxxxxxxx	15 mm
DBS60x-RJxxxxxxxxx	5/8"

## Attachment specifications


Through hollow shaft with rear clamping



#### Customer side

Type Through hollow shaft with rear clamping	Shaft diameter xj7
DBS60x-RAxxxxxxxx DBS60x-R1xxxxxxxxx	6 mm
DBS60x-RBxxxxxxxx DBS60x-R2xxxxxxxxx	8 mm
DBS60x-RCxxxxxxxx DBS60x-R3xxxxxxxxx	3/8"
DBS60x-RDxxxxxxxx DBS60x-R4xxxxxxxx	10 mm
DBS60x-RExxxxxxxx DBS60x-R5xxxxxxxx	12 mm
DBS60x-RFxxxxxxxxx DBS60x-R6xxxxxxxxx	1/2"
DBS60x-RGxxxxxxxx DBS60x-R7xxxxxxxxx	14 mm
DBS60x-RHxxxxxxxxx DBS60x-R8xxxxxxxxx	15 mm
DBS60x-RJxxxxxxxx	5/8"


## PIN assignment




Wire colors (ca- ble connection)	Male connector M12, 8-pin	Male connector M23, 12-pin	TTL/HTL 6- channel signal	Explanation
Brown	1	6	A-	Signal wire
White	2	5	A	Signal wire
Black	3	1	B-	Signal wire
Pink	4	8	В	Signal wire
Yellow	5	4	Z-	Signal wire
Purple	6	3	Z	Signal wire
Blue	7	10	GND	Ground connection
Red	8	12	+U <sub>s</sub>	Supply voltage
-	-	9	Not assigned	Not assigned
-	F	2	Not assigned	Not assigned
-	-	11	Not assigned	Not assigned
-	F	7	Not assigned	Not assigned
Screen	Screen	Screen	Screen	Screen connected to encoder housing

## **Diagrams**





Signal outputs for electrical interfaces TTL and HTL




Cw with view on the encoder shaft in direction "A", compare dimensional drawing.

Supply voltage	Output
4,5 V 5,5 V	ΠL
10 V 30 V	ΠL
10 V 27 V	HTL
4,5 V 30 V	TTL/HTL universal
4,5 V 30 V	ΠL

## Operation note

Through hollow shaft with rear clamping



- ① Zero pulse mark on flange
- ② Zero pulse is active when screw of clamping is inline with zero pulse mark on flange or housing mark

#### Recommended accessories

Other models and accessories → www.sick.com/DBS60

	Brief description	Туре	Part no.
Plug connecto	ors and cables		
<u></u>	Head A: cable Head B: Flying leads Cable: SSI, Incremental, HIPERFACE <sup>®</sup> , PUR, halogen-free, shielded	LTG-2308-MWENC	6027529
	Head A: cable Head B: Flying leads Cable: SSI, Incremental, PUR, shielded	LTG-2411-MW	6027530
<u></u>	Head A: cable Head B: Flying leads Cable: SSI, Incremental, PUR, halogen-free, shielded	LTG-2512-MW	6027531
	Head A: cable Head B: Flying leads Cable: SSI, TTL, HTL, Incremental, PUR, halogen-free, shielded	LTG-2612-MW	6028516
	Head A: male connector, M12, 8-pin, straight, A-coded Cable: Incremental, shielded	STE-1208-GA01	6044892
	Head A: male connector, M23, 12-pin, straight Cable: HIPERFACE <sup>®</sup> , SSI, Incremental, shielded	STE-2312-G01	2077273
		STE-2312-GX	6028548
Shaft adapta	ion		
	Collet plastic insulated for hollow shaft, shaft diameter 6 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-006-P	2076228
	Collet metal for hollow shaft, shaft diameter 8 mm, outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-008-M	2076219
	Collet plastic insulated for hollow shaft, shaft diameter 8 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-008-P	2076229
	Collet metal for hollow shaft, shaft diameter 10 mm, outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-010-M	2076220
	Collet plastic insulated for hollow shaft, shaft diameter 10 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-010-P	2076230
	Collet metal for hollow shaft, shaft diameter 11 mm, outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-011-M	2094671
	Collet metal for hollow shaft, shaft diameter 12 mm, outer diameter $5/8$ " (15.875 mm), metal	SPZ-58Z-012-M	2076221
	Collet plastic insulated for hollow shaft, shaft diameter 12 mm, outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-012-P	2076231
	Collet metal for hollow shaft, shaft diameter 14 mm, outer diameter 5/8" (15.875 mm), metal $$	SPZ-58Z-014-M	2076222

# DBS60E-RJFK04096 | DBS60

INCREMENTAL ENCODERS

	Brief description	Туре	Part no.
	Collet plastic insulated for hollow shaft, shaft diameter 14 mm, outer diameter $5/8$ " (15.875 mm), plastic	SPZ-58Z-014-P	2076232
	Collet metal for hollow shaft, shaft diameter 15 mm, outer diameter 5/8" (15.875 mm), metal $$	SPZ-58Z-015-M	2076223
	Collet plastic insulated for hollow shaft, shaft diameter 15 mm, outer diameter $5/8$ " (15.875 mm), plastic	SPZ-58Z-015-P	2076233
	Collet metal for hollow shaft, shaft diameter 1/2" (12.7 mm), outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-12Z-M	2076225
	Collet plastic insulated for hollow shaft, shaft diameter 1/2" (12.7 mm), outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-12Z-P	2076227
	Collet metal for hollow shaft, shaft diameter 3/8" (9.525 mm), outer diameter 5/8" (15.875 mm), metal	SPZ-58Z-38Z-M	2076224
	Collet plastic insulated for hollow shaft, shaft diameter 3/8" (9.525 mm), outer diameter 5/8" (15.875 mm), plastic	SPZ-58Z-38Z-P	2076226

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

## **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

