# 5146800-1 - ACTIVE

TE Internal #: 5146800-1 DC Jack Connectors, Board-to-Board, 5 Position, .197 in [5 mm] Centerline, Receptacle, 50 VDC, Vertical, Printed Circuit Board, Power & Signal

View on TE.com >



Connectors > PCB Connectors > Battery Connectors & Holders > DC Jack Connectors



Connector System: Board-to-Board Number of Positions: 5 Centerline (Pitch): 5 mm [.197 in ] Connector & Housing Type: Receptacle Operating Voltage: 50 VDC

### Features

### Product Type Features

Connector System

Connector & Housing Type

Connector & Contact Terminates To

Board-to-Board

Receptacle

Printed Circuit Board

#### **Configuration Features**

Number of Positions	5
PCB Mount Orientation	Vertical
Electrical Characteristics	
Operating Voltage	50 VDC
Contact Features	
Contact Current Rating (Max)	8.8 A
Mechanical Attachment	
PCB Mount Retention	Without
Connector Mounting Type	Board Mount
Housing Features	
Centerline (Pitch)	5 mm[.197 in]
Usage Conditions	
Operating Temperature Range	-30 – 70 °C[-22 – 158 °F]
Operation/Application	

**C** For support call+1 800 522 6752

### 5146800-1

DC Jack Connectors, Board-to-Board, 5 Position, .197 in [5 mm] Centerline, Receptacle, 50 VDC, Vertical, Printed Circuit Board, Power & Signal



Circuit Application	Power & Signal
Packaging Features	
Packaging Quantity	121
Packaging Method	Tray
Product Compliance For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

## **Compatible Parts**




### 5146800-1

DC Jack Connectors, Board-to-Board, 5 Position, .197 in [5 mm] Centerline, Receptacle, 50 VDC, Vertical, Printed Circuit Board, Power & Signal



### Customers Also Bought



TE Part #0298696001

DWFC-8/2-X-STK

### Documents

Product Drawings BATT INT,KEYLESS,5P,7.2V

English

CAD Files Customer View Model ENG\_CVM\_5146800-1\_0.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_5146800-1\_O.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_5146800-1\_O.2d\_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use

**S** For support call+1 800 522 6752

### 5146800-1

DC Jack Connectors, Board-to-Board, 5 Position, .197 in [5 mm] Centerline, Receptacle, 50 VDC, Vertical, Printed Circuit Board, Power & Signal



Datasheets & Catalog Pages 2\_PIECE\_POWER\_CONNECTORS\_qrg\_4-1773458-1

English

Product Specifications Application Specification

English