

SLT060-0B010J700 SLT

SENSOR VISUALIZATION





Ordering information

Туре	Part no.
SLT060-0B010J700	6075938

Other models and accessories → www.sick.com/SLT



Detailed technical data

Features

Product category	LED signal lamp
Application	Indoor area
Features	
Number of colors	21, pre-defined
Number of LED segments	20
Types of light	Continuous light, blinking light, flashing light, pulse light
Light frequency	Slow (0.5 Hz), medium (1.5 Hz), fast (2.0 Hz)
Dimmer function	Yes
Brightness levels	0% 100%, can be adjusted in 10% increments
Operating modes	
Signal lamp mode	✓
Filling level mode	✓
Animation mode	✓
Further functions	IO-Link signal lamp Parameterization via IO-Link Simple configuration directly via the SOPAS ET user interface, the engineering tool from SICK

Mechanics/electronics

Connections	
IO-Link	1 x M12, 5-pin male connector, A-coded
Nominal voltage	24 V DC
Supply voltage	18 V DC 30 V DC
Current consumption	\leq 300 mA $^{1)}$

 $^{^{1)}\,\}mbox{Including accessories}$ for beeper SLB060-0B010K700.

 $^{^{2)}}$ For 0.1 ms.

Switch-on current	30 A ²⁾
Switch-on time	0.1 ms
Housing material	Polycarbonat (PC)
Housing color	Black
Weight	590 g
Dimensions (W x H x D)	60 mm x 306 mm x 60 mm
Mounting direction	Vertical
Protection class	III
Enclosure rating	IP65
UL File No.	E198242

 $^{^{1)}}$ Including accessories for beeper SLB060-0B010K700. $^{2)}$ For 0.1 ms.

Communication interface

Communication interface	IO-Link V1.12, Port Class A
Communication Interface detail	COM2 (38,4 kBaud)
Cycle time	< 8 ms
Process data length	2 Byte Out
Operator interfaces	SOPAS ET, the engineering tool for configuration (connection to an IO-Link master required)
Additional interfaces	Interface for accessories for beeper SLB060-0B010K700
Optical indicators	1 LED (green, for IO-Link communication)

Ambient data


Ambient operating temperature	-25 °C +50 °C
Ambient temperature, storage	-30 °C +60 °C
Permissible relative humidity	90 % (Non-condensing)
Electromagnetic compatibility (EMC)	EN 61000-6-4 / EN 61000-6-2

Classifications

eCl@ss 5.0	27371220
eCl@ss 5.1.4	27371220
eCl@ss 6.0	27371220
eCl@ss 6.2	27371220
eCl@ss 7.0	27371220
eCl@ss 8.0	27371220
eCl@ss 8.1	27371220
eCl@ss 9.0	27371220
eCl@ss 10.0	27371220
eCl@ss 11.0	27371220
eCl@ss 12.0	27371220
ETIM 5.0	EC000232
ETIM 6.0	EC000232
ETIM 7.0	EC000232
ETIM 8.0	EC000232

39121107

Dimensional drawing (Dimensions in mm (inch))



- ① Cover
- ② LED segment display
- ③ IO-Link status LED
- ④ Fastening nuts (1 x); width across 46, polycarbonate (PC)
- ⑤ SLB060-0B010K700 buzzer (optional accessories)
- ⑥ IO-Link connection, male connector, M12, 5-pin
- 7 Thread 1/2"

Recommended accessories

Other models and accessories → www.sick.com/SLT

	Brief description	Туре	Part no.	
Signal and sta	Signal and status indicators			
	This product is a buzzer unit exclusively for model SLT060-0B010J700.	SLB060-0B010K700	6076072	
Plug connectors and cables				
No No.	Head A: female connector, M12, 4-pin, straight, A-coded Head B: male connector, M12, 4-pin, straight, A-coded Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 1 m	YF2A14- 010UB3M2A14	2095997	
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: male connector, M12, 4-pin, straight, A-coded Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 2 m	YF2A14- 020UB3M2A14	2096000	
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: male connector, M12, 4-pin, straight, A-coded Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 5 m	YF2A14- 050UB3M2A14	2096001	

	Brief description	Type	Part no.
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: male connector, M12, 4-pin, straight, A-coded Cable: Sensor/actuator cable, PUR, halogen-free, unshielded, 10 m	YF2A14- 100UB3M2A14	2096002
Others			
	IO-Link V1.1 Class A port, USB2.0 port, optional external power supply 24V $/$ 1A		On request
Sensor Integra	ation Gateway		
	 Further functions: Web server integrated, USB connection for easy configuration of the SIG200 Sensor Integration Gateway with SOPAS ET, the engineering tool from SICK, logic editor is available for easy configuration of logic functions Connection CONFIG: 1 x M8, 4-pin female connector, USB 2.0 (USB-A) Logic editor: yes Communication interface: IO-Link, USB, Ethernet, PROFINET, REST API Product category: IO-Link Master 	SIG200-0A0412200	1089794
	Description: The SIG200 Sensor Integration Gateway is an IO-Link master with 4 configurable ports through which the IO-Link devices or standard inputs or standard outputs can be connected to a PLC or cloud application using the REST API. Further functions: Web server integrated, USB connection for easy configuration of the SIG200 Sensor Integration Gateway with SOPAS ET, the engineering tool from SICK, logic editor is available for easy configuration of logic functions Connection CONFIG: 1 x M8, 4-pin female connector, USB 2.0 (USB-A) Logic editor: yes Communication interface: IO-Link, USB, Ethernet, EtherNet/IP™, REST API Product category: IO-Link Master	SIG200-0A0512200	1089796
	 Further functions: Web server integrated, USB connection for easy configuration of the SIG200 Sensor Integration Gateway with SOPAS ET, the engineering tool from SICK, logic editor is available for easy configuration of logic functions Connection CONFIG: 1 x M8, 4-pin female connector, USB 2.0 (USB-A) Logic editor: yes Communication interface: IO-Link, USB, Ethernet, REST API Product category: IO-Link Master 	SIG200-0A0G12200	1102605

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

