



### Main

Range of Product	L100/300
Series name	Severe duty
Product or Component Type	Limit switch lever
Device short name	L100/300
Associated complete product	HML300 L300 HL100 ML300 HML100 ML100 L100 HL300
Movement of operating head	Rotary
Type of operator	Aluminium stay put forked arm with rollers 2.25 in (57.15 mm) - adjustable angle 75° to 180° forked arm with rollers
Type of roller	2 steel outside roller 0.75 in (19.05 mm) 0.25 in (6.35 mm)
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Switch actuation	By specific cam
Net Weight	0.1 lb(US) (0.05 kg)

### Environment

Ambient air temperature for operation	-10...185 °F (-23...85 °C)
Ambient Air Temperature for Storage	-10...185 °F (-23...85 °C)
Environmental characteristic	Standard environment


### Ordering and shipping details

Category	US10DS121519
Discount Schedule	0DS1
GTIN	785901176008
Returnability	No
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.30 in (13.462 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	7.60 in (19.304 cm)
Package 1 Weight	1.60 oz (45.359 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
For all Reach Rohs enquiries contact us at	<a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>

## Contractual warranty

Warranty	18 months
----------	-----------