

GL10-R9812 G10

**SMALL PHOTOELECTRIC SENSORS** 





## Ordering information

Туре	Part no.
GL10-R9812	1076130

Included in delivery: BEF-G10UC01 (1), P250 (1)
Other models and accessories → www.sick.com/G10

Illustration may differ



#### Detailed technical data

#### **Features**

Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	Dual lens
Dimensions (W x H x D)	20 mm x 50 mm x 51.5 mm
Housing design (light emission)	Rectangular
Sensing range max.	0.08 m 15 m <sup>1)</sup> 0.08 m 12 m <sup>2)</sup>
Sensing range	0.15 m 12 m <sup>1)</sup> 0.15 m 10 m <sup>2)</sup>
Type of light	Visible red light
Light source	PinPoint LED <sup>3)</sup>
Light spot size (distance)	Ø 58 mm (5 m)
Wave length	625 nm
Adjustment	Potentiometer, 270°

<sup>&</sup>lt;sup>1)</sup> Reflector PL80A.

<sup>&</sup>lt;sup>2)</sup> Reflector P250.

 $<sup>^{3)}</sup>$  Average service life: 100,000 h at  $\rm T_U$  = +25  $^{\circ}\rm C.$ 

### Mechanics/electronics

Supply voltage	24 V AC/DC 240 V AC/DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Power consumption	≤ 2.5 VA
Switching output	Relay, SPDT, electrically isolated <sup>3)</sup>
Switching load max. (current/voltage)	0.11 A (250 V DC) 3 A (30 V DC) 3 A (250 V AC)
Response time	≤ 10 ms
Switching frequency	20 Hz <sup>4)</sup>
Connection type	Cable, 5-wire, 5 m <sup>5)</sup>
Cable material	PVC
Conductor cross section	0.25 mm <sup>2</sup>
Circuit protection	C <sup>6)</sup>
Protection class	$\Pi^{(7)}$
Weight	115 g
Polarisation filter	✓
Interference emission	EN 61000-6-3 (2011-09) <sup>8)</sup>
Housing material	Plastic, ABS/PMMA
Enclosure rating	IP67
Relay switching cycles min.	100.000 cycles (3 A)
Items supplied	Mounting bracket BEF-G10UC01, Reflector P250
Electromagnetic compatibility (EMC)	EN 60947-5-2 EN 61000-6-3 (2011-09)
Ambient operating temperature	-30 °C +60 °C <sup>9)</sup>
Ambient temperature, storage	-40 °C +70 °C
UL File No.	NRKH.E348498 & NRKH7.E348498
More standards	UL325 <sup>10)</sup>

<sup>&</sup>lt;sup>1)</sup> +- 10 %.

#### Classifications

eCl@ss 5.0	27270902
eCl@ss 5.1.4	27270902
eCl@ss 6.0	27270902
eCl@ss 6.2	27270902
eCl@ss 7.0	27270902

 $<sup>^{2)}</sup>$  May not exceed or fall below  $\mathrm{U}_{\mathrm{v}}$  tolerances.

 $<sup>^{</sup>m 3)}$  Provide suitable spark suppression for inductive or capacitive loads.

<sup>4)</sup> With light/dark ratio 1:1.

<sup>&</sup>lt;sup>5)</sup> Do not bend below 0 °C.

 $<sup>^{6)}</sup>$  C = interference suppression.

<sup>&</sup>lt;sup>7)</sup> Reference voltage: 250 V AC.

<sup>8)</sup> In the case of a DC supply (ref. to EN 61000-6-3) the length of cable between the supply source and the sensor must be < 30 m.

<sup>&</sup>lt;sup>9)</sup> UL: 0 °C ... +50 °C.

<sup>&</sup>lt;sup>10)</sup> Complies with the UL325 standard when used with sturdy protection hood (e.g. BEF-G10WSG, 2071960).


# GL10-R9812 | G10

## SMALL PHOTOELECTRIC SENSORS

eCI@ss 8.0	27270902
eCl@ss 8.1	27270902
eCl@ss 9.0	27270902
eCl@ss 10.0	27270902
eCl@ss 11.0	27270902
eCl@ss 12.0	27270902
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528

## Connection diagram


#### Cd-163



#### Characteristic curve


#### GL10

#### Operating reserve



## Light spot size


#### Light spot size



5 (16.4) Distance in m (feet)

## Sensing range diagram


#### GL10



15 (49.2)

- Sensing range
- Sensing range max.
- ① Reflective tape REF-IRF-56② Reflector PL20A
- ③ Reflector PL30A
- ④ Reflector P250 ⑤ Reflector PL40A
- 6 Reflector PL80A


### Adjustments



6 Adjustment of sensing range

### Dimensional drawing (Dimensions in mm (inch))

GTE10, GL10, GL10G, AC/DC, cable



- ① Center of optical axis, sender
- ② Center of optical axis, receiver
- 3 Mounting hole, Ø 4.2 mm
- 4 LED indicator yellow: Status of received light beam
- ⑤ LED indicator green: power on

#### Recommended accessories

Other models and accessories → www.sick.com/G10

	Brief description	Туре	Part no.	
Universal bar clamp systems				
1013	Q-Lock, bar clamp system for G10 and reflector P250, Die-cast zinc, steel, zinc coated	BEF-KHSQ12R01	2071260	
Mounting brackets and plates				
	Universal mounting bracket for reflectors, steel, zinc coated	BEF-WN-REFX	2064574	
Plug connectors and cables				
	Head A: male connector, M12, 5-pin, straight Cable: unshielded For field bus technology	STE-1205-G	6022083	
Reflectors				
	Rectangular, screw connection, 51 mm x 61 mm, PMMA/ABS, Screw-on, 2 hole mounting	P250	5304812	

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

