

GRTE18-P1152

GR18

CYLINDRICAL PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
GRTE18-P1152	1074997

Other models and accessories → www.sick.com/GR18

Illustration may differ



Detailed technical data

Features

Functional principle	Photoelectric proximity sensor
Functional principle detail	Energetic
Dimensions (W x H x D)	18 mm x 18 mm x 71.5 mm
Housing design (light emission)	Cylindrical
Thread diameter (housing)	M18 x 1
Optical axis	Axial
Sensing range max.	5 mm 550 mm ¹⁾
Sensing range	10 mm 400 mm ¹⁾
Type of light	Infrared light
Light source	LED ²⁾
Light spot size (distance)	Ø 26 mm (400 mm)
Wave length	850 nm
Adjustment	Potentiometer
Indication	
LED green	Operating indicator Static on: power on
LED yellow	Status of received light beam Static on: object present Static off: object not present

 $^{^{1)}}$ Object with 90% remission (based on standard white, DIN 5033).

 $^{^{2)}}$ Average service life: 100,000 h at T_U = +25 °C.

Mechanics/electronics

Supply voltage	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	30 mA
Switching output	PNP
Output function	Complementary
Switching mode	Light/dark switching
Signal voltage PNP HIGH/LOW	V_S - ($\leq 3 \text{ V}$) / approx. 0 V
Output current I _{max.}	\leq 100 mA $^{3)}$
Response time	< 1,000 µs ⁴⁾
Switching frequency	500 Hz ⁵⁾
Connection type	Cable, 4-wire, 2 m ⁶⁾
Cable material	PVC
Circuit protection	A ⁷⁾ B ⁸⁾ D ⁹⁾
Protection class	III
Housing material	Metal, Nickel-plated brass and ABS
Optics material	Plastic, PMMA
Enclosure rating	IP67
Items supplied	Fastening nuts (2 x)
Electromagnetic compatibility (EMC)	EN 60947-5-2
Ambient operating temperature	-25 °C +55 °C ¹⁰⁾
Ambient temperature, storage	-40 °C +70 °C
UL File No.	E348498

 $^{^{1)}}$ Limit values. Operated in short-circuit protected network: max. 8 A.

Classifications

eCl@ss 5.0	27270903
eCl@ss 5.1.4	27270903
eCl@ss 6.0	27270903
eCl@ss 6.2	27270903
eCl@ss 7.0	27270903
eCl@ss 8.0	27270903
eCl@ss 8.1	27270903

 $^{^{2)}\,\}text{May}$ not exceed or fall below U_{V} tolerances.

 $^{^{3)}}$ At Uv > 24 V or ambient temperature > 49 °C, IA max. = 50 mA.

 $^{^{4)}}$ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

 $^{^{6)}}$ Do not bend below 0 °C.

 $^{^{7)}}$ A = V_S connections reverse-polarity protected.

⁸⁾ B = inputs and output reverse-polarity protected.

⁹⁾ D = outputs overcurrent and short-circuit protected.

 $^{^{10)}}$ At U_V <=24V and I_A<50mA.

GRTE18-P1152 | GR18

CYLINDRICAL PHOTOELECTRIC SENSORS

eCl@ss 9.0	27270903
eCl@ss 10.0	27270904
eCl@ss 11.0	27270904
eCl@ss 12.0	27270903
ETIM 5.0	EC001821
ETIM 6.0	EC001821
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

Connection diagram


Cd-094



Characteristic curve

GRTE18S, 400 mm


Operating reserve



- ① Sensing range on black, 6% remission
- ② Sensing range on gray, 20 % remission
- 3 Sensing range on white, 90% remission

Light spot size


Diameter in mm (inch)



Distance in mm (inch)

Sensing range diagram

GRTE18S, 400 mm




- Sensing range Sensing range max.
- ① Sensing range on black, 6% remission
- ② Sensing range on gray, 20 % remission
- 3 Sensing range on white, 90% remission

Response range

GRTE18S, 400 mm

Parallel operating range y in mm (inch)




Distance x in mm (inch)

Adjustments

GRTB18(S), GRTE18(S), Sensing range setting: Potentiometer, 270°


Sensing range





Dimensional drawing (Dimensions in mm (inch))

GRTE18, GRL18, GRSE18, metal, cable, straight



- ① Connection cable 2 m
- ② Threaded mounting hole M18 x 1
- 3 LED indicator yellow
- 4 LED indicator green
- Sensitivity control: potentiometer 270°
- Fastening nuts (2x); width across 24, metal

Recommended accessories

Other models and accessories → www.sick.com/GR18

	Brief description	Туре	Part no.		
Mounting brackets and plates					
40	Mounting bracket for M18 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M18	5308446		
Plug connectors and cables					
	Head A: male connector, M12, 4-pin, straight Cable: unshielded	STE-1204-G	6009932		

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

