



Main

Range of Product	Pumptrol
Product or Component Type	Float switch
Device Application	Open tank heavy duty
Device short name	9036G
Product Specific Application	Liquid level control
Electrical circuit type	Power circuit
Quantity per Set	Set of 1
Type of Packing	Individual

Complementary

Product destination	For open tank or sump
Device mounting	Pedestal
Cable entry number	3 knock-outs for 1/2" conduit UL 508
Contacts type and composition	NC-NO, snap action, DPST-DB, Form Zb
Controlled fluid	Fresh water specific gravity of 0.85 in or higher Sea water specific gravity of 0.85 in or higher Hydraulic oil specific gravity of 0.85 in or higher Corrosive fluid specific gravity of 0.85 in or higher
Motor power kW	0.37 KW 0.5 hp)115 V DC 0.37 KW 0.5 hp)230 V DC 0.75 KW 1 hp)115 V AC, 1 phase 1.5 KW 2 hp)230 V AC, 1 phase 1.5 KW 2 hp)460 V AC, 1 phase 1.5 kW 2 hp)475 V AC, 1 phase
Electrical connection	Screw-clamp terminals 10 AWG
Contact operation	Contacts close on liquid rise
Float movement	Variable adjustable
Float position	Any
Float rod angle	Vertical
Force down to trip	27 Ozf long lever 39 ozf short lever
Force up to trip	21 Ozf long lever 33 ozf short lever
Short-circuit protection	20 A cartridge fuse gG
Local signalling	Without
Enclosure Material	Noryl thermoplastic resin or equivalent
Operating position	Vertical position only
Electrical durability	100 cycles 60 cyc/mn
Mechanical durability	300 cycles
Terminal block type	4 terminals
Maximum operating rate	60 cyc/mn
[Ui] rated insulation voltage	575 V UL 508
Net Weight	2.5 lb(US) (1.13 kg)
Terminals description ISO n°1	Line-load-load-line
Factory modification	Without
Kit composition	Rod and float are to be choosen in accessories Float switch

Environment

Standards	UL 508 CE
Ambient air temperature for operation	-22...200 °F (-30...93 °C)
Ambient Air Temperature for Storage	-22...200 °F (-30...93 °C)
NEMA degree of protection	NEMA 1 UL 50
Product Certifications	UL Listed[RETURN]CSA

Ordering and shipping details

Category	US1CP7G21591
Discount Schedule	CP7G
GTIN	785901054016
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19.05 in (48.387 cm)
Package 1 Width	7.50 in (19.05 cm)
Package 1 Length	48.39 in (122.903 cm)
Package 1 Weight	2.50 lb(US) (1.134 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------