

WL9-3F2234S20 w9

SMALL PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
WL9-3F2234S20	1050928

Other models and accessories → www.sick.com/W9

Illustration may differ



Detailed technical data

Features

Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	Autocollimation
Dimensions (W x H x D)	12.2 mm x 49.8 mm x 23.6 mm
Housing design (light emission)	Rectangular
Mounting hole	M3
Sensing range max.	0 m 5 m ¹⁾
Sensing range	0 m 3 m ¹⁾
Type of light	Visible red light
Light source	PinPoint LED ²⁾
Light spot size (distance)	Ø 45 mm (1.5 m)
Wave length	650 nm
Adjustment	Single teach-in button Cable
Special features	Inclusive DG-Folie 15 x 20 mm External teach

¹⁾ Reflector PL80A.

 $^{^{2)}}$ Average service life: 100,000 h at $\rm T_U$ = +25 $^{\circ}\rm C.$

Mechanics/electronics

Supply voltage U _B	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	30 mA ³⁾
Switching output	PNP ⁴⁾
Switching mode	Dark switching ⁴⁾
Output current I _{max.}	≤ 100 mA ⁵⁾
Response time	< 0.5 ms ⁶⁾
Switching frequency	1,000 Hz ⁷⁾
Connection type	Male connector M8, 4-pin
Circuit protection	A ⁸⁾ B ⁹⁾ C ¹⁰⁾
Protection class	III
Weight	13 g
Polarisation filter	✓
Special device	✓
Housing material	Plastic, VISTAL®
Optics material	Plastic, PMMA
Enclosure rating	IP66 IP67 IP69K
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A.

Classifications

ECLASS 5.0	27270902
ECLASS 5.1.4	27270902
ECLASS 6.0	27270902
ECLASS 6.2	27270902
ECLASS 7.0	27270902
ECLASS 8.0	27270902
ECLASS 8.1	27270902
ECLASS 9.0	27270902
ECLASS 10.0	27270902

 $^{^{2)}\,\}text{May}$ not exceed or fall below U_{V} tolerances.

³⁾ Without load.

⁴⁾ Q = dark switching.

⁵⁾ At and above Tu 50 °C, a max. load current of Imax. = 50 mA is permitted.

⁶⁾ Signal transit time with resistive load.

⁷⁾ With light/dark ratio 1:1.

 $^{^{8)}}$ A = V_S connections reverse-polarity protected.

⁹⁾ B = inputs and output reverse-polarity protected.

 $^{^{10)}}$ C = interference suppression.


WL9-3F2234S20 | W9

SMALL PHOTOELECTRIC SENSORS

ECLASS 11.0	27270902
ECLASS 12.0	27270902
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528

Adjustments

Single teach-in button




- ③ LED indicator yellow: Status of received light beam
- ④ LED indicator green: power on
- ® Teach-in button

Connection type




Connection diagram



Characteristic curve


WL9-3, red light, 5 m



- ① Reflector PL80A
- ② Reflector P250
- ③ Reflector PL40A
- 4 Reflector PL20A
- ⑤ PL10F reflector
- © Reflective tape REF-IRF-56


Light spot size

WL9-3, red light, 5 m



Sensing range diagram


WL9-3, red light, 5 m



- ① Reflector PL80A
- ② Reflector P250F
- 3 Reflector PL40A
- 4 Reflector PL20F
- ⑤ PL10F reflector
- ® Reflective tape REF-IRF-56

Dimensional drawing (Dimensions in mm (inch))

WL9-3, WSE9-3



- ① Sender and receiver optical axis center
- ② Mounting hole M3 (Ø 3.1 mm)
- ③ LED indicator yellow: Status of received light beam
- 4 LED indicator green: power on
- ⑤ Connecting cable or connector
- Male connector M8, 4-pin
- 7 Male connector M12, 4-pin

Recommended accessories

Other models and accessories → www.sick.com/W9

	Brief description	Туре	Part no.		
Mounting brackets and plates					
	Mounting bracket, steel, zinc coated, mounting hardware included	BEF-WN-W9-2	2022855		
Reflectors					
	Rectangular, screw connection, 40 mm x 60 mm, PMMA/ABS, Screw-on, 2 hole mounting	PL40A	1012720		

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

