

9013GMG2J99H

Pumptrol, pump or compressor switch
9013GM, adjustable diff., factory setting



Main

Range of Product	Pumptrol
Pressure sensor name	9013GM
Pressure sensor size	35 psi (241.32 kPa) 5.5...30.5 psi (37.92...210.29 kPa)
Value of setting	Specify pressure settings
Electrical circuit type	Power circuit
Product Specific Application	Control electrically driven water pumps and air compressors
Quantity per Set	1
Type of Packing	Individual

Complementary

Pressure sensor type	Electromechanical pressure switch
Controlled fluid	Air 32...158 °F (-0...70 °C)) Fresh water 32...158 °F (-0...70 °C))
Adjustable range on rising pressure	10...35 psi (68.95...241.32 kPa)
Approximate adjustable differential	4...8 psi (27.58...55.16 kPa)
Destruction pressure	100 psi (689.48 kPa)
Pressure actuator	Diaphragm
Pressure switch type of operation	Regulation between 2 thresholds
Scale type	Adjustable differential
Setting	Internal
Local display	Without
Contacts type and composition	NC-NO, snap action, DPST-DB, Form Zb
Cable entry number	3 knock-outs for 1/2" conduit UL 508
Electrical connection	Screw-clamp terminals 10 AWG Screw-clamp terminals 5.261 mm²
Fluid connection type	0.25 inch NPSF internal UL 508
Short-circuit protection	20 A cartridge fuse gG
Materials in contact with fluid	Zinc plated steel or equivalent flange Nitrile (Buna-N) or equivalent rubber diaphragm
Material	Polypropylene: Cover Noryl thermoplastic resin or equivalent: Cover
Operating position	Any position
Motor power kW	1.5 KW 2 hp)230 V AC, 1 phase 0.37 KW 0.5 hp)115 V DC 0.37 KW 0.5 hp)230 V DC 0.75 KW 1 hp)115 V AC, 1 phase 1.5 KW 2 hp)460 V AC, 1 phase 1.5 kW 2 hp)575 V AC, 1 phase
Electrical durability	100000 cycles 10 cyc/mn
Mechanical durability	300000 cycles
Terminal block type	4 terminals
Maximum operating rate	10 cyc/mn
[Ui] rated insulation voltage	575 V UL 508
Net Weight	2.25 lb(US) (1.02 kg)
Repeat accuracy	+/- 3 %
Terminals description ISO n°1	L1-T1 L2-T2
Width	4.44 in (112.78 mm)

Height	5.8 in (147.32 mm)
Depth	4.44 in (112.78 mm)
Factory modification	-

Environment

Standards	UL 508 NSF ANSI 372 CE
Ambient air temperature for operation	-22...158 °F (-30...70 °C)
Ambient Air Temperature for Storage	-22...158 °F (-30...70 °C)
Protective treatment	None
NEMA degree of protection	NEMA 1 UL 50
IP degree of protection	IP20 conforming to IEC 60529
Product Certifications	CSA[RETURN]UL Listed

Ordering and shipping details

Category	US1CP7G21536
Discount Schedule	CP7G
GTIN	785901776697
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.40 in (31.484 cm)
Package 1 Width	4.88 in (12.395 cm)
Package 1 Length	31.48 in (79.969 cm)
Package 1 Weight	32.00 oz (907.185 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------