


THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



**NOTES**

- 1 MOUNTING HOLES WILL ACCEPT  $.087$  MAX DIA PINS OR SCREWS ON  $.186 \pm .002$  CENTERS
- 2 ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- 3 WEIGHT OF SWITCH ONLY IS  $.16$  OZ MAX WEIGHT OF SWITCH WITH WIRE LEADS IS  $.71$  OZ MAX


**CHARACTERISTICS**

|                     |          |
|---------------------|----------|
| OPERATING FORCE     | 5-17 OZ  |
| RELEASE FORCE       | 4 OZ MIN |
| RELEASE TRAVEL      | .004 MIN |
| DIFFERENTIAL TRAVEL | .005 MAX |
| OVERTRAVEL          | .004 MIN |

**ELECTRICAL DATA**

| CONTACT ARRANGEMENT       |                       |
|---------------------------|-----------------------|
| S P N O                   |                       |
| <b>28 VOLTS DC RATING</b> |                       |
| INDUCTIVE                 | SEA LEVEL --- 4 AMP   |
|                           | 50,000 FT --- 2.5 AMP |
| RESISTIVE                 | SEA LEVEL --- 7 AMP   |
|                           | 50,000 FT --- 7 AMP   |
| MAXIMUM INRUSH            | 24 AMP                |

THIRD ANGLE PROJECTION



SCALE 2:1

DO NOT SCALE PRINT

| UNLESS OTHERWISE SPECIFIED TOLERANCES ARE |        |            |
|-------------------------------------------|--------|------------|
| ONE PLACE                                 | (.0)   | $\pm .030$ |
| TWO PLACE                                 | (.00)  | $\pm .015$ |
| THREE PLACE                               | (.000) | $\pm .005$ |
| ANGLES                                    |        | $\pm$      |

WEIGHT (Note 3)

CATALOG LISTING  
5XE17-2  
PAGE 1 OF 1  
ISSUE  
5  
RELEASE NO. PR-12486  
CHECK  
REVISIONS  
A PR 12486  
SLB 14 OCT 83  
B CO 57328-A  
WJM 15 APL 85  
C CO 60773  
MAP 7 NOV 86  
D CO 96069  
DLM 18 FEB 00  
CHECK  
18 OCT 83  
CEC  
CHECK  
14 OCT 83  
DRAWN  
FORMTEK