




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

D.C. RESISTANCE (@20°C):	7-8 (5+6+7, 8+9+10), 0.010 Ohms max. 1-3, 0.500 Ohms max. (.120typ.)
DIELECTRIC RATING:	1000VAC, 1 minute tested by applying 1250VAC for 1 second between PRI - SEC
INDUCTANCE:	5.0μH ±10%, 50kHz, 10mVAC, 0mADC, 7-8(tie 5+6+7, 8+9+10), Ls.
LEAKAGE INDUCTANCE:	100nH max., 100KHz, 1.0VAC, 7-8(tie 1+3, 5+6+7, 8+9+10), Ls.
URNS RATIO:	( 13-3 ):( 1-13 ), ( 1 ):(1.00), ±1%. ( 1-3 ):( 5-10 ), ( 10 ):(1.00), ±1%. ( 1-3 ):( 6-9 ), ( 10 ):(1.00), ±1%. ( 1-3 ):( 7-8 ), ( 10 ):(1.00), ±1%.

T\_0\_4473

<b>Midcom, Inc.</b> Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: ±1°      Fractions: ±1/64 Decimals: ±.005(.127mm)		<b>Midcom, Inc.</b>	
	Drawing Title <h2 style="text-align: center;">Transformer</h2>		Drawing Number <h2 style="text-align: center;">750310349</h2>	Rev. 00
This drawing is dual dimensioned. Dimensions in brackets are in millimeters	Revisions: See Sheet 1		Scale ----	Sheet 2 of 5
Engineer:APS			10/30/2007	