

# Product data sheet

Specifications



Miniature plug in relay, Harmony, 6A, 4CO, with LED, lockable test button, 48V AC

RXM4AB2E7

Product availability : Stock - Normally stocked in distribution facility

## Main

|                               |                                  |
|-------------------------------|----------------------------------|
| Range of Product              | Harmony Electromechanical Relays |
| Series name                   | Miniature                        |
| Product or Component Type     | Plug-in relay                    |
| Device short name             | RXM                              |
| Contacts type and composition | 4 C/O                            |
| [Uc] control circuit voltage  | 48 V AC 50/60 Hz                 |
| Status LED                    | With                             |
| Control Type                  | Lockable test button             |
| Utilisation coefficient       | 20 %                             |

## Complementary

|  |   |
|--|---|
| Shape of pin                           | Flat  |
| [Ui] rated insulation voltage          | 250 V IEC<br>300 V CSA<br>300 V UL  |
| [Uimp] rated impulse withstand voltage | 2.5 kV 1.2/50 µs  |
| Contacts material                      | AgNi  |
| [Ie] rated operational current         | 3 A 28 V DC) NC IEC<br>3 A 250 V AC) NC IEC<br>6 A 28 V DC) NO IEC<br>6 A 250 V AC) NO IEC<br>6 A 277 V AC) UL<br>8 A 30 V DC) UL |
| Continuous output current              | 5 A   |
| Maximum switching voltage              | 250 V IEC   |
| Resistive rated load                   | 6 A 250 V AC<br>6 A 28 V DC   |
| Maximum switching capacity             | 1500 VA/168 W   |
| Minimum switching capacity             | 170 mW 10 mA, 17 V  |
| Operating rate                         | <= 1200 cycles/hour under load<br><= 18000 cycles/hour no-load  |
| Mechanical durability                  | 10000000 cycles   |
| Electrical durability                  | 100000 cycles resistive   |

|                                  |                        |
|----------------------------------|------------------------|
| Average coil consumption in VA   | 1.2 60 Hz              |
| Average consumption              | 1.2 VA 60 Hz           |
| Drop-out voltage threshold       | >= 0.15 Uc             |
| Operate time                     | 20 ms                  |
| Release time                     | 20 ms                  |
| Average coil resistance          | 710 Ohm 20 °C +/- 15 % |
| Rated operational voltage limits | 38.4...52.8 V AC       |
| Safety reliability data          | B10d = 100000          |
| Protection category              | RT I                   |
| Test levels                      | Level A                |
| Operating position               | Any position           |
| CAD overall height               | 3.26 in (82.8 mm)      |
| CAD overall depth                | 3.16 in (80.35 mm)     |
| Net Weight                       | 0.08 lb(US) (0.037 kg) |
| Device presentation              | Complete product       |

## Environment

|                                       |  |
|---------------------------------------|--|
| Dielectric strength                   | 1300 V AC between contacts with micro disconnection<br>2000 V AC between coil and contact with basic insulation<br>2000 V AC between poles with basic insulation |
| Product Certifications                | CSA<br>Lloyd's<br>UL<br>GOST<br>CE   |
| Standards                             | CSA C22.2 No 14<br>UL 508<br>EN/IEC 61810-1  |
| Ambient Air Temperature for Storage   | -40...185 °F (-40...85 °C)   |
| Ambient air temperature for operation | -40...131 °F (-40...55 °C)   |
| Vibration resistance                  | 3 gn +/- 1 mm 10...150 Hz)5 cycles in operation<br>5 gn +/- 1 mm 10...150 Hz)5 cycles not operating  |
| IP degree of protection               | IP40 conforming to EN/IEC 60529  |
| Shock resistance                      | 10 gnin operation<br>30 gnnot operating  |
| Pollution degree                      | 2  |

## Ordering and shipping details

|                   |                             |
|-------------------|-----------------------------|
| Category          | 21127-ZELIO ICE CUBE RELAYS |
| Discount Schedule | CP2                         |
| GTIN              | 3389119403825               |
| Returnability     | No                          |
| Country of origin | ID                          |

## Packing Units

|                              |                    |
|------------------------------|--------------------|
| Unit Type of Package 1       | PCE                |
| Number of Units in Package 1 | 1                  |
| Package 1 Height             | 0.79 in (2.000 cm) |

|                              |                         |
|------------------------------|-------------------------|
| Package 1 Width              | 0.87 in (2.200 cm)      |
| Package 1 Length             | 1.69 in (4.300 cm)      |
| Package 1 Weight             | 1.27 oz (36.000 g)      |
| Unit Type of Package 2       | BB1                     |
| Number of Units in Package 2 | 10                      |
| Package 2 Height             | 1.18 in (3.000 cm)      |
| Package 2 Width              | 4.06 in (10.300 cm)     |
| Package 2 Length             | 5.04 in (12.800 cm)     |
| Package 2 Weight             | 13.79 oz (391.000 g)    |
| Unit Type of Package 3       | S02                     |
| Number of Units in Package 3 | 240                     |
| Package 3 Height             | 5.91 in (15.000 cm)     |
| Package 3 Width              | 11.81 in (30.000 cm)    |
| Package 3 Length             | 15.75 in (40.000 cm)    |
| Package 3 Weight             | 21.70 lb(US) (9.842 kg) |


### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a>   |
| RoHS exemption information | <a href="#">Yes</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |
| Circularity Profile        | <a href="#">End of Life Information</a>  |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.   |


### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions



Pin Side View



Wiring Diagram



Symbols shown in blue correspond to Nema marking.

Electrical Durability of Contacts

Durability (inductive load) = durability (resistive load) x reduction coefficient.

Resistive AC load



- X Switching capacity (kVA)
- Y Durability (Number of operating cycles)
- A RXM2AB...
- B RXM3AB...
- C RXM4AB...
- D RXM4GB...

Reduction coefficient for inductive AC load (depending on power factor cos φ)



- Y Reduction coefficient (A)


Maximum switching capacity on resistive DC load



- X Voltage DC
- Y Current DC
- A RXM2AB...
- B RXM3AB...
- C RXM4AB...
- D RXM4GB...

**Note :** These are typical curves, actual durability depends on load, environment, duty cycle, etc.

AC Coil Voltage and Operating Temperature under continuous duty



X : Operating temperature (°C)  
Y : AC coil voltage (UC)

Recommended replacement(s)