

Round Cable Snap-It[™] (0461164181)



Part Number: 0461164181

61 ROUND CABLE CORE ASSEMBLY

Explanation of Part Numbers:

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade


Round cable snap-itTM can easily accommodate round cables or bundled wires with diameters from 2.5 mm (0.100) to 25.4 mm (1.000). These assemblies are available in four ferrite material classes to suppress differential or common-mode conducted EMI from 1 MHz into the GHz region. The polypropylene cases are meeting the RoHS restrictions of hazardous substances and have a flammability rating of UL 94 V-0.

Many of the snap-itTM parts have round core equivalents. See Round Cable EMI Suppression Cores.

Round Cable Snap-ItTM Kits are available for each of the four suppression materials. 31 Snap-ItTM Kit (0199000030), 43 Snap-ItTM Kit (0199000031), 46 Core and Snap-ItTM Kit (0199000032) and 61 Snap-ItTM Kit (0199000033).

Catalog Drawing 3D Model

SNAP-IT™ DIAMETER RANGE



The B dimension is the core inside diameter.

Weight: 61 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	30	+/- 1.5	1.181	
В	12.75		0.502 min	
С	39.5	+/- 2.0	1.555	_
D	15.50	+/75	0.61	_

Cable Information						
Max Diameter	Max Dimension	Solid Equivalent	Flat Cable Cores			
12.7 0.5	_	2661102002	-			

Chart Legend

+ Test frequency

•For solid cable cores, see Round Cable EMI Suppression Cores

Typical Impedance (Ω)		
100 MHz	224	
250 MHz ⁺	360	
500 MHz ⁺	500	
1000 MHz	365	

Round cable snap-itTM assemblies are controlled for impedances only. Minimum impedance values are specified for the + marked frequencies. The minimum impedance is typically the listed impedance less 20%.

Catalog Drawing

Single turn impedance tests for 31, 43 and 46 material cores are performed on the E4991A/HP4291B Impedance Analyzer. The 61 material parts are tested on the E4991A / HP4291B Impedance Analyzer and 75 material parts are tested on the E4990A Impedance Analyzer. Cores are tested with the shortest practical wire length.

