

WL24-2B240 W24

**COMPACT PHOTOELECTRIC SENSORS** 





#### Ordering information

Туре	Part no.
WL24-2B240	1017859

Other models and accessories → www.sick.com/W24

Illustration may differ



#### Detailed technical data

#### **Features**

Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	Dual lens
Dimensions (W x H x D)	27 mm x 87.5 mm x 65 mm
Housing design (light emission)	Rectangular
Sensing range max.	0 m 22 m <sup>1)</sup>
Sensing range	0 m 15 m <sup>1)</sup>
Type of light	Visible red light
Light source	LED <sup>2)</sup>
Light spot size (distance)	Ø 250 mm (15 m)
Adjustment	Potentiometer

<sup>1)</sup> Reflector PL80A.

#### Mechanics/electronics

Supply voltage U <sub>B</sub>	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Current consumption	50 mA <sup>3)</sup>
Switching output	NPN, PNP

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

 $<sup>^{2)}</sup>$  Average service life: 100,000 h at TU = +25 °C.

 $<sup>^{2)}\,\</sup>mbox{May}$  not exceed or fall below  $\mbox{U}_{\mbox{\scriptsize V}}$  tolerances.

<sup>3)</sup> Without load.

 $<sup>^{4)}</sup>$  Signal transit time with resistive load.

<sup>5)</sup> With light/dark ratio 1:1.

 $<sup>^{6)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

 $<sup>^{7)}</sup>$  C = interference suppression.

<sup>8)</sup> D = outputs overcurrent and short-circuit protected.

<sup>9)</sup> Reference voltage: 50 V DC.

 $<sup>^{10)}</sup>$  Static, low heat output, use in +5 ° C ... +15 ° C.

Switching mode	Light/dark switching
Switching mode selector	Selectable via PNP/NPN selector, selectable via light/dark selector
Output current I <sub>max.</sub>	≤ 100 mA
Response time	≤ 500 µs <sup>4)</sup>
Switching frequency	1,000 Hz <sup>5)</sup>
Time functions	On delayoff delay
Delay time	Adjustable via time delay selector switch, 0.5 s 10 s
Connection type	Terminal connection with M16 gland
Circuit protection	A <sup>6)</sup> C <sup>7)</sup> D <sup>8)</sup>
Protection class	П <sup>9)</sup>
Weight	330 g
Polarisation filter	<b>✓</b>
Front screen heating	<b>✓</b> <sup>10)</sup>
Housing material	Metal, zinc diecast
Optics material	Plastic, PMMA
Enclosure rating	IP67
Test input sender off	TE to 0 V
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493

 $<sup>^{1)}\,\</sup>mathrm{Limit}$  values when operated in short-circuit protected network: max. 8 A.

#### Safety-related parameters

MTTF <sub>D</sub>	588 years
<b>DC</b> <sub>avg</sub>	0 %
T <sub>M</sub> (mission time)	20 years

#### Classifications

ECLASS 5.0	27270902
ECLASS 5.1.4	27270902
ECLASS 6.0	27270902
ECLASS 6.2	27270902
ECLASS 7.0	27270902
ECLASS 8.0	27270902

 $<sup>^{2)}\,\</sup>mbox{May}$  not exceed or fall below  $\mbox{U}_{\mbox{\scriptsize V}}$  tolerances.

<sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Signal transit time with resistive load.

<sup>5)</sup> With light/dark ratio 1:1.

 $<sup>^{6)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

 $<sup>^{7)}</sup>$  C = interference suppression.

 $<sup>^{8)}</sup>$  D = outputs overcurrent and short-circuit protected.


<sup>9)</sup> Reference voltage: 50 V DC.

 $<sup>^{10)}</sup>$  Static, low heat output, use in +5 ° C ... +15 ° C.

ECLASS 8.1	27270902
ECLASS 9.0	27270902
ECLASS 10.0	27270902
ECLASS 11.0	27270902
ECLASS 12.0	27270902
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528


# Adjustments

WT24-2, WL24-2, WS/WE24-2, DC, with time functions




- ② LED signal strength indicator
- Sensitivity control
- Light/dark selector
- NPN/PNP changeover switch
- 1 Time control  $t_2$ = OFF delay
- Time control t<sub>1</sub>= ON delay
- Time delay selector switch

## Connection type




## Connection diagram

#### Cd-120



#### Characteristic curve



- ① Reflector PL80A
- ② Reflector PL50A
- 3 Reflector PL40A
- ④ Reflector PL30A
- ⑤ Reflector PL20A
- ® Reflective tape Diamond Grade
- ⑦ Reflector C110A


## Sensing range diagram

①     0.03     15     22       ②     0.03     11     16       ③     0.03     11     16       ④     0.03     7     10       ⑤     0.03     7     10
3 0.03 11 16 4 0.03 7 10
(5) 0.03 7 10
6 0.03 7 10
7 0.15 10 13
0 4 8 12 16 20 24 (13.12) (26.25) (39.37) (52.49) (65.62) (78.7

- Sensing range
- Sensing range max.
- ① Reflector PL80A
- ② Reflector PL50A
- 3 Reflector PL40A
- ④ Reflector PL30A
- ⑤ Reflector PL20A
- ® Reflective tape Diamond Grade
- ⑦ Reflector C110A

#### Dimensional drawing (Dimensions in mm (inch))

#### WL24-2



- ① Alignment sight
- ② LED signal strength indicator
- 3 Center of optical axis, sender
- 4 Center of optical axis, receiver
- ⑤ M5 threaded mounting hole, 6 mm deep
- M5 threaded mounting hole, through-hole
- $\ensuremath{\mathfrak{T}}$  M16 screw fixing and plug rotatable by 90  $^\circ$

#### Recommended accessories

Other models and accessories → www.sick.com/W24

	Brief description	Туре	Part no.	
Mounting brad	Mounting brackets and plates			
3	Mounting bracket, large, stainless steel, without mounting hardware for the sensor	BEF-WG-W24	4026324	
	Universal mounting bracket for reflectors, steel, zinc coated	BEF-WN-REFX	2064574	
Reflectors				
	Rectangular, screw connection, 84 mm x 84 mm, PMMA/ABS, Screw-on, 2 hole mounting	PL80A	1003865	

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

